

HSM® Classic

225.2 document shredder

Ideal central device for large offices



- Automatic start/stop control via electronic eye
- Automatically stops when container is full or door is open
- New auto stop with LED plus auto reverse in case of paper jam
- Additional safety shield for easy feed of CD/DVDs
- Hardened 100% solid steel cutters can handle occasional standard paper clips or staples
- Powerful, specially adjusted motor for longer periods of use - with thermal protection for high performance
- Cutting rollers with patented V-groove complete with a lifetime warranty
- Tried and tested closed-tooth wheel drive prevents penetration of dirt and slows wear, increasing the service life
- Enclosed housing protects against the spread of paper dust
- Mobile for shared use
- Cross cut & micro cut shredders should be oiled regularly to maintain top working condition
- Optional auto-oiler available for cross-cut and micro cut models.
- Uses a 58 gallon capacity shred bag; Part #HSM2117



HSM part#	HSM1341	HSM1343	HSM1344
Cutting type	Strip cut	Cross cut	Micro cut
Cutting size	1/4"	1/8" x 1 1/2"	1/32" x 7/16"
Security level DIN 32757-1	2	3	5
Security level DIN 66399	P-2 / O-2 / T-2 / E-2	P-4 / O-3 / T-4 / E-3 / F-1	P-6 / F-3
Cutting capacity per run in sheets	40- 42	25 - 27	10 - 11
Cutting Speed	25 ft / min	27 ft / min	26 ft / min
Throat opening	12"	12"	10"
Motor at max. no. of sheets	1440W	1440W	1440W
Motor power (horsepower)	1.93	1.93	1.93
Voltage	115 V / 60Hz	115 V / 60Hz	115 V / 60Hz
Dimensions (H x W x D)	35 1/5" x 19 7/10" x 18 1/2"	35 1/5" x 19 7/10" x 18 1/2"	35 1/5" x 19 7/10" x 18 1/2"
Weight	93 lbs	99 lbs	106 lbs
Shred-bin volume	31.7 gal	31.7 gal	31.7 gal
Cutting capabilities			

All technical specifications are approximate values. Technical and design modifications reserved.

HSM of America, LLC
419 Boot Road
Downingtown, PA 19335
www.hsmofamerica.com
Customer Service: 800.613.2110

Great Products, Great People.

HSM®