



Westinghouse

SPECIFICATION SHEET

Item Number **7214100**

Harmony Ceiling Fan

48" Brushed Nickel Finish Weathered Maple Blades
Includes Light Kit with Opal Frosted Glass

Specifications

Size	48"
Blades.....	Plywood Blades (Weathered Maple)
Blade Pitch.....	13°
Approved Location	Indoor
Suggested Room Size	Large Room (up to 15x15)
Down Rod.....	3/4" x 6"
Installation.....	Down Rod Only
Max. Ceiling Angle.....	20°
Lead Wire	78"
Light Bulb Usage.....	Includes (2) Candelabra (E12) Base, 40 Watt Torpedo Lamps
Control.....	Remote Control Adaptable
Motor Finish.....	Brushed Nickel
Motor Material	Silicon Steel Motor 153mm x 20mm
Reverse Airflow.....	Yes
Capacitor	Triple
Switch Housing Cap.....	Not Included



Energy Information


Airflow Efficiency.....	92 Cubic Feet Per Minute Per Watt
Electricity Use.....	53 Watts (excludes lights)
Airflow.....	4881 Cubic Feet per Minute
Max rpm	N/A

Warranty

Ceiling fans backed by our Limited Lifetime Warranty have a lifetime motor warranty and a 2-year warranty on all other parts.



A. Top of Canopy to Bottom of Blades	10.6"
B. Top of Canopy to Bottom of Switch House	12.8"
C. Top of Canopy to Bottom of Canopy	2"
D. Width of Motor Housing.....	7.5"
E. Width of Canopy.....	6"
F. Top of Canopy to Bottom of Glass	17.1"



Specifications are subject to change without notice, please visit www.westinghouselighting.com for latest information.

Call 1-800-999-2226 or visit www.westinghouselighting.com.

©, WESTINGHOUSE, and INNOVATION YOU CAN BE SURE OF are registered trademarks of Westinghouse Electric Corporation. Used under license by Westinghouse Lighting. All Rights Reserved.