



Westinghouse

SPECIFICATION SHEET

Item Number 7224500

Wengue Ceiling Fan

30" Espresso Finish Reversible Blades (Espresso/Dark Cherry) Includes Light Kit with Opal Frosted Glass

Specifications

Size	30"
Blades.....	Reversible MDF Blades (Espresso/Dark Cherry)
Blade Pitch.....	18°
Approved Location	Indoor
Suggested Room Size	Small Room (10x10) or smaller
Down Rod.....	3/4" x 4"
Installation.....	Down Rod Only
Max. Ceiling Angle.....	18°
Lead Wire	78"
Light Bulb Usage.....	Includes (2) Candelabra (E12) Base, 40 Watt G16 1/2 Lamps
Control.....	Remote Control Adaptable
Motor Finish.....	Espresso
Motor Material	Silicon Steel Motor 153mm x 9mm
Reverse Airflow.....	Yes
Capacitor	Dual
Switch Housing Cap.....	Not Included



Reversible Dark Cherry Finish Blades

Energy Information


Airflow Efficiency.....	53 Cubic Feet Per Minute Per Watt
Electricity Use.....	34 Watts (excludes lights)
Airflow.....	1816 Cubic Feet per Minute
Max rpm	125

Warranty

Ceiling fans backed by our Limited Lifetime Warranty have a lifetime motor warranty and a 2-year warranty on all other parts.



A. Top of Canopy to Bottom of Blades	9"
B. Top of Canopy to Bottom of Switch House	10.4"
C. Top of Canopy to Bottom of Canopy	2.5"
D. Width of Motor Housing.....	6.8"
E. Width of Canopy.....	5.1"
F. Top of Canopy to Bottom of Glass	12.1"



Specifications are subject to change without notice, please visit www.westinghouselighting.com for latest information.

Call 1-800-999-2226 or visit www.westinghouselighting.com.

©, WESTINGHOUSE, and INNOVATION YOU CAN BE SURE OF are registered trademarks of Westinghouse Electric Corporation. Used under license by Westinghouse Lighting. All Rights Reserved.