



Westinghouse

SPECIFICATION SHEET

Item Number 7226565

Xavier Ceiling Fan

44" Brushed Nickel Finish with Copper Accents
Reversible Blades (Maple/Mahogany) Includes Light Kit
with Spot Lights

Specifications

Size	44"
Blades.....	Reversible MDF Blades (Maple/Mahogany)
Blade Pitch.....	13°
Approved Location	Indoor
Suggested Room Size	Large Room (up to 15x15)
Down Rod.....	3/4" x 4"
Installation.....	Combo
Max. Ceiling Angle.....	17°
Lead Wire	78"
Light Bulb Usage.....	Includes (3) GU10 Base, 50 Watt MR16 Halogen Lamps
Control.....	Remote Control Adaptable
Motor Finish.....	Brushed Nickel
Motor Material	Silicon Steel Motor 153mm x 15mm
Reverse Airflow.....	Yes
Capacitor	Triple
Switch Housing Cap.....	Included



Reversible Mahogany
Finish Blades

Energy Information


Airflow Efficiency.....	67 Cubic Feet Per Minute Per Watt
Electricity Use.....	65 Watts (excludes lights)
Airflow.....	4381 Cubic Feet per Minute
Max rpm	210

Warranty

Ceiling fans backed by our Limited Lifetime Warranty have a lifetime motor warranty and a 2-year warranty on all other parts.



A. Top of Canopy to Bottom of Blades	16"
B. Top of Canopy to Bottom of Switch House	17.5"
C. Top of Canopy to Bottom of Canopy	2"
D. Width of Motor Housing.....	10"
E. Width of Canopy.....	5"
F. Top of Canopy to Bottom of Glass	22.5"



Specifications are subject to change without notice, please visit www.westinghouselighting.com for latest information.

Call 1-800-999-2226 or visit www.westinghouselighting.com.

©, WESTINGHOUSE, and INNOVATION YOU CAN BE SURE OF are registered trademarks of Westinghouse Electric Corporation. Used under license by Westinghouse Lighting. All Rights Reserved.