



4 Channel DVR | Real-time | D1 Resolution | H.264

QT454

Features:

- 4 Channel Real-time D1 Resolution DVR
- Remote internet monitoring (up to 10 users at the same time)
- Mobile Phone Surveillance
- Compatible with MAC and PC
- Customize up to 4 cameras when you need
- Zoom in on live or playback footage with 2X digital zoom!
- Receive instant email alerts and snapshot images when motion is detected
- Send email alerts up to 3 different email addresses
- Backup and retain important footage on a PC, Flash Drive or USB Hard Drive
- Video is captured in real-time, broadcast-quality D1 on each channel (704x480 pixel resolution at a rate of 30 frames per second per camera), which results in smooth, continuous video motion and a larger D1 video image for improved recognition of people a
- Manage and monitor multiple QT-series DVRs with Central Management Software (CMS).

What's Included:

- (1) 4 Channel Full D1 real-time DVR
- (1) Power supply for DVR 12V /3A
- RJ-45 Ethernet network cable
- BNC to RCA Video cable
- Remote control
- USB Mouse
- CD with manuals and software
- Quick Start Guide

Remote Monitoring Compatibility:



System Compatibility:



Windows XP, Vista, 7



Mac OS X 10.6 & 10.7

Specification:

DVR

| | |
|-----------------------------|--|
| DVR Model | QT454 |
| Video Compression | Advanced H.264 |
| Max Hard Drive Storage | Supports 1 SATA HDD up to 2 TB |
| Backup Via | PC, Flash Drive, USB Hard Drive |
| Power | DC 12V / 3A (Adapter Included) |
| Operating Temperature | 50°F-104°F / 10°C-40°C |
| Full D1 Recording Option | Real Time: 120 FPS (30 FPS Per Channel) |
| Full D1 Playback Resolution | 704x480 |
| Recording Mode | Motion Detection, Time Schedule, Alarm Trigger, Manual |
| USB Interface | USB Mouse, USB Backup |
| Video Inputs/Outputs | 4 BNC Input(s)/1 VGA Output(s)/1 BNC Output(s) |
| Audio Inputs/Outputs | 4 RCA Input(s) /1 RCA Output(s) |
| Alarm Sensor Inputs/Outputs | 4 Input(s)/1 Output(s) |
| Network Interface | RJ-45 for Router Connection Enabling Remote Monitoring |
| Pan/Tilt/Zoom Control | 1 RS-485 Connection (PTZ Camera Not included) |
| DVR Dimensions/Weight | 15"x 11"x 4" / 4lbs |

Viewing

| | |
|-----------------------------|---|
| Live Display Resolution | 704x480 |
| Display Modes | Single Camera, Split Screen Multi-Camera, Auto-Sequence |
| Video Search | Time, Motion Detection, Alarm Trigger, Manual |
| Computer System Support | Windows XP, Vista, 7, Mac OS X 10.6 & 10.7 |
| Compatible Browsers | Chrome, Internet Explorer, Mozilla Firefox, Safari |
| Mobile Phone Support | Android, BlackBerry 5, 6 & 7, iPhone/iPad, Windows Mobile Pro 5, 6 & Phone 7, Symbian |
| Simultaneous Remote Viewers | Up to 10 Users |
| Stream | Dual Stream |