



## CSHT1208TNC2G Home Theater Surge Protector

Offering vital surge protection for your home theater equipment from damaging electrical surges.

The CyberPower Home Theater Series CSHT1208TNC2G Surge Protector is ideal for home entertainment and Home Office protection with 4350 joules, 12 outlets, and an 8 ft. cord. The surge protector provides protection for HDTVs, cable/satellite receivers, personal computers, cable modems, phones/fax/DSL, printers, stereos, and CD/DVD players.

Master controlled outlets reduce energy costs by turning off idle peripherals. The CSHT1208TNC2G has a single master outlet that will control up to six devices attached to the master controlled outlets. When the master device is turned off or goes into power saving standby mode, the master controlled outlets will automatically shut off power to the attached devices to save energy.

A Limited Lifetime Warranty ensures that this surge protector has passed our highest quality standards in design, assembly, material or workmanship and further protection is offered by a \$500,000 Connected Equipment Guarantee.

### Typical Applications

- HDTVs
- Cable/Satellite Receivers
- Desktop Computers
- Personal Electronics

### Features

- 12 Surge Protected Outlets
- 6 Energy-Saving Outlets
- 4350 Joules of Surge Protection
- DSL / Phone / Fax Protection – RJ11
- Network Device Protection – RJ45
- Cable / Satellite Protection – RG6
- 15A Circuit Breaker
- 8 ft. Cord
- EMI/RFI Noise Filters
- Lifetime Warranty

# CSHT1208TNC2G Home Theater Surge Protector

Offering vital surge protection for your home theater equipment from damaging electrical surges.

GENERAL	
Product Type	Surge Protector
INPUT	
Voltage	125V
Rotating Power Cord	None
Switch	Non Lighted On/Off - Reset
Circuit Breaker	15 Amp
Plug Type	NEMA 5-15P
Plug Style	Right Angle - 45° Offset
Cord Length	8'
OUTPUT	
Outlets - Total	12
Outlet Type	NEMA 5-15R
Outlets - Energy Saving	6
Outlets - Widely Spaced	4
SURGE PROTECTION & FILTERING	
Surge Suppression	4350 Joules
Maximum Surge Current	210,000 Amps
Maximum Surge Current H-N	150,000 Amps
Maximum Surge Current H-G	30,000 Amps
Maximum Surge Current N-G	30,000 Amps
Clamping Voltage	330V (L-N) 400V (L-G, N-G)
Response Time	< 1 nanosecond
Phone Protection RJ11	1-In, 2-Out
Network Protection RJ45	1 in / 1 out
Coaxial Protection RG6	2 Pair
EMI/RFI Filtration	150 kHz to 100 MHz
Attenuation	Up to 43dB
INDICATORS	
Indicators	Protected (Green), Grounded (Green)
PHYSICAL	
Keyhole Mounting Slots	Yes
Cord Management	Yes
Safety Covers	Yes
CERTIFICATIONS	
Safety	UL1363 / UL1449 3rd Edition, cUL
Environmental	RoHS Compliant
WARRANTY	
Product Warranty	Limited Lifetime
Connected Equipment Guarantee	Lifetime
CEG Amount	\$500,000