



**Tripp Lite**  
1111 West 35th Street  
Chicago, IL 60609 USA  
Telephone: +(773) 869 1234  
E-mail: [saleshelp@tripplite.com](mailto:saleshelp@tripplite.com)

## Model #: B094-008-2E-M-F

### 8-Port Serial Console / Terminal Server Management Switch



### Highlights

- Dual Ethernet, and Built-in Modem for Out of Band Access
- Secure In-band and Out-of-band access for a Host of Equipment
- Manage all equipment in the rack: Servers, UPS, Routers, Switches, Firewalls, etc
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases
- Made in the USA

### Description

Tripp Lite's B094-008-2E-M-F is the most advanced console / terminal server platform available today. In one secure appliance, it offers an in-band and out-of-band management solution for serial console ports, servers, virtual servers, service processors, UPS & PDUs, environmental monitoring and more. This 8 port console server management switch enables system administrators to securely access and control their data centers and networks from anywhere in the world. And this enterprise level unit is equipped with a built in modem, dual Ethernet NIC, 4 gigs USB flash, and runs on Linux for scalability and reduced downtime.

The B094-008-2E-M-F offers advanced software features that surpass the requirements of even the most demanding applications. These features include Network UPS Tools for UPS monitoring, PowerMan for integrated PDU and RPS functions with in session hotkey support, Pattern match alerting, Open access to the Linux shell for scripting, heartbeat monitoring with automatic fail-over, Cisco pinouts and much more. Made in the USA. Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases.

### Package Includes

- B094-008-2E-M-F 8port Console Server with dual NIC and Modem
- 2 x Cat5 Blue Patch Cable
- DB9F-RJ45 Adapter: 1 Straight pinned and 1 Crossed
- External Power Supply
- Quick Start Guide and CD-ROM

### Features

- Built in modem for out-of-band dial-in access
- 4 Gigabyte local FTP/TFTP storage for device configuration files
- IPsec VPN support
- Secure Shell (SSH V2 and V3)
- TACACS+, RADIUS and LDAP authentication
- PAP/CHAP authentication (dial up)
- Local authentication
- System event syslog
- SSH port and IP forwarding support
- IP packet filtering
- Break over SSH support
- Port triggers with SMNP and email alerts
- Offline data logging (Syslog, NFS, CIFS)
- Online data buffering and logging
- Multiple users per port (with port sniffing)
- Telnet/SSH/Raw TCP connect

- RFC 2217 - Port Redirection
- Integrated AJAX serial console and system terminal via web interface
- Native IPMI 1.5 and 2.0 (RMCP/RMCP+) support for BMC and service processor access and control
- Service processor access (IPMI, ILO, LOM and more)
- Access to KVM built in to service processors (DRAC, RSA)
- Limit user access by LAN device and SDT service for that device
- Port triggers with SMNP and email alerts for all tunnel traffic
- Each gateway can port forward to an unlimited number of locally networked hosts (computers, routers)
- Embedded DHCP server for management LAN devices
- Network UPS Tools for UPS Monitoring and Management
- PowerMan for PDU and RPS Management
- Command Line interface (Linux Shell)
- NAGIOS distributed monitoring
- Out-of-band (dial-up modem access) included - V.92 Serial Data/Fax Embedded Modem 3.3V Model, 14.4K Fax
- Linux with source code access
- Constructed of heavy-duty steel housing

## Specifications

OVERVIEW	
IP Remote Access	YES, BUILT IN
PHYSICAL	
Unit Dimensions (HWD/in)	1.4 x 6.5 x 4
Unit weight (lbs)	4
ENVIRONMENTAL	
Operating Temperature Range	Ambient operating temperature: 5C to 50C (41F to 122F)
Storage Temperature Range	Non operating storage temperature: -30C to +60C (-20F to +140F)
Relative Humidity	5% to 90%
BTUs	120V: 52 BTU per hour
Power Consumption (Watts)	
CONNECTIONS	
Ports	8
Other Ports - Port 1	RJ45 LAN x 2
Other Ports - Port 2	USB x 2
Other Ports - Port 3	RJ11 Modem
CERTIFICATIONS	
Approvals	FCC Part 15 A, UL 1950, CE (EN55022 A, EN55024, EN60950), TUV, C-Tick
WARRANTY	
Product Warranty Period (Worldwide)	2-year limited warranty

## Related Items

### Required Products

Related Model	Description	Qty.
B090-A9F	DB9F - RJ45 Modular Serial Adapter	1

B090-A9F-X	DB9F - RJ45 Modular Serial Adapter	1
B090-A9M	DB9M - RJ45 Modular Serial Adapter	1
N001-007-BK	7-ft. Cat5e 350MHz Snagless Molded Cable (RJ45 M/M) - Black	1
N001-014-BK	14-ft. Cat5e 350MHz Snagless Molded Cable (RJ45 M/M) - Black	1
N001-025-BK	25-ft. Cat5e 350MHz Snagless Molded Cable (RJ45 M/M) - Black	1
N201-007-BK	7-ft. Cat6 Gigabit Snagless Molded Patch Cable (RJ45 M/M) - Black	1
N201-014-BK	14-ft. Cat6 Gigabit Snagless Molded Patch Cable (RJ45 M/M) - Black	1
N201-025-BK	25-ft. Cat6 Gigabit Snagless Molded Patch Cable (RJ45 M/M) - Black	1

**Optional Products**

Related Model	Description	Qty.
B092-016	16-Port Serial Console / Terminal Server with Built-in PowerAlert and KVM inputs	1
B095-003-1E-M	3 Port IP Serial Console / Terminal Server Built-in Modem	1
B095-004-1E	4 Port IP Serial Console / Terminal Server	1
B096-016	16-Port Serial Console / Terminal Server Management Switch	1
B096-048	48-Port Serial Console / Terminal Server Management Switch	1

More information, including related products, owner's manuals, and additional technical specifications, can be found online at [www.tripplite.com/en/products/model.cfm?txtModelID=5065](http://www.tripplite.com/en/products/model.cfm?txtModelID=5065).

Copyright © 2012 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.