


## Configuration

### Samsung Colour Laser Multifunction Printer CLX-3305FN



## Specifications

### CLX-3305FN

<b>Print</b>	
Speed (Mono)	Up to 18 ppm in A4 (19 ppm in Letter)
Speed (Colour)	Up to 4 ppm in A4 (4 ppm in Letter)
First Print Out Time (Mono)	Less than 14 seconds (From Ready Mode)
First Print Out Time (Colour)	Less than 26 seconds (From Ready Mode)
Resolution	Up to 2,400 x 600 dpi effective output (600x600x2bit)
Emulation	SPL-C (Samsung Printer Language), PCL-5c, PCL-6c, PS3, URF
Duplex	Manual
<b>Copy</b>	
Speed (Mono)	Up to 18 cpm in A4 (19 cpm in Letter)
Speed (Colour)	Up to 4 cpm in A4 (4 cpm in Letter)
First Copy Out Time (Mono)	Less than 14 sec (Platen)
First Copy Out Time (Colour)	Less than 36 sec (Platen)
Zoom Rate	25 - 400 % (ADF, Platen)
Multi Copy	1 - 99 pages
Copy Features	Auto-fit Copy, N-up Copy, ID Copy
<b>Scan</b>	
Compatibility	TWAIN Standard / WIA Standard
Method	Colour CIS
Resolution (Optical)	Up to 600 x 600 dpi
Resolution (Enhanced)	Up to 4,800 x 4,800 dpi
Scan to	PC, USB, Application
<b>Fax</b>	
Compatibility	ITU-T G3 / ECM
Modem Speed	33.6Kbps
Resolution	Up to 300 x 300 dpi (Mono), Up to 200 x 200 dpi (Colour)
Memory	5 MB
Auto Dial	Yes
Fax Feature	Speed Dial / Auto Redial / Last Number Redial / Distinctive Ring / Caller ID / External Phone Interface / Colour Fax / Secure Receive
<b>Paper Handling</b>	
Input Capacity and Types	150-sheet Cassette
Output Capacity and Type	50-sheet Face Down
Media Size	76 x 152.4 mm (3" x 6") ~ 216 x 355.6 mm (8.5" x 14")
Media Type	Plain Paper / Thin Paper / Bond / Pre-Printed / Recycled / Label / CardStock / Thick / Cotton / Coloured / Glossy
ADF Capacity	40-sheet
ADF Document Size	148 mm (5.8") ~ 216 x 356 mm (8.5" x 14")
<b>General Feature</b>	
Processor	Dual CPU (Main: 533 MHz, Sub: 150MHz)
Display	2-Line LCD
Interface	Hi-Speed USB 2.0 / 10/100 Base Tx
Noise Level	Less than 46 dBA (Colour Printing), Less than 48 dBA (Mono Printing) / Less than 52dBA (Copying) / Less than 53dBA (ADF)
Memory/Storage	128 MB
OS Compatibility	Windows XP/2003/Vista/2008/7/2008 R2 / Mac OS X 10.4~10.7/Various Linux
Duty Cycle, Monthly	Up to 20,000 images
Dimension (WxDxH)	406 x 362 x 333.5mm (16" x 14.3" x 13.1") (except paper tray)
Weight	13.98 kg (30.82 lb)
Power Consumption	290 W (Printing) / 60 W (Standby) / 1.6 W (Sleep)
<b>Consumables</b>	
Black Toner Cartridge	Average Cartridge Yield 1,500 *Standard pages (Ships with 700 pages Starter Toner Cartridge) *Declared cartridge yield in accordance with ISO/IEC 19798
Yellow/Magenta/Cyan Toner Cartridge	Average Cartridge Yield 1,000 *Standard pages (Ships with 500 pages Starter Toner Cartridge) *Declared cartridge yield in accordance with ISO/IEC 19798
Waste Toner Container	Approx. 7,000 images

Distributed by

## CLX-3305FN Colour Laser Multi-Function Printer

For your daily life





## True on colour Compact on size

### Samsung Colour Laser Multifunction Printer CLX-3305FN

With the CLX-3305FN you can enjoy superior colour printing output at your home office without sacrificing your precious space.

## True colour quality for your documents

Text, graphs or images - the CLX-3305FN helps you print anything in brilliant quality that meets even the highest expectations.



ReCP (Rendering engine for clean pages) technology gives you sharper text, cleaner images and brilliant looking prints every time.



Our newly developed polymerized toner has smaller and more uniform particles, resulting in crisper lines and glossier colours.



Create and use your own colour profiles with Samsung's Easy Colour Manager. Match the exact colours of a company logo or simply give your print outs the individual look you want.



Its 600x600 dpi can be enhanced to an impressive 2,400x600 dpi by varying the dots size and the position of the dot itself. This means you can print more detail and have smoother and sharper images.

## Compact design

Don't worry about this printer crowding your space. Its beautiful and compact design makes it a pleasure to share a desk with.



With a footprint of just 40.6 x 36.2 cm, it's one of the world's smallest colour laser MFPs.



Its ergonomic design with ebony brown and ice grey colour creates a modern and elegant work environments.

## Easy to use

Designed for simple and intuitive operation the CLX-3305FN saves you precious time and effort.



Easy Document Creator helps you create digital documents in multiple formats such as '.epub' file format for E-book support and makes it easy to share them with others - via e-mail, fax or social networks.



Easily print images and documents directly from a USB memory stick with the intuitive menu and navigation keys.



Just one push of the Eco button and you can save on toner, paper, and energy. Print multiple pages on one sheet, change colour to greyscale or skip blank pages.



Samsung Eco-Driver earned  
*the 2012 "Outstanding Achievement"*  
Award from Buyers Lab, Inc.