

Affordable, wireless HP LaserJet printing from virtually anywhere in the home or office with several users. Print at up to 19 ppm letter/18 ppm A4 with no need for extra wires. Built-in environmental features can save money and resources.

Print Speed: Black (letter): Up to 19 ppm; Black (A4): Up to 18 ppm **Print Resolution:** Up to $400 \times 600 \times 2$ dpi (600 dpi effective output) **Print Technology Resolution:** HP FastRes 600, HP FastRes 1200 **Standard Connectivity:** Hi-Speed USB 2.0 port, WiFi 802.11 b/g

Monthly Volume (Duty Cycle): Up to 5,000 pages

Duplex Print Options: Manual (driver support provided)





Tractice.



Print from virtually anywhere in your home or office with wireless networking¹

- Network the printer without extra cables, using 802.11 b/g wireless networking.¹
- Print up to 19 ppm letter/18 ppm A4.
- Start and finish printing sooner with Instant-on Technology.
- Print on a wide variety of media, using the 150-sheet paper tray and 10-sheet priority input slot.

Rely on HP for an easy, dependable printing experience

- Install in a flash—no CD required—using HP Smart Install.²
- Set up and start printing right away with an easy-to-use, intuitive control panel.
- Receive consistent results with Original HP cartridges and easily reorder with HP SureSupply.³
- Get the services, solutions, software and support of HP Total Care.

Meet your environmental goals, while boosting your bottom line

- Conserve energy with Instant-on Technology and save even more with HP Auto-On/Auto-Off Technology.⁴
- Reduce wasted paper by printing only the content you want, using HP Smart Web Printing.⁵
- Save space with an ultra-compact printer with a sleek, industrial design.
- HP helps reduce your impact—less packaging, plus free cartridge recycling with HP Planet Partners.⁶

Create professional documents that make a statement for your business, while keeping your bottom line in check

- Produce professional-quality business prints with bold, crisp text and sharp images.
- Receive improved print quality with HP FastRes 1200.⁷

Wireless performance is dependent upon physical environment and distance from access point. "HP Smart Install works with Windows only." Program features and availability may vary by country. For more information, visit http://www.hp.com/learn/suresupply. "HP Auto-On and Auto-Off capabilities subject to printer and settings." To use this feature, you need Internet Explorer 6.0–8.0. "HP print cartridge return and recycling is available in 49 countries and territories around the world, covering 88% of the addressable market; see http://www.hp.com/recycle for details. "HP FastRes 1200 provides the best print quality setting for this device. Choose HP FastRes 600 for fast printing.















| PRINT TECHNOLOGY | Laser |
|--|---|
| PRINT SPEED ¹ | Black (letter): Up to 19 ppm; Black (A4): Up to 18 ppm |
| PRINT RESOLUTION | Black (best): Up to $600 \times 600 \times 2$ dpi (1200 dpi effective output); Black (normal): Up to $400 \times 600 \times 2$ dpi (600 dpi effective output); First Page Out Black (letter, ready): As fast as 8.5 sec |
| PRINT TECHNOLOGY RESOLUTION | HP FastRes 600, HP FastRes 1200 |
| STANDARD PRINTER LANGUAGES | Host-based printing |
| NUMBER OF PRINT CARTRIDGES ² | 1 (black) |
| SURESUPPLY SUPPORTED ³ | Yes |
| PRINTER MANAGEMENT | HP Status and Alerts; HP Usage tracking (CD install only) |
| STANDARD CONNECTIVITY | Hi-Speed USB 2.0 port; WiFi 802.11 b/g |
| WIRELESS CAPABILITY | Yes, WiFi 802.11 b/g |
| NETWORK CAPABILITIES | Via built-in WiFi 802.11 b/g wireless network |
| OPTIONAL CONNECTIVITY | HP Jetdirect en3700 Fast Ethernet Print Server; HP Jetdirect en1700 IPv4/IPv6 Print Server; HP Jetdirect ew2500 802.11g Print Server |
| CONTROL PANEL | 3 LED indicator lights (Wireless, Attention, Ready); 2 buttons (Wireless, Cancel) |
| RECOMMENDED MEDIA WEIGHT (DUPLEX) | 16 to 28 lb |
| RECOMMENDED MONTHLY PAGE VOLUME | 250 to 1,500 |
| DUTY CYCLE (MONTHLY, LETTER) | Up to 5,000 pages |
| MAXIMUM/STANDARAD MEMORY | 8 MB |
| MEDIA TYPES SUPPORTED | Paper (laser, plain, photo, rough, vellum), envelopes, labels, cardstock, transparencies, postcards |
| MEDIA SIZES SUPPORTED | Letter, legal, executive, postcards, envelopes (No. 10, Monarch) |
| CUSTOM MEDIA SIZES | 150-Sheet input Tray: 5.8×8.27 to 8.5×14 in; Priority Feed Slot: 3×5 to 8.5×14 in |
| PAPER HANDLING | Input Capacities: 10-sheet priority feed slot, 150-sheet input tray, Up to 160 sheets, Up to 15 envelopes Output Capacities: 100-sheet face-down bin, 100 sheets, Up to 15 envelopes, Up to 100 sheets transparencies |
| DUPLEX PRINT OPTIONS | Manual (driver support provided) |
| PROCESSOR | Tensilica / 400 MHz |
| SOFTWARE INCLUDED | HP Usage tracking, HP Status and Alerts, CD Launch Pad, Control Panel Simulator, Print Driver, Software Installer/Uninstaller |
| MINIMUM SYSTEM REQUIREMENTS | PC: Microsoft® Windows® 7 (32-bit/64-bit): 1 GB RAM, Windows Vista® (32-bit/64-bit), Windows® XP, Windows® Server 2008 (32-bit/64-bit), Windows® Server 2003: 512 MB RAM, all systems: 350 MB free hard disk space, CD-ROM drive, USB port; Mac: Mac OS X v 10.4, 10.5, 10.6, 256 MB RAM, 150 MB available hard disk space, CD-ROM drive, USB port |

| COMPATIBLE OPERATING SYSTEMS | Microsoft® Windows® 7 (32-bit/64-bit), Windows Vista® (32-bit/64-bit), Windows® XP (32-bit/64-bit), Windows® Server 2008 (32-bit/64-bit), Windows® Server 2003 (32-bit/64-bit), Mac OS X v 10.4, v 10.5, v 10.6, Linux (see http://www.hplip.net for current) |
|------------------------------|--|
| OPERATING ENVIRONMENT | Operating Humidity Range: 10 to 80% RH; Recommended Humidity Operating Range: 30 to 70% RH; Operating Temperature Range: 15 to 32.5° C; Recommended Operating Temperature Range: 63.5 to 77° F (17.5 to 25° C); Maximum Operating Temperature Range: 59 to 90.5° F; Storage Temperature Range: -4 to 104° F (-20 to 40° C); Non-Operating Humidity: 10 to 90% RH |
| ACOUSTICS | Acoustic Power Emissions: 6.4 B(A); Acoustic Power Emissions (Ready): Inaudible; Acoustic Pressure Emissions: 50 dB(A); Acoustic Pressure Emissions Bystander (Ready): Inaudible |
| POWER | Power Requirements: Input voltage 115 to 127 VAC (+/- 10%), 60 Hz (+/- 2 Hz), 12 amp; 220 to 240 VAC (+/- 10%), 50 Hz (+/- 2 Hz), 6.0 amp; Power Supply Type: Internal; Power Consumption ⁴ : 370 watts active, 0.6 watts off, 2.0 watts (Auto-Off) powrsave, 2.7 watts standby ENERGY STAR® qualified models; see http://www.hp.com/go/energystar |
| PRODUCT DIMENSIONS | W X D X H: 13.66 x 8.82 x 7.64 in (347 x 224 x 194 mm) Maximum: 13.66 x 12.99 x 7.64 in |
| PRODUCT WEIGHT | 11.6 lb (5.3 kg) |
| WHAT'S IN THE BOX | HP LaserJet Pro P1102w Printer, introductory HP LaserJet Black print cartridge, power cord, CD(s) with printer software and documentation, Getting Started Guide, support flyer, Smart Install Flyer, USB install cable (1m) |
| ACCESSORIES | Hi-Speed USB A to B printer cable (6 ft./1.8-meter, Q6264A |
| REPLACEMENT CARTRIDGES | HP LaserJet Black Print Cartridge, CE285A |
| WARRANTY | One-year limited warranty |
| HP CARE PACK SERVICES | UG605E HP 2-year NBD ExchPrinting and Imaging-M SVC UG608E HP 3-year NBD ExchPrinting and Imaging-M SVC UH609E HP 4-year NBD ExchPrinting and Imaging-M SVC US284E HP Basic Installation Service for one consumer printer with wireless capability US285E HP Premium Installation Service with wireless network setup for up to three PCs and/or printers |

ADDITIONAL INFORMATION

| BUSINESS UNIT | Transaction Laser Products |
|--------------------|--|
| COUNTRY OF ORIGIN | Product of Vietnam |
| MATERIAL TYPE CODE | FERT |
| TARIFF NUMBER | 8443321020 |
| PALLET INFORMATION | Dimensions: 47.3 x 39.4 x 100 in Weight: 1390 lb Layers: 8 |

FOR MORE INFORMATION VISIT OUR WEBSITE AT WWW.HP.COM

HP LASERJET PRO P1102W PRINTER Product Number: CE657A

Exact speed varies depending on the system configuration, software application, driver and document complexity. Introductory cartridge included; yields ~700 pages. Replacement cartridge declared yield ~1600 pages based on ISO/IEC 19752 and continuous printing. Actual yields vary considerably based on images printed and other factors. For details see http://www.hp.com/go/learnaboutsupplies. ItP SureSupply alerts you when your print cartridge is running low and helps you purchase online or locally through HP or a participating retailer. Only available with Original HP supplies; Internet access required. For more information, visit http://www.hp.com/go/SureSupply. Values subject to change. See http://www.hp.com/go/lip1600_regulatory for current information. Power numbers are the highest values measured using all standard voltages.