



E2260SWDA

54.6cm (21.5") LCD MONITOR

Energy-saving LED backlighting, high contrast ratios and 5ms response time deliver sharp, vibrant imagery. Smart features like Eco Mode and e-Saver further reduce power consumption.



AUDIO



TILT

GENERAL FEATURES

Line	Pro-line
Panel Type	TN
Panel Size	21.5" / 54.6 cm
Aspect Ratio	16:9
Brightness	250 cd/m ²
Contrast Ratio Dynamic	100M:1
Contrast Ratio Static	1000:1
Pixel Pitch(H) (V)	0.248
Display Area (H x V)	477.5x268.5
Viewing Angle (CR >= 10)	170/160
Response time	5ms
Color	Black

SCANNING FREQUENCY

Scanning Frequency	30-83khz/55-75Hz
Pixel Frequency	148.5MHZ

RESOLUTION

Maximum Resolution	1920x1080@60Hz
Recommended Resolution	1920x1080@60Hz
Colors	16.7 Million
HDCP compatible	Yes

CONNECTORS

D-Sub	Yes
DVI	Yes
HDMI	-
USB	-
MHL	-
DisplayPort	-

POWER

Power Source	100 - 240V 50/60Hz
Power Consumption	On: 18W, Standby: 0.5W, Off: 0.3W
Zero Power Switch	-

OTHER FEATURES

Plug and play	Yes
Kensington Lock	Yes
i-Menu	Yes
e-Saver	Yes
Vesa Wallmount	100x100
Speakers	Yes

Regulations	Energystar 6 TCO 6 EPEAT Gold TUV-GS TUV-Bauart CE FCC EAC RoHS compliant
-------------	---

ACCESSORIES

VGA Cable
DVI Cable
Audio Cable
Power Schuko C7 Cable

ERGONOMIC DATA

Pivot	No
Tilt	-5/+20

DIMENSIONS

Product with stand (W×H×D)	511x373x185 mm
Packaging (W×H×D)	567x437x118 mm
Weight	2.7 kg wo/packaging 4.09 kg w/packaging
Warranty	3 Years
EAN	4038986121729