

Product Data Sheet

iCOMPEL[™] P Series VESA Mountable Subscriber Unit



Features

- Our highest-quality SMB signage system.
- Flash processor at >20 fps and video at >30 fps.
- Shows video in up to four zones.
- Supports the display of professional-quality flash alongside of video, static images, HTML, XML, and RSS Web content.
- 40 GB SSD storage for digital content library.


Specifications

Approvals	Unit: FCC, RoHS2, WEEE; Power Supply: FCC, UL®, CE, CSA, RoHS2, WEEE	
CPU Processor	Intel® Core I3	
System RAM	2 GB	
System Storage	40 GB HDD	
Media Supported	Video—Standard Definition (Encoded up to 10 MB, except where indicated): MPEG2 - MP @ ML, POPAI Standard DS; MPEG4 - OpenDixX, POPAI Standard not supported; MPEG4 - DVB-T, POPAI Standard not supported; MPEG4 - LZ64 AVC, POPAI Standard not supported; MPEG4 - DVB-T H.264, POPAI Standard not supported; Microsoft* MPEG4 V1,2,3, POPAI Standard not supported; Microsoft* MPEG4 V1,2,3, POPAI Standard not supported; Microsoft* MPEG2 - VC1 (also up to 20 MbpS), POPAI Standard fa; Apple* QuickTime* (SMC & RPZA Codecs), POPAI Standard not supported; MPEG2 - MP @ HL, POPAI Standard not supported; MPEG2 - DVB-T, POPAI Standard not supported; MPEG2 - DVB-T, POPAI Standard not supported; MPEG4 - L264 AVC, POPAI Standard not supported; MPEG4 - L264 AVC, POPAI Standard not supported; MPEG4 - L264 AVC, POPAI Standard not supported; MPEG4 - L98-T H.264 AVC, POPAI Standard not supported; MPEG4 - L98-T H.264 AVC, POPAI Standard not supported; MMVV9 (VC1+), POPAI Standard not supported; MVWV9 (VC1+), POPAI Standard not supported; MWWV9 (VC1+), POPAI Standard not supported; MWWV9 (VC1+), POPAI Standard not supported; MICG4 - US-TH .264 AVC*, POPAI Standard not supported; Animation: HTML, JavaScript and SVG (as per WebKit), POPAI Standard not supported; Animated GIF (within an HTML file), POPAI Standard not supported; Presentation: Microsoft PowerPoint 2010 (save as WWV), POPAI Standard not supported; Still Images: TIFF - Tagged Image File Format, POPAI Standard not supported; JPG/JPEG - Joint Photographic Experts Group, POPAI Standard not supported; MVF Not supported, POPAI Standard s52, S3; GIF - Graphics Interchange Format, POPAI Standard not supported; PMG - Portable Network Graphic, POPAI Standard not supported; PMG - Portable Network Graphic, POPAI Standard not supported; PMG - Portable Network Graphic, POPAI Standard not supported; PMG - POPAI Standard not supported; AC3, POPAI Standard not supported; AC4, POPAI Standard not supported; AC4, POPAI Standard not supported; AC4, POPAI Standard no	

Specifications (continued)

Media Zones Supported	Unlimited text, stills, audio; (4) video zones; Transparent zone capable
Video Output Resolution	Digital to 2560 x 1600; HD to 1080p
Connectors	Video: (1) DisplayPort F, (1) HDMI F, (1) DVI-F; Audio: (1) 3.5-mm; USB: (6) USB Type A F: (2) USB 2.0, (2) USB 3.0, (2) USB Sleep-and-Charge; Ethernet: (1) RJ-45 (10/100/1000 Mbps); External Storage: (1) eSATA
Power	Input: 90–240 VAC, 50–60 Hz
Dimensions	1.1"H x 11"W x 7.3"D (2.9 x 28 x 18.6 cm)
Weight	4.0 lb. (1.8 kg)

Dimensional Diagrams



Disclaimer:

Black Box Network Services shall not be liable for damages of any kind, including, but not limited to, punitive, consequential or cost of cover damages, resulting from any errors in the product information or specifications set forth in this document and Black Box Network Services may revise this document at any time without notice.

© Copyright 2014. Black Box Corporation. All rights reserved. Black Box[®] and the Double Diamond logo are registered trademarks, and iCOMPEL is a trademark, of BB Technologies, Inc. Intel is a registered trademark of Intel Corporation in the U.S. and/or other countries. UL is a registered trademark of Underwriters' Laboratories. Any third-party trademarks appearing in this publication are acknowledged to be the property of their respective owners.

icps-ve-su-n_ds_Rev1