

IRIScan™ Anywhere 3

Get mobile! Scan anything, anywhere...

Cordless, battery-powered and compact, the IRIScan™ Anywhere 3 enables on-the-go users to easily capture information from all kinds of documents when away from their computer. Ideal for today's mobile lifestyle, it turns document management into a child's play.

The sheet of paper is simply zipped through the cordless and lightweight A4 scanner, and the scanned image is then either saved in the built-in memory, on an SD™ Card or on a standard USB key. Once back at home or in the office simply insert the SD™ card into your computer, and the scanned documents are automatically processed by I.R.I.S' flagship OCR software Readiris™ 14 and exported to the Cloud (Evernote®, Google Drive™, Dropbox, SkyDrive®, iCloud®, etc.).

Key Features

Mobile scanner

- Cordless, battery-powered and very lightweight. No computer needed to scan!
- Scan up to 100 letter size documents on battery mode.
- Scanner speed: up to 6 pages per minute.
- Directly save JPEG file to SD™ card, USB key or internal memory (512MB).
- Free SD™ card on demand (voucher).
- Scan your business cards and use Cardiris™ Pro to manage your contacts.
- iPad® compatible (with SD™ card adaptor for iPad®, not included in the box).

State of the art OCR software Readiris™ Pro 14 (Windows® and Mac®)

- Convert any paper document, PDF, or image file into editable Office documents.
- Worldwide OCR solution - 137 recognized languages (incl. Asian languages and Arabic).
- Create fully indexed and hyper-compressed PDF files up to 5 times smaller than the original image thanks to iHQC™, ideal for archiving and sharing via email.
- Upload your documents to the Cloud in a single click! (Evernote®, Google Drive™, Dropbox, SkyDrive®, Box.net®, etc.).
- Free inside the box!

1-year Evernote® Premium voucher (worth \$45).

Quick reference guide

Product name	IRIScan™ Anywhere 3
SKU	457485
UPC-A code	765010725007
Custom code	847190
MSRP (USD)	\$199
Box size (H x L x D)	5.43 x 12.12 x 2.28 in
Box weight	Around 35.27 oz
Scanner size (H x L x D)	1.73 x 10.62 x 2.12 in
Scanner weight	13.75 oz
Box languages	Arabic, Dutch, English, French, German, Italian, Portuguese, Russian, Spanish
Box content	IRIScan™ Anywhere 3 scanner • USB cable • Voucher for free SD™ Card • Calibration sheet • Cleaning swab • Software suite for PC and Mac® on CD-ROM • I.R.I.S. products catalogue • Discount voucher for next purchase • Quick user guide • Free 1-year Evernote® Premium voucher

* Windows® only.

for Windows® and Mac®

Scanner specifications

Document feeding	Sheet feed type (single)
Resolution	Low resolution : 300 dpi (default) High resolution : 600 dpi
Document size (max)	Up to letter size
Interfaces	SD, xD, MS, MS Pro, MMC (for optional memory) USB slave (type-B Mini) (for computer connection) USB host (type-A) for USB key (for optional memory)
Output file format	JPEG
Flash memory	512MB (expandable with SD™ card or USB key)
Battery	Lithium-ion polymer rechargeable battery through USB cable Scanning capacity when fully charged : up to 100 letter documents based on test conditions
Charging method	USB cable

Minimum computer requirements

Scanner

- At least one USB port available.
- Installable on any operating system that supports mass storage protocols (Windows®, Mac OS®, Linux®, Unix®, etc.).
- No driver installation needed!

Software suite for Windows®

- Intel® Pentium® based PC or equivalent recommended.
- Microsoft® Windows® 8, 7, Vista® or XP.
- 512MB RAM recommended.
- 300MB of available hard disk space.
- CD-ROM drive.

Software suite for Mac OS®

- Mac® computer with PowerPC™ G3 or Intel® processor.
- Mac OS® X version 10.4 or above (compatible with Mac OS® X Lion!).
- 260MB of available hard disk space.
- CD-ROM drive.

1 year FREE!



Evernote®
Premium



PRODUCTS & TECHNOLOGIES

www.irislink.com

© Copyright 2013 I.R.I.S. s.a.
All rights reserved for all countries. I.R.I.S., I.R.I.S.® product names, I.R.I.S. logos and I.R.I.S. product logos are I.R.I.S. trademarks. All other products and names mentioned are trademarks or registered trademarks from their respective owners.



J130418-6