

Data sheet

HP t310 Zero Client

High-performance. Zero hassles.



Amazing performance with the latest PCoIP technology with VMware Horizon™ DaaS®, VMware Horizon View and Amazon WorkSpaces support.¹

Tailor-made for PCoIP protocol.

Don't hassle with set up. This PCoIP zero client is ready to plug and deploy right out of the box for VMware Horizon™ DaaS®, VMware Horizon View and Amazon WorkSpaces¹ environments.

Reduce complexity with a zero client made specifically for your business requirements. Save time without the need to customize your install base.

Our best-performing PCoIP thin zero client.

Finish ahead of deadlines with fast boot and response times. Forget the lags. See multimedia, online videos² and 3D applications running smoothly at native frame rates.

Expand your view. The HP t310 supports dual displays for multi-tasking and fine-tuning media projects.³

No local data storage. No space hog. True Zero Client.

Focus IT efforts on top priorities by cutting maintenance needs on desktops. Upgrade users quickly and inexpensively by updating application software hosted on servers.

Reduce the risks of your data getting into the wrong hands. With no data stored on the HP t310, your intellectual property stays on your secure server.

Boost security measures even more with the fiber network interface card (NIC).

Clear clutter from your desk. The small size (5.9 in/149.8 mm x 5.2 in/132.1 mm) keeps your work area free of distractions. You stay focused.

Warranty, service and support.

Easy setup, manageability and maintenance. Count on global service and support through a network of over 50,000 IT professionals in over 100 countries.

Worry less with a standard, three-year limited hardware warranty in most regions.

Choose from HP Care Pack Services⁴ to extend service contracts beyond your standard warranties.

HP t310 Zero Client

Hardware specifications

Operating system	No Operation System
Processor	TERA2321 PCoIP Zero Client processor
System memory	512 MB DDR3 1333 MHz SDRAM
Flash memory	32 MB SPI
Protocols	VMware® Horizon View™ through PCoIP VMware Horizon® DaaS® through PCoIP Amazon WorkSpaces ¹ through PCoIP
Monitor support	Supports up to 2 displays; 1 DVI-D, 1 DVI-I with resolutions up to 1920x1200 at 60Hz or single digital display at resolutions up to 2560x1600 using a custom DVI dual-link cable. ⁶
Audio	1 microphone, 1 headphone, 1 speaker
Communications	10/100/1000 BASE-T Ethernet (RJ-45) or 100 Mbps Fiber NIC, Wake on LAN (WoL) using magic packet
Ports and connectors	4 USB 2.0 (two in front, two in rear), 1 NIC (RJ-45), 1 power connector, 1 12VDC power Single-link DVI-D connector, Single-link DVI-I connector
Input devices	Keyboard USB and Mouse USB
Dimensions (W x D x H)	5.98 x 5.24 x 1.85 in (15.2 x 13.31 x 4.7 cm)
Weight	1.39 lbs (.63 kg)
Warranty	HP Total Care Warranty and Services: limited three-year hardware warranty in most regions. Optional HP Care Pack Services ^{4,5} extends service contracts beyond your standard warranties. For more details visit hp.com/go/lookuptool .

1 Amazon Workspaces require Teradici firmware version 4.6 or higher. HP SoftPaqs are available for download November 2014 at 8.hp.com/us/en/drivers.html.

2 Internet access required.

3 Displays and display stand sold separately.

4 Service levels and response times for HP Care Pack Services may vary depending on your geographic location. Service starts from date of hardware purchase.

5 Restrictions and limitations apply. HP Care Pack Services extend service contracts beyond the standard warranties. To choose the right level of service for your HP product, use the HP Care Pack Services Lookup Tool at hp.com/go/lookuptool. Additional HP Care Pack Services information by product is available at hp.com/hps/carepack.

6 DVI dual-link cable sold separately.

For more information visit
hp.com/go/thincomputing

