

Epson WorkForce WF-2010W

DATASHEET



This single-function printer has a compact design with a small footprint. It can be placed almost anywhere within a small office or home office environment, and is robust and durable for important business documents.

The WorkForce WF-2010W uses Epson's fast drying DURABrite Ultra Ink for professional-quality business documents and means that prints are water, smudge and highlighter resistant. Cartridges are also available in XL size, helping to save further on costs, as users can print up to 2.5x more pages*1.

This printer also has flexible connectivity options, as users can connect the printer to their office network via Wi-Fi or Ethernet. With automatic Wi-Fi set-up, users don't need to know their network settings or connect with a USB cable during set up, as the printer automatically finds the relevant connection settings in order to configure itself*2.

The WorkForce WF-2010W comes with a robust 100-sheet rear paper tray, providing media flexibility for a variety of paper.

KEY FEATURES

- Wi-Fi and Ethernet connectivity
- Compact footprint
- Print more pages with Epson XL inks*1
- 3,000 page duty cycle per month

PRODUCT SPECIFICATIONS

TECHNOLOGY	
Printing Method	4-colour inkjet printer
Nozzle Configuration	180 Nozzles black, 59 Nozzles per colour
Minimum Droplet Size	3 pl, With Variable-Sized Droplet Technology
Ink Technology	Epson DURABrite™ Ultra
Category	Office
PRINT	
Draft printing speed	34 Pages/min Monochrome (plain paper 75 g/m²), 18 Pages/min Color (plain paper 75 g/m²), 38 Seconds per 10 x 15 cm photo (Epson Premium Glossy Photo Paper)
Printing Speed ISO/IEC 24734	9 Pages/min Monochrome, 4.7 Pages/min Color
Printing Resolution	5,760 x 1,440 dpi
Max Duty cycle	3,000 Pages per month
Colours	Black, Cyan, Yellow, Magenta
For detailed information on printing speeds please visit http://www.epson.eu/testing .	
CONNECTIVITY	
Interfaces	USB 2.0 Type B, Wireless LAN IEEE 802.11b/g/n, Ethernet interface (100 Base-TX / 10 Base-T), USB 2.0 Type A
WLAN Security	WEP 64 Bit, WEP 128 Bit, WPA PSK (TKIP), WPA PSK (AES)
PAPER / MEDIA HANDLING	
Paper Formats	A4, A5, A6, B5, C6 (Envelope), DL (Envelope), No. 10 (Envelope), Letter, Letter Legal, 10 x 15 cm, 13 x 18 cm, 16:9, User defined
Duplex	No
Paper Tray Capacity	100 Sheets Standard, 100 Sheets maximum, 20 Photo Sheets
Number of paper trays	1
GENERAL	
Energy Use	2 W (sleep mode), 12 W (printing), ENERGY STAR® qualified all-in-one
Supply Voltage	AC 220 V - 240 V, 50 Hz - 60 Hz
Product dimensions	392 x 264 x 148 (Width x Depth x Height)
Product weight	3.2 kg
Noise Level	51 B (A) according to ISO 7779 pattern with Epson Premium Glossy Photo Paper / Photo RPM mode - 36 dB (A) according to ISO 9296
Compatible Operating Systems	Mac OS 10.5.8 or later, Mac OS 10.6+, Windows 7, Windows 7 x64, Windows 8, Windows Vista, Windows Vista x64, Windows XP, Windows XP x64
Included Software	EpsonNet Config, EpsonNet Print
Power Supply	240V
ADDITIONAL FEATURES	
Media Handling	Manual duplex

LOGISTICS INFORMATION

SKU	C11CC40301
Barcode	8715946517070
Dimensions Single Carton	454 x 345 x 223 mm
Carton Weight	4.7 Kg
Pallet Size Euro	45 Units (5 x 9)
Pallet Size Block	54 Units (6 x 9)

Epson WorkForce WF-2010W

WHAT'S IN THE BOX

- Main unit
- Individual Ink Cartridges
- Wi-Fi/network setup guide
- User manual (CD)
- Software (CD)
- Warranty document
- Power cable

INK YIELD DATA

	penandcrossword	penandcrossword
	16	16XL
●	175 pages*	500 pages*
● ● ●	165 pages*	450 pages*

* Approx. page yield based on ISO/IEC 24711/24712 or ISO/IEC 29102/29103. Actual yield will vary depending on images printed and usage conditions. For more information visit %LINK%

SUPPLIES

- Singlepack Magenta 16XL DURABrite Ultra Ink C13T16334010 (450 pages)
- Singlepack Cyan 16XL DURABrite Ultra Ink C13T16324010 (450 pages)
- Singlepack Magenta 16 DURABrite Ultra Ink C13T16234010 (165 pages)
- Singlepack Cyan 16 DURABrite Ultra Ink C13T16224010 (165 pages)
- Singlepack Black 16 DURABrite Ultra Ink C13T16214010 (175 pages)
- Singlepack Black 16XL DURABrite Ultra Ink C13T16314010 (500 pages)
- 16XL Series 'Pen and Crossword' multipack C13T16364010
- 16 Series 'Pen and Crossword' multipack C13T16264010



For more information please contact:

Telephone: 0871 222 6702 (UK)+
01 436 7742 (Republic of Ireland)
E-mail: enquiries@epson.co.uk
Chat: etalk.epson-europe.com
Fax: 0871 222 6740

Web: www.epson.co.uk
www.epson.ie

+ Calls cost 10p per minute plus network extras.

Trademarks and registered trademarks are the property of Seiko Epson Corporation or their respective owners. Product information is subject to change without prior notice.

1. For more information, please visit www.epson.eu/inkjetsaving
2. Automatic set-up compatible with Windows 8, Windows 7, Windows Vista and Mac OS
3. The maximum number of printed pages per month based on the performance capabilities of the printer, including ISO rated print speeds and paper handling capabilities
4. For more information, please visit www.epson.eu/testing
5. Determined in accordance with ISO/IEC 24734 showing the average of ESAT from the Office Category Test for default simplex. For more information, please visit www.epson.eu/testing

EPSON®