

Epson Expression Photo XP-850



DATASHEET



The Epson Expression Photo XP-850 is the ideal 4-in-1 with double-sided ADF for photo enthusiasts who want a top-of-the-range printer to showcase their photography skills. This printer is up to 40 percent smaller*2 than previous models and features an 8.8cm touch-screen, with user-friendly interactive menu, and a motorised control panel and output tray which open automatically before printing.

Epson's new six-colour Claria Photo HD Ink is ideal for keen photographers looking to produce and display superior-quality, long-lasting photographs and delivers smooth tonal gradations, natural blacks and rich, vibrant colours.


Express your creativity by printing onto thick card and heavyweight photo paper with the rear speciality media feed. You can also easily switch between photo and A4 printing, thanks to the dual front-loading paper trays, and personalise family films and digital photo albums by printing directly onto suitable CDs and DVDs.

Epson Connect*3 allows you to print wirelessly from smartphones and tablet PCs within the home, and print from anywhere in the world by emailing documents directly to the printer's unique email address. The Remote Printer Driver offers more flexibility to print from your PC to any Epson Connect printer anywhere in the world, while Scan-to-Cloud enables you to store scanned documents directly in Cloud services. In addition the XP-850 is Apple AirPrint and Google Cloud print ready.

Wi-Fi and Ethernet offer flexible connectivity, while the automatic Wi-Fi set-up automatically finds the relevant connection settings in order to configure itself*4. Wi-Fi Direct connects directly to other Wi-Fi devices without the need for a wireless access point, such as a router.

KEY FEATURES

- Print, scan, copy and fax with ADF
- Superior-quality, long-lasting photos
- 40% smaller than previous models*2
- Freedom to print and scan anywhere
- 8.8cm touch-screen and motorised trays



PRODUCT SPECIFICATIONS

TECHNOLOGY

Printing Method	Epson Micro Piezo™ print head
Minimum Droplet Size	1,5 pl, With Variable-Sized Droplet Technology
Ink Technology	Epson Claria™ Photo HD Ink
Printing Resolution	5.760 x 1.440 dpi

PRINT

Draft printing speed	32 Pages/min Monochrome (plain paper 75 g/m²), 32 Pages/min Color (plain paper 75 g/m²), 10 Seconds per 10 x 15 cm photo (Epson Premium Glossy Photo Paper)
----------------------	--

Printing Speed ISO/IEC 24734 9,5 Pages/min Monochrome, 9 Pages/min Color

Colours Black, Light Cyan, Cyan, Yellow, Magenta, Light Magenta

For detailed information on printing speeds please visit <http://www.epson.eu/testing>.

SCAN

Scanning Resolution	4.800 dpi x 4.800 dpi (Horizontal x Vertical)
Scanner type	Contact image sensor (CIS)

FAX

Fax speed dials (max)	60 names and numbers
Page memory	Up to 180 pages (ITU-T No.1 chart)
Fax Functions	PC Fax, Auto Redial, Speed Dial

PAPER / MEDIA HANDLING


Number of paper trays	2
Paper Formats	A4, A5, A6, B5, C6 (Envelope), DL (Envelope), No. 10 (Envelope), Letter, 9 x 13 cm, 10 x 15 cm, 13 x 18 cm, 13 x 20 cm, 100 x 148 mm, 16:9, HLT, Legal
Duplex	Yes
Print Margin	0 mm top, 0 mm right, 0 mm bottom, 0 mm left (Wherever margin is defined. Otherwise 3mm top, left, right, bottom.)
Automatic Document Feeder	30 Pages
Paper Tray Capacity	100 Sheets Standard, 20 Photo Sheets
Media Handling	Auto Sheet Feeder, Automatic duplex, Borderless print, CD/DVD print, Rear specialty media feed

GENERAL

Energy Use	21 W (standalone copying, ISO/IEC 24712 pattern), 2 W (sleep mode), ENERGY STAR® qualified all-in-one
Product dimensions	390 x 339 x 191 (Width x Depth x Height)
Product weight	8,7 kg
Noise Level	5,1 B (A) with Epson Premium Glossy Photo Paper / Photo RPM mode - 37 dB (A) with Epson Premium Glossy Photo Paper / Photo RPM mode
Compatible Operating Systems	Mac OS 10.5.8 or later, Windows 7, Windows 7 x64, Windows 8, Windows Vista, Windows Vista x64, Windows XP, Windows XP x64

LOGISTICS INFORMATION

SKU	C11CC41302
Barcode	8715946515656
Dimensions Single Carton	484 x 263 x 427 mm
Carton Weight	11 Kg
Pallet Size Euro	16 Units (2 x 8)



Epson Deutschland GmbH
Otto-Hahn-Str. 4
D-40670 Meerbusch
Info-Line: 01805/23 41 10 (0,14 /Min. aus dem dt. Festnetz,
max. 0,42 /Min. aus dem Mobilfunk)
Telefax: +49 (0) 2159/538-3000
www.epson.de

Epson in Österreich
Info-Line: 0810/20 01 13 (0,07 /Min.)
www.epson.at

Epson in der Schweiz
Info-Line: 0848 44 88 20 (8 Rp./Min.)
www.epson.ch

Alle Marken und eingetragenen Warenzeichen sind das Eigentum der Seiko Epson Corporation oder der jeweiligen Rechteinhaber.
Diese Produktinformationen können ohne vorherige Ankündigung geändert werden.

Epson Expression Photo XP-850

WHAT'S IN THE BOX

- Individual Ink Cartridges
- Main unit
- Setup guide
- Software (CD)
- Warranty document
- Power cable

INK CARTRIDGE COMPATIBILITY

- 24
- 24
- 24
- 24
- 24
- 24
- 24
- 24
- 24
- 24
- 24
- 24



- 24XL



INK YIELD DATA



elephant 24

elephant 24XL

- 240 pages* 500 pages*
- 360 pages* 740 pages*

* Approx. page yield based on ISO/IEC 24711/24712 or ISO/IEC 29102/29103. Actual yield will vary depending on images printed and usage conditions. For more information visit %LINK%

1. This printer and original ink cartridges are for sale and use in EMEA only
2. Based on total volume of the printer, with trays closed, compared to previous models
3. Requires a wireless connection to the internet. For more information, supported languages and devices please visit www.epsonconnect.eu
4. Automatic set-up compatible with Windows 7, Windows Vista and Mac OS

EPSON®