

Lexmark MS610 Series Monochrome Laser Printer

Power Up Your Business. Print to Impress.

The Lexmark MS610 Series delivers. With its speed, reliability and convenient features, your business can handle everyday document tasks more quickly and easily. *Want productivity solutions? Get the MS610de.*



Up to 50
ppm



Direct USB



Solutions



Security

Unison
TONER

More Productivity. Compact Design.

Power and speed come together in a space-saving size. Built to handle the requirements of a professional office, the MS610 Series produces high quality, professional prints in next to no time.

Print Complex Documents Fast - Print documents with graphics and images effortlessly with up to 2.5 GB of upgradable memory and a powerful 800 MHz dual-core processor.

Reliable Performance - Easily print up to 16,000 pages per month, plus enjoy fewer maintenance hassles, thanks to our state-of-the-art paper handling.

Run Jobs without Interruption - With an input capacity of up to 2,300 sheets and ultra high yield toner cartridge options, you won't have to add paper or change cartridges as often.

Get Work Done Quickly - Print up to 50 pages per minute—plus get your first page in as little as 6.5 seconds.

Professional Results. Performance Ready.

With our exceptional laser printers, it's easy to make a great impression. And our system is simple to use, thanks to the larger, easy-to-read control panel, eco-friendly supplies and more.

High Resolution Graphics - With up to true 1200x1200 dpi resolution, images and graphics stay crisp. Lexmark's Unison™ Toner ensures consistent print quality.

Easy-to-use Displays - The bright 2.4-inch color display lets you stay on top of your work. Need more control and productivity solutions? Get the solutions-capable MS610de with the 4.3-inch color touch screen.

Innovative Toner That Optimizes Performance - Get greater system performance with Lexmark's Unison™ Toner, which delivers consistent image quality from first to last print.

Convenient Controls - Preview your held jobs to print only the pages you need, so you can make changes on the fly. Choose multi-image printing on one page or select two-sided printing to save paper.

Smoother Workflows. Solution Capable.

The MS610 Series delivers volumes of high quality documents without a hassle. For productivity solutions that let you print often-used forms, print on demand and more, get the MS610de.

Help Workers Do More - With standard Gigabit Ethernet networking, our system can print jobs from the network faster, so your teams stay productive. Plus, you can protect sensitive data using standard network security protocols.


Streamline Tasks with Ease - Be more productive and efficient with our easy-to-use color touch screen, customizable apps, optional card reader and more.

Save Resources and the Planet - An instant warm-up fuser, built-in 2-sided printing, an ultra high yield toner option, plus Quiet, Hibernate and Eco modes minimize noise and save paper and energy.

Print Anytime and Anywhere⁶ - With this system, you can print from desktops as well as mobile devices that can run applications.

LEXMARK
TM

Lexmark MS610 Series Monochrome Laser Printer



Product specifications	Lexmark MS610dn	Lexmark MS610de	Lexmark MS610dte
Printing			
Display	2.4-inch color LCD display	Lexmark e-Task 4.3-inch (10.9 cm) color touch screen	Lexmark e-Task 4.3-inch (10.9 cm) color touch screen
Print Speed: Up to ¹		Black: 50 ppm	
Time to First Page: As fast as		Black: 6.5 seconds	
Print Resolution		Black: 1200 Image Quality, 1200 x 1200 dpi, 2400 Image Quality, 600 x 600 dpi	
Memory / Processor	Standard: 256 MB / Maximum: 1280 MB / Processor: Dual Core, 800 MHz	Standard: 512 MB / Maximum: 2560 MB / Processor: Dual Core, 800 MHz	Standard: 512 MB / Maximum: 2560 MB / Processor: Dual Core, 800 MHz
Hard Disk	Not Available	Option available	Option available
Recommended Monthly Page Volume ²		3000 - 16000 pages	
Maximum Monthly Duty Cycle: Up to ³	100000 pages per month	150000 pages per month	150000 pages per month
Supplies⁵			
Laser Cartridge Yields	1,500 ¹ -page Cartridge, 5,000 ¹ -page Black High Yield Cartridge, 10,000 ¹ -page Extra High Yield Cartridge, 20,000 ¹ -page Ultra High Yield Cartridge		
Cartridge(s) Shipping with Product	6,000 ¹ -page Starter Return Program Toner Cartridge		
Paper Handling			
Included Paper Handling	550-Sheet Input, 100-Sheet Multipurpose Feeder, Integrated Duplex, 250-Sheet Output Bin	550-Sheet Input, 100-Sheet Multipurpose Feeder, Integrated Duplex, 250-Sheet Output Bin	550-Sheet Input, 100-Sheet Multipurpose Feeder, Integrated Duplex, 250-Sheet Output Bin, 550-Sheet Tray
Optional Paper Handling	250-Sheet Tray, 550-Sheet Tray		
Paper Input Capacity: Up to	Standard: 650 pages 20 lb or 75 gsm bond / Maximum: 2300 pages 20 lb or 75 gsm bond	Standard: 650 pages 20 lb or 75 gsm bond / Maximum: 2300 pages 20 lb or 75 gsm bond	Standard: 1200 pages 20 lb or 75 gsm bond / Maximum: 2300 pages 20 lb or 75 gsm bond
Paper Output Capacity: Up to	Standard: 250 pages 20 lb or 75 gsm bond / Maximum: 250 pages 20 lb or 75 gsm bond		
Media Types Supported	Card Stock, Envelopes, Paper Labels, Plain Paper, Transparencies, Refer to the Card Stock & Label Guide		
Media Sizes Supported	10 Envelope, 7 3/4 Envelope, 9 Envelope, A4, A5, DL Envelope, Executive, Folio, JIS-B5, Legal, Letter, Statement, Universal, Oficio, A6		
General			
Standard Ports	USB 2.0 Specification Hi-Speed Certified (Type B), Gigabit Ethernet (10/100/1000), Front USB 2.0 Specification Hi-Speed Certified Port (Type A)	One Internal Card Slot, USB 2.0 Specification Hi-Speed Certified (Type B), Gigabit Ethernet (10/100/1000), Front USB 2.0 Specification Hi-Speed Certified Port (Type A), Rear USB 2.0 Specification Hi-Speed Certified Port (Type A)	One Internal Card Slot, USB 2.0 Specification Hi-Speed Certified (Type B), Gigabit Ethernet (10/100/1000), Front USB 2.0 Specification Hi-Speed Certified Port (Type A), Rear USB 2.0 Specification Hi-Speed Certified Port (Type A)
Optional Network Ports / Optional Local Ports	MarkNet N8352 802.11b/g/n Wireless	MarkNet N8352 802.11b/g/n Wireless / Internal RS-232C serial, Internal 1284-B Bidirectional Parallel	MarkNet N8352 802.11b/g/n Wireless / Internal RS-232C serial, Internal 1284-B Bidirectional Parallel
Noise Level, Operating	Printing: 55 dBA		
Product Warranty	1-Year Exchange Service, Next Business Day		
Size (in. - H x W x D) / Weight (lb.)	12.1 x 15.7 x 15.0 in. / 34.6 lb.	12.1 x 15.7 x 15.6 in. / 35.7 lb.	16.3 x 15.7 x 15.6 in. / 46.1 lb.

¹ Average standard page yield value declared in accordance with ISO/IEC 19752. ² "Recommended Monthly Page Volume" is a range of pages that helps customers evaluate Lexmark's product offerings based on the average number of pages customers plan to print on the device each month. Lexmark recommends that the number of pages per month be within the stated range for optimum device performance, based on factors including: supplies replacement intervals, paper loading intervals, speed, and typical customer usage. ³ "Maximum Monthly Duty Cycle" is defined as the maximum number of pages a device could deliver in a month using a multishift operation. This metric provides a comparison of robustness in relation to other Lexmark printers and MFPs. ⁴ Print and copy speeds measured in accordance with ISO/IEC 24734, excludes first set of test documents. For more information see: www.lexmark.com/ISOspeeds. ⁵ Product functions only with replacement cartridges designed for use in a specific geographical region. See www.lexmark.com/regions for more details. ⁶ For more information on Lexmark Mobile Solutions see: http://www1.lexmark.com/en_US/solutions/business-solutions/mobile-print/index.shtml

