



## NSVB200-102S20

**Part Number:** NSVB200-102S20  
**Category:** Basic  
**Sub Category:** Basic  
**Power Configuration:** 20A, 120V, 1.9kW  
**Physical Configuration:** 66 in / 1682 mm, Vertical



**Description:** The NSVB200-102S20 non-surge unit is ideal for facilities already equipped with surge protection.

**Product Summary:** NSVB200-102S20, Basic, 20A, 120V, Vertical, (20) NEMA 5-20R, power switch, breaker, 10 ft power cord with 5-20P, Black Powder Coat.

**Plug Form:**



5-20P

**Receptacle:**



NEMA 5-20R  
(Quantity: 20)

Geist Americas

800.432.3219  
geistglobal.com

Geist DCIM  
1.877.449.4150  
geistglobal.com

Geist Europe

+44 (0) 1823.275100  
geistglobal.com

Geist Asia

China  
+86.755.86639505  
geistglobal.com

## Product Specification and Options:

Quantity Of Inputs	1
Voltage	120V
Current	20A
VA per Input (Load Capacity)	1.9kW
Frequency	50/60 Hz
Over Current Protection	20A Thermal Breaker
Switch	Yes
Indicators - LED(s)	1 - Power ON Green LED
Power Cable Wire Gauge	12/3
Power Cable Length	10ft
Plug Type	NEMA 5-20P
Receptacle/Socket Type #1	NEMA 5-20R
Quantity on Face #1	20
Center to Center Receptacle Spacing	2.8
Quantity per Breaker #1	20
Style #1	Individual - In-Line
Maximum Output per Receptacle/Socket #1	20A
Voltage per Receptacle/Socket #1	120V
Continuous Operating Temperature Range	10-45C / 50-113F
Heavy Steel - Powder Coat Finish	Black
Configuration	66in / 1682mm Vertical Rackmount
Plastic Mounting Clips	1 - Bottom; 2 - Top
Made in the USA	Yes
Product Warranty	Lifetime
Certification/Agency Approvals	RoHS Compliant
Certification/Agency Approvals	UL & c-UL Listed 60950
Chassis Dimensions (LxWxD)	66.25in x 1.61in x 1.61in
Shipped Weight	9lbs (4.08kg)