

Part Number	VHVR120-102D20ST6
	Basic, Non-Surge
Power Configuration	20A, 208V, 3.3kW
Physical Configuration	19 in / 483 mm Horizontal



Description	The VHVR120-102D20ST6 non-surge unit is ideal for facilities already equipped with surge protection.
Product Summary	VHVR120-102D20ST6 - Non-Surge, 20A, 208V, Horizontal, (12) NEMA 6-20R, breakered, 10 ft power cord with 6-20P
Monitoring	None
Plug Form	 6-20P
Receptacle	 NEMA 6-20R (Quantity: 12)

VHVR120-102D20ST6 - Product Specification and Options

Quantity Of Inputs	1
Voltage	208V
Current	20A
VA per Input (Load Capacity)	3.3kW
Frequency	50/60 Hz
Over Current Protection	20A Double Pole Magnetic Breaker
Switch	Breaker/Switch Combination
Power Cable Wire Gauge	12/3
Power Cable Length	10ft
Plug Type	NEMA 6-20P
Receptacle/Socket Type #1	NEMA 6-20R
Quantity on Face #1	2
Quantity on Rear #1	10
Quantity per Breaker #1	12
Style #1	Duplex
Maximum Output per Receptacle/Socket #1	20A
Voltage per Receptacle/Socket #1	208V
Heavy Steel -Black Powder Coat	Yes
Configuration	19in / 435mm Horizontal Rackmount
Adjustable Mount Brackets	Yes
Made in the USA	Yes
Product Warranty	Lifetime
Certification/Agency Approvals	NOM-003-SCFI-2000
Certification/Agency Approvals	RoHS Compliant
Certification/Agency Approvals	UL & c-UL Listed 60950
Chassis Dimensions (HxWxD)	1.72in x 17in x 6.50in
Shipped Weight	7lbs (3.18kg)

Geist Americas

1821 Yolande Ave
Lincoln, NE 68521 USA
1.800.432.3219 or
1.402.474.3400
www.geistglobal.com

Geist Europe

Unit 1, The Monarch Centre,
Venture Way,
Priorswood, Taunton,
Somerset, TA2 8DE UK
+44 (0) 1823 275100
www.geisteurope.com

Geist Asia

China
Tiley Plaza Bldg. A, Unit #2808,
No. 199 Haide 3 Road,
Nanshan Shenzhen,
Guangdong Province, China.
Postal Code: 518000
Tel: +86.755.86639505
www.geistglobal.com

Geist Asia

Hong Kong
Tel: +852 90361927
Email: salesasia@geistglobal.com