



PRODUCT SPECIFICATIONS

- Image Sensor: 1/3" Color
- Resolution: 600 TV Lines
- Picture Elements: 720 x 480
- Lens: 3.6mm Fixed Lens
- Number of IR LEDs: 30 IR LEDs
- Night Vision Range: 80'
- Min Illumination: 0 Lux (IR On)
- S/N Ratio: More than 48dB
- Electronic Shutter: 1/60S~1/100,000S
- Gain Control: Auto
- White Balance: Auto
- Gamma: 0.45
- Lens Furnished: Board Lens
- Audio: Built-In Microphone
- Body Construction: Plastic
- IP Rating: Indoor
- Power Consumption: 60mA IR LED OFF; 300mA 30 IR LED ON
- Power Supply: DC 12V±10%

FEATURES

- Built-in High Quality Image Sensor and High Performance Infrared Illuminator Module
- 350K Total Pixels
- High Sensitivity, Low Smear, Excellent Anti-Blooming and High S/N Ratio
- Supports Auto Electronic Shutter (AES), Auto Gain Control (AGC), Auto White Balance (AWB), Back Light Compensation (BLC), and Flickerless Mode (FL)
- 3-Axis Gimble for Free Lens Rotation
- Automatic IR Cut Filter Removal
- Low DC Power Consumption

www.revoamerica.com

Intelligent Surveillance. Innovative Technology. **COMPLETE VIDEO SECURITY SYSTEM FOR YOUR BUSINESS OR HOME.**