

ioSafe SOLO G3

+ Data Recovery Service



FIREPROOF

Protects against data loss in fire up to 1550°F,
1/2 hour Per ASTM E119



WATERPROOF

Protects data from flood, full submersion, 10' depth,
72 hours fresh or salt water



SILENT AIRFLOW COOLING

NEW Fanless design



DATA RECOVERY SERVICE

Up to \$2500 for forensic data recovery



USB 3.0 SUPERSPEED

Data transfer up to 5Gb/s



THEFTPROOF

Built in Kensington security slot or bolt down
with anti-theft tab

ioSafe SOLO G3 External Hard Drive

Product Specifications

Operational Details

- Single 3.5 SATA disk: 1TB, 2TB, 3TB capacities available
- Quiet fanless air cooling
- Multi-platform compatibility with Mac & PC/Windows
- USB 3.0 Interface

Disaster & Security Specifications

- Fire protection - 1550°F, 1/2 hour per ASTM E119
- Flood / Submersion protection - to 10 feet water depth, 72 hours
- Proven data protection and recovery
- Tested per UL, FCC and CE Standards
- Physical theft protection
- Cable lock or floor mount
- Kensington® Lock Compatible

Support

- Data Recovery Service (DRS) Plan Available
- Starting at 99¢ / TB per Month for DRS Basic. \$2.99/TB/Mo. for DRS Pro
- Up to \$2500 for forensic recovery for DRS Basic
- Up to \$5000 for forensic recovery for DRS Pro (also covers primary computer)
- Includes Full Version Bare Metal Restore and Continuous Data Protection Software
- Live Support Setup Assistance (Phone or Chat)
- 1 Year Standard "No Hassle Warranty" - repair or replace if broken for any reason
- DRS Plan automatically extends Warranty (Up to 5 Years)

Inside The Box

- ioSafe SOLO G3 External Hard Drive
- USB Cable
- Power Supply
- Owners Manual and Warranty

Electrical

- Electrical – AC input
- Voltage: 80 ~ 264 VAC at 50/60 HZ
- Typical Power Consumption: < 25W

System Requirements

- Intel Pentium II 350 Mhz-compatible or Mac G3 processor & greater
- USB for Microsoft Windows 7/Vista/XP, Mac OS 8.6 & greater or Linux based NAS devices
- For USB 3.0 speeds, the system must support applicable specifications

Operating Environment

- Operating: 0-35° C (95°F)
- Non-operating: 0-1550°F, 1/2 hr per ASTM E119
- Operating Humidity: 20% - 80% (non-condensing)
- Non-operating Humidity: 100%, Full water immersion, 10 feet, 3 days.

Physical

- Size: 5.0"W x 7.1"H x 11.0"L
- Weight: 15 lbs