



ECA3280A-BR



ECA3280B-BR



ECA3280A-B



ECA3280A-BW



ECA3280A-BL

Features

- **Meshed bezel with inherited gene of Ostrog and advanced ventilation**
- **32mm clearance for easy backside cable routing**
- **Top I/O for easy connection of external devices**
- **Easy installation**
 - Enermax patented SlideIn™ ODD design (Patent no. M438105)
 - Rails with anti-vibration rubber pads for 3.5" HDD installation
 - Removable HDD cage allows high-end VGA card installation
- **Utmost expandability**
 - Massive hard drive storage supports up to 13 devices
 - 8 expansion slots to support triple graphic cards
 - Internal USB 3.0 support for the fastest data transfer
- **Supreme cooling performance**
 - Maximum support up to 12x fans
 - Support 23/20cm monster fan
 - Support 280/240mm liquid cooling radiator
- **Transparent acrylic side panel shows individual inside view**
- **Bottom mounted PSU slot with rubber pads and removable dust filter**

Close-up for features



Top I/O and device tray for easy connection




Removable HDD cage



9 (8+1) expansion slots



Enermax patented SlideIn™ ODD design



32mm clearance for backside cable routing

Advanced Cooling System



VGA Card Support



Specifications

Model		ECA3280A	ECA3280B
Dimensions (DxWxH)		485 x 244 x 495 mm	
Drive bays	5.25"	3	
	3.5"	8 x hidden (4 x removable)	
	2.5"	2 x hidden	
M/B		Micro ATX, ATX	
Power		ATX 12V (Optional)	
I/O		USB 3.0 x 2, USB 2.0 x 2, HD Audio	
Cooling	Front	2 x 14cm LED fan with LED on/off function	2 x 14cm fan (1 x 14cm fan is Optional)
	Rear	1 x 12cm fan	
	Side	Acrylic window	
	Top	1 x 23/20cm or 2 x 14/12cm fan (optional)	
	Bottom	1 x 12cm fan (Optional)	
	HDD	4 x 12cm fan (Optional)	
Expansion Slots		8 + 1 (Vertical)	