

Highlights

Interactive displays have become one of the most powerful office tools today, replacing traditional meetings and trainings with a new style of business communication that's proven to enhance meeting efficiency, training effectiveness, collaborative discussion, and team building. A winning solution for your business, the BenQ Interactive Flat Panel IL460 combines the power of infrared touch panel and multimedia connectivity to maximize your presentations. Designed with safety and flexibility in mind, the IL460 is easy and simple to install in any office setting using a VESA wall mount.



Infrared 6 Points Touch Technology

Pair the IL460 with Windows® 8 / Windows® 7 and watch the infrared touch technology work its magic turning the displayed image or spreadsheet figure into a multi-touch screen. Trainer or speaker can invite audiences to come up to the board for a quick contest and trial.





Ambient Light Sensor

The IL460 is built with an ambient light sensor to detect the amount of ambient lighting in its surrounding and adjust the display setting accordingly without user intervention. This means the audience can always enjoy optimal picture quality in office.



Integrated Speaker

To help professional elites gain the competitive edge by enriching their meeting with multimedia resources, BenQ has built 12W speakers into the IL460. The use of videos, music and sound effects make every presentation more engaging and effective.



- 1 AC OUT
- 2 AC IN
- 3 AC SWITCH ON/OFF
- 4 USB
- 5 SPEAKERS (R/L) (IL650 not available)
- 6 AUDIO OUT (R/L)

- 7 AUDIO IN (AUDIO2)
- 8 AUDIO IN (AUDIO1)
- 9 VGA IN
- 10 VGA OUT
- 11 AV IN
- 12 AV OUT
- 13 VIDEO IN (S-VIDEO)
- 14 VIDEO IN (YPbPr)
- 15 RS232C IN / OUT
- 16 DVI-IN
- 17 HDMI
- 18 DISPLAY PORT
- 19 RJ-45

Specifications

Screen Size	46"
Type	PID
Light Source	E-LED
Active Area (mm)	1018.08 H x 572.67 V
Resolution (pixels)	FHD 1920 x 1080 (16:9)
Brightness (typ.)	500 cd/m ²
Native Contrast Ratio (typ.)	4,000:1
Response Time (GTG)	6.5 ms
Pixel Pitch (H x W)	0.53025 H x 0.53025 W mm
Frame Rate	60Hz
Viewing Angle (H / V)	178° / 178°
Color Gamut (x% NTSC)	72%
Color Depth	10-bit (8-bit+FRC), 1.07 billion
Technology	IR 6-point touch
Resolution (points area function)	4096x4096
Capacity	6 simultaneous touches
Accuracy	+/- 2.5mm
Touch Output	USB 2.0
OS Supported	Windows® XP (single point), Vista, Win 7, Win 8 (6 points), Linux (need to check distribution and kernel version) MAC (single point)
USB (Touch to External PC)	O
Power (AC) Input / Output	O / O
Power Switch	O
VGA Input / Output	O / O
DVI Input / Output	O / X
HDMI Input / Output	O / X
Composite Video In / Out (BNC)	O / O
Component In (YPbPr, RCA)	O
S-Video In / Out	O / X
DisplayPort Input	O
USB Player (Photo, Video)	X
RS232 Input / Output	O / O
OPS Slot	X
RJ45 Port	O
Audio W (Amp)	12W + 12W
Internal Speaker	12W x 2
Power Supply	AC 100~240V, 50 / 60 Hz
Power Consumption (Max)	<150W
Power Consumption (Standby)	<0.5W
Power Consumption (Off)	<0.5W
Operation Temp (dC)	0° C ~ 40° C
Storage Temp (dC)	20° C ~ 60° C
Usage (hrs/days)	24/7
Weight (without / with packing)	28 / 32.5 kg
Dimension (W x H x D)	1066 x 621 x 100 mm
Bezel Width (T / B / L / R)	22.5 / 22.5 / 22 / 22 mm
VESA Wall Mounting (mm)	400 x 200 (4 Holes)
Remote Controller	O
PWR Cord	O
VGA Cable	O
Quick Start Guide	O
User's manual electronic file	O
UPC Code / Part #	8400460-2883-1 / 9H.F09PQ.NA2
Stand Accessory (Optional)	P/N: 5J.F0714.001 (optional, on VESA mount)

Features

- Image Setting • Source / Volume Control • Analog Daisy Chain • RS232 Control Daisy Chain • ID Setting
- Sharpness Enhancement • Proof of Image Retention • Diming Control (Adaptive Contrast) • Picture in Picture (PIP)
- Picture by Picture (PBP) • DVI-HDCP (IL460 / IL460 not available) • DVI-HDCP • De-Interlacing / Comb Filter
- 10-bit Color Processing (IL460 not available) • Build-in Video Wall Support • Scheduling • Ambient Light Sensor
- Total Turn-On Time • Diagnostic DC voltage (12v / 5v) • Internal Temperature Sensor • CEC Control



IL460 07-25-13-BQca

BenQ Canada Corp.

Tel: (416) 363-2367 www.BenQ.ca

BenQ is a registered trademark of BenQ Corp. All rights reserved.

Product names, logos, brands, and other trademarks featured or referred to in the materials are the property of their respective trademark holders.

Specifications subject to change without notice.

BenQ

Enjoyment Matters