

IRIScan™ Book 3

You slide, it scans.

IRIScan™ Book 3 is a portable scanner that allows you to scan books and magazines anytime, anywhere and without ripping pages off. Simply roll your way across the document, and your scan will be saved automatically onto the provided MicroSD™ card and ready to be transferred into your PC or Mac.

Once back at home or in the office, the scanned documents are automatically turned into editable documents by I.R.I.S' flagship OCR software Readiris™ Pro 12.

Mobile scanner

- Cordless, battery-powered and very lightweight. Carry it anywhere!
- Ideal to scan books, magazines & newspapers.
- 300/600/900 dpi scanning resolutions.
- Scanning speed: 2 sec. for a B&W document/ 3 sec. for a color document.
- Directly scan to PDF and JPEG.
- Save scans onto the MicroSD™ card (included).
- Color screen (that preview the scanned images).
- Powered by 3 AAA alkaline batteries (included).

State-of-the-art OCR software Readiris™ Pro 12

- Convert any paper document, PDF, or image file into editable Office documents (Word, Excel®, Outlook®, etc.).
- Worldwide OCR solution - 137 recognized languages (incl. Asian and Arabic!).
- Create hyper-compressed PDF files, ideal for archiving and sharing via email.

Quick reference guide

Product name	IRIScan™ Book 3
SKU	457888
UPC-A code	765010730506
Custom code	847190
MSRP (USD)	\$99
Box size (H x L x D)	5.4 x 12.3 x 1.9 in
Box weight	19.4 oz
Scanner size (H x L x D)	1 x 10.1 x 1.4 in
Scanner weight	6.7 oz
Box languages	Arabic, Dutch, English, French, German, Italian, Portuguese, Russian, Spanish
Box content	IRIScan™ Book 3 scanner • Readiris™ Pro 12 software for PC and Mac® on CD-ROM • Free IRISCompressor™ Pro software • MicroSD™ card (including SD™ card adaptor) • USB cable • Transport pouch • Discount voucher for next purchase • Quick user guide



for Windows® and Mac®

Scanner specifications

Image sensor	A4/letter color contact image sensor
Image sensor width	8.54 in
Resolution	300/600/900 dpi
Maximum scanning speed for A4/letter document	Color high resolution : 13 seconds Black & white high resolution : 10 seconds Color low resolution : 3 seconds Black & white low resolution : 2 seconds
Capacity (A4/letter documents, based on 2GB MicroSD™ card. Depends on the content complexity)	900 dpi color : 250 JPEG images 600 dpi color : 500 JPEG images 300 dpi color : 1800 JPEG images
File formats	JPEG & PDF
LCD	Scanning status display
Auto power off	3 minutes
USB port	USB 2.0 high speed
External memory	MicroSD™ card / MicroSDHC™ card up to 32 GB
Batteries	3 x AAA alkaline batteries
Battery life (scanning to MicroSD™ card)	550 pages (A4/letter, 300 dpi, color)

Minimum computer requirements

Scanner

- MicroSD™/SD™ card port (not mandatory).
- At least one USB port available.
- Not driver installation needed!

Software suite for Windows®

- Microsoft® Windows® 8, 7, Vista® or XP.
- 512MB RAM (1GB recommended).
- 300MB of available hard disk space.
- CD-ROM drive and at least one USB port available.

Software suite for Mac OS®

- A Mac® computer with Intel® processor.
- Mac OS® X Leopard, Snow Leopard, Lion or Mountain Lion (earlier versions not supported).
- Minimum 300MB of available hard disk space.
- 512MB RAM (1GB recommended).
- CD-ROM drive and at least one USB port available.



www.irislink.com



PRODUCTS & TECHNOLOGIES

© Copyright 2013 I.R.I.S. s.a.
All rights reserved for all countries. I.R.I.S., I.R.I.S.' product names, I.R.I.S.' logos and I.R.I.S.' product logos are I.R.I.S. trademarks. All other products and names mentioned are trademarks or registered trademarks from their respective owners.

J130531-3