

Fujitsu recommends Windows 8 Pro.

# Data Sheet

## Fujitsu LIFEBOOK P702

### Notebook

#### Ultra-Mobile Performance to Go

If you need a versatile and lightweight notebook for your everyday business tasks, the Fujitsu LIFEBOOK P702 should be your first choice. Its small form factor, 30.7 cm (12.1-inch) display and long battery runtime ensure enhanced mobile productivity. The ShockSensor protects your hard disk drive against physical impacts while its robust magnesium lid and various security features guarantee that the notebook is secure both on the move and in the office.

#### Full performance mobility

Maximum productivity even for the most demanding applications thanks to state-of-the-art technology.

- 3rd generation Intel® Core™i3 or Core™i5 processor with Intel® HM76 chipset



#### Maximum security

Protect your company data against unauthorized third-party access.

- Advanced Theft Protection (Intel® Anti Theft & Computrace®), integrated SmartCard slot, optional fingerprint sensor, TPM module and OmniPass Security Software



#### Reliable companion

Secure and effective working even for the most demanding of users in all situations

- Robust and lightweight magnesium lid, ShockSensor, long battery runtime, spill-resistant keyboard
- Optional 0-Watt AC Adapter guarantees that the notebook does not consume electricity when switched off

#### Ergonomic working

Enhance your user experience with clever ergonomic features.

- ScrollWheel, optional HD webcam, small form factor
- Anytime USB Charge to charge phones/media devices even when the system is turned off



#### Ultimate connectivity

Stay connected wherever you are; wireless connectivity anytime anywhere, even if there is no hotspot nearby.

- Optional embedded 3G/UMTS or 4G/LTE, WLAN
- Bluetooth® and integrated DisplayPort



# Components

<b>Processor</b>	Intel® Core™ i5-3230M processor (2.6 GHz, up to 3.2 GHz, 3 MB) * Intel® Core™ i3-3120M processor (2.5 GHz, 3 MB) * Intel® Core™ i5-3340M processor (2.7 GHz, up to 3.4 GHz, 3 MB) Intel® Core™ i5-3320M processor (2.6 GHz, up to 3.2 GHz, 3 MB)
	*Processor only for retail, SMB, education and government
	Intel® Core™ i5 processor
<b>Operating systems</b>	
<b>Operating system</b>	Windows 8 Pro 64-bit Windows 8 64-bit Windows 7 Professional 64-bit Windows 7 Home Premium 64-bit Windows 7 Home Basic 64-bit (EM)
<b>Operating system compatible</b>	Windows® XP 32-bit Windows 8 32-bit
<b>Operating system notes</b>	Limited Windows® XP support. Microsoft discontinued Windows® XP certification on system level, basic drivers via <a href="http://support.ts.fujitsu.com">http://support.ts.fujitsu.com</a>
<b>Memory modules</b>	2 GB (1 module(s) 2 GB) DDR3, 1,600 MHz, PC3-12800, SO DIMM 4 GB (1 module(s) 4 GB) DDR3, 1,600 MHz, PC3-12800, SO DIMM 8 GB (1 module(s) 8 GB) DDR3, 1,600 MHz, PC3-12800, SO DIMM
<b>Hard disk drives (internal)</b>	SSD SATA III FDE, 128 GB, 2.5-inch SSD SATA III, 256 GB, 2.5-inch SSD SATA III, 128 GB, 2.5-inch SATA, 7,200 rpm, 500 GB, 2.5-inch, S.M.A.R.T. SATA, 7,200 rpm, 320 GB, 2.5-inch, S.M.A.R.T. SATA, 5,400 rpm, 320 GB, 2.5-inch, S.M.A.R.T. FDE, 5,400 rpm, 320 GB, 2.5-inch, S.M.A.R.T.
<b>Hard disk notes</b>	ShockSensor for HDD shock protection One Gigabyte equals one billion bytes, when referring to hard disk drive capacity. Accessible capacity may vary, also depending on used software. Up to 20 GB of HDD space is reserved for system recovery Internal HDD interface: S-ATA III (6Gb/s)
<b>Interface add on cards/components (optional)</b>	
<b>3G/4G (optional)</b>	Sierra Wireless Gobi 3000 (Downlink speed 14.4 Mbit/s, Uplink speed 5.76 Mbit/s) LTE Sierra Wireless MC7710 (Downlink speed up to 100 Mbit/s, Uplink speed up to 50 Mbit/s)
<b>WLAN (optional)</b>	Intel® Centrino® Wireless-N2200 b/g/n Intel® Centrino® 6205 802.11 a/b/g/n
<b>Bluetooth</b>	Bluetooth 4.0
<b>Display</b>	30.7 cm (12.1-inch), LED backlight, (WXGA), Anti-glare display, magnesium, 1,280 x 800 pixel, 300:1, 200 cd/m <sup>2</sup>
<b>Multimedia</b>	
<b>Camera</b>	Optional: Built-in HD webcam or Full HD webcam (Microsoft® Lync™) (depending on configuration)

## Base unit

<b>Base unit</b>	LIFEBOOK P702
<b>General system information</b>	
<b>Chipset</b>	Intel® HM76
<b>Memory slots</b>	2 DIMM (DDR3)
<b>Supported capacity RAM (min.)</b>	2 GB
<b>Supported capacity RAM (max.)</b>	16 GB
<b>Memory notes</b>	DDR3 - 1,600 MHz
<b>LAN</b>	Built-in 10/100/1,000 MBit/s Intel® 82579 V
<b>BIOS features</b>	BIOS based on Phoenix SecureCore
<b>Audio type</b>	On board
<b>Audio codec</b>	Realtek ALC269
<b>Audio features</b>	Stereo speakers, 1x built-in microphone
<b>Display</b>	
<b>Display notes</b>	ISO 9241-307 - Pixel class II
<b>Graphics</b>	
<b>Base unit</b>	LIFEBOOK P702
<b>TFT resolution (DisplayPort)</b>	up to 2,560 x 1,600
<b>TFT resolution (VGA)</b>	up to 1,920 x 1,200
<b>TFT resolution (DVI on Port Replicator)</b>	up to 1,920 x 1,200
<b>TFT resolution (DisplayPort on Port Replicator)</b>	up to 2,560 x 1,600
<b>Graphics brand name</b>	Intel® HD Graphics 4000 with 3rd generation Core i processors
<b>Graphics features</b>	3 Display Support with 3rd generation Core i processors (1x internal display, 1x Displayport with system, 1x Displayport with port replicator)
<b>Graphics notes</b>	Shared memory depending on main memory size and operating system
<b>Interfaces</b>	
<b>DC-in</b>	1
<b>Audio: line-out / headphone</b>	1
<b>Audio: line-in / microphone</b>	1
<b>Internal microphones</b>	1 (digital)
<b>USB 2.0 total</b>	2
<b>USB 3.0 total</b>	1 (with Anytime USB Charge functionality)
<b>VGA</b>	1
<b>DisplayPort</b>	1 (V1.1a)
<b>Ethernet (RJ-45)</b>	1
<b>Modem (RJ-11)</b>	
<b>Memory card slots</b>	1 (SD up to 2GB, SDHC up to 32GB, SDXC up to 64GB)
<b>Express card slots</b>	1 (34 mm supported)
<b>SmartCard slot</b>	1
<b>SIM card slot</b>	1
<b>Port Replicator interfaces (optional)</b>	
<b>DC-in</b>	1 (19V)
<b>Power on switch</b>	1
<b>USB 2.0 total</b>	4
<b>DisplayPort</b>	1 (up to 2560 x 1600) (not usable in parallel with DVI) In case both are connected DisplayPort has higher priority.
<b>VGA</b>	1
<b>DVI</b>	1 (up to 1920 x 1200) (not usable in parallel with DisplayPort)
<b>Ethernet (RJ-45)</b>	1 (10/100/1000)
<b>eSATA</b>	1
<b>Notes</b>	Port replicator supports 0-Watt functionality. Display port is shared with DVI - exclusive usage

**Keyboard and pointing devices**

Spill-resistant keyboard (new layout)  
 Number of keyboard keys: 83, Keyboard pitch: 18 mm, Keyboard stroke: 2.0 mm  
 Multi-gesture touchpad with two mouse buttons and ergonomic ScrollWheel  
 Optional: Fingerprint sensor  
 Application buttons

**Wireless technologies**

<b>Antennas</b>	2 Dual band WLAN antennas, 2 UMTS/LTE antennas optional, 1 Bluetooth antenna optional
<b>WLAN notes</b>	Import and usage according to country-specific regulations.

**Power supply**

<b>AC Adapter</b>	19 V / 65 W (3.42 A), 100 V - 240 V, 50 Hz - 60 Hz, Slim and light AC-Adapter, 0.180 kg, 133x30x30 mm 19 V / 65 W (3.42 A), 100 V - 240 V, 50 Hz - 60 Hz, Standard AC-Adapter, 0.250 kg, 108x46x30 mm 19 V / 100 W (5.27 A), 100 V - 240 V, 50 Hz - 60 Hz, 3-pin (grounded) AC-Adapter, 0.250 kg, 148x56x32 mm 19 V / 80 W (4.22 A), 100 V - 240 V, 50 Hz - 60 Hz, Standard Adapter, 0.340 kg, 140x56x29 mm 19 V / 80 W (4.22 A), 100 V - 240 V, 50 Hz - 60 Hz, 0-Watt AC Adapter technology, 0.340 kg, 140x56x28 mm
-------------------	--

<b>Notes</b>	65W AC Adapter for usage with system/ 80W AC Adapter for usage with Port Replicator
--------------	---

<b>1st battery options</b>	Li-Ion battery 6-cell, 6,700 mAh, 72 Wh Li-Ion battery 6-cell, 5,800 mAh, 63 Wh
----------------------------	--

<b>Runtime 1st battery</b>	up to 13 h
----------------------------	------------

<b>Battery charging time</b>	~160 min (63Wh) ~ 190 min (72Wh)
------------------------------	----------------------------------

<b>Battery notes</b>	Battery runtime information is based on worldwide acknowledged BAPCO Mobile Mark 2007 Benchmark (readers mode e.g. surfing the internet, writing E-mails, viewing documents) which provides results that enable direct product comparisons between manufacturers. It does not guarantee any specific battery runtime which actually can be lower and may vary depending on product model, configuration, application and power management settings. The battery capacity slightly decreases with every charging cycle and over the lifetime.
----------------------	--

**Power consumption**

<b>Power consumption note</b>	See white paper Energy Consumption
<b>Link to Energy White Paper</b>	<a href="http://docs.ts.fujitsu.com/dl.aspx?id=4516235c-6e4d-46cc-8533-1adfe46b4771">http://docs.ts.fujitsu.com/dl.aspx?id=4516235c-6e4d-46cc-8533-1adfe46b4771</a>

**Dimensions / Weight / Environmental**

<b>Dimensions (W x D x H)</b>	283 x 215 x 25 (front) / 32 (rear) mm
<b>Weight</b>	1.48 kg
<b>Weight notes</b>	Actual weight may vary depending on configuration
<b>Operating ambient temperature</b>	5 - 35 °C
<b>Operating relative humidity</b>	20 - 85 %

**Compliance**

<b>Europe</b>	CE CB
<b>USA/Canada</b>	FCC (depending on configuration)
<b>Global</b>	RoHS (Restriction of hazardous substances) WEEE (Waste electrical and electronic equipment) Microsoft Operating Systems (HCT / HCL entry / WHQL) ENERGY STAR® 5.0 EPEAT® Gold (dedicated regions)
<b>China</b>	CCC (depending on configuration)
<b>Compliance link</b>	<a href="http://globalsp.ts.fujitsu.com/sites/certificates">http://globalsp.ts.fujitsu.com/sites/certificates</a>

**Additional Software**

<b>Additional software (preinstalled)</b>	Adobe® Reader® (pdf reader) Fujitsu LIFEBOOK Application Panel Fujitsu Display Manager ShockSensor Utility Power Saving Utility Fujitsu Plugfree Network (network management utility) EasyGuide online user documentation Win8: Microsoft Push Button Recovery (hard disk based recovery) Microsoft Office (buy license to activate the pre-installed Microsoft Office) Win7: Fujitsu Recovery (hard disk based recovery) McAfee Internet Security and Antivirus Software (60 days trial version)
<b>Additional software (optional)</b>	Drivers & Utilities DVD (DUDVD) UMTS connection manager (optional with UMTS)

**Manageability**

<b>Manageability technology</b>	DeskUpdate Driver management PXE 2.1 Boot code Wake up from S5 (off mode) WoL (Wake on LAN)
<b>Manageability software</b>	DeskView Client DeskView Instant BIOS Management DeskView Integration for Symantec Management Platform
<b>DeskView components</b>	Inventory Management BIOS Management Driver Management Security Management Alarm Management
<b>Supported standards</b>	WMI PXE BootP (made4you)
<b>Manageability link</b>	<a href="http://www.fujitsu.com/fts/solutions/high-tech/solutions/workplace/manageability/feature-finder.html">http://www.fujitsu.com/fts/solutions/high-tech/solutions/workplace/manageability/feature-finder.html</a>

**Security**

<b>Physical Security</b>	Kensington Lock support
<b>System and BIOS Security</b>	Advanced Theft Protection (Intel® Anti Theft & Computrace®) Optional: Trusted platform module (TPM 1.2)
<b>User Security</b>	Hard disk password Integrated SmartCard slot User and supervisor BIOS password Integrated fingerprint sensor including OmniPass software (optional)

**Warranty**

<b>Standard Warranty</b>	1 year (depending on country)
<b>Service level</b>	Collect & Return Service / Bring-in Service (for countries within region FTS CEMEA&I, for all other countries depending on local regulations)
<b>Warranty Terms &amp; Conditions</b>	<a href="http://support.ts.fujitsu.com/warranty">http://support.ts.fujitsu.com/warranty</a>
<b>Maintenance and Support Services - the perfect extension</b>	
<b>Recommended Service</b>	9x5, Response Time: Next Business Day
<b>Spare Parts availability</b>	5 years after end of product life
<b>Service Weblink</b>	<a href="http://www.fujitsu.com/fts/services/support">http://www.fujitsu.com/fts/services/support</a>

## Recommended Accessories

### Port Replicator



Flexibility, expandability, desktop replacement and investment protection are just a few benefits of Fujitsu docking options. It takes just a second to attach your notebook to the Port Replicator and get connected to your external display, keyboard and mouse. Your workplace is simple and tidy while you are instantly ready to work with your notebook.

Order Code:  
S26391-F977-L100

### LIFEBOOK Bundle (Port Replicator, AC Adapter, EU Cable Kit)



The combination of a Fujitsu Port Replicator and AC Adapter (with EU cable) is the perfect docking solution for your LIFEBOOK. Simplify your mobile life. In the office or at home it takes just a second to attach your notebook to the port replicator and get connected to your peripherals.

Order Code:  
S26391-F977-L200

### AC Adapter LIFEBOOK



Power your notebook at work, at home or on the road with a second power source. You can easily recharge your notebook everywhere. Depending on your notebook you can choose from various AC Adapters ranging from a slim stick type adapter to standard adapters, or even the innovative 0-Watt AC Adapter.

Order Code:  
S26391-F886-L200

### PocketSaver



The Fujitsu Kensington PocketSaver with its pocketable design and 1200mm retractable steel cable is the perfect anti-theft solution for when you are on the go. The patented T-bar lock mechanism and the tempered steel cable provide maximum security. The Fujitsu Kensington PocketSaver keeps your device protected wherever you roam.

Order Code:  
S26391-F6045-L100

### Privacy filter



Privacy filters help block the screen view from anyone viewing the computer from a side view. 3M's unique microlouver privacy technology allows persons directly in front of the computer to see on-screen data clearly.

Order Code:  
S26391-F6097-L312

### Supreme Case



The Supreme Case protects notebooks with up to 15.6-inch screens and provides ample storage for power adapters, office supplies and documents. The high-quality leather used for this case is sure to impress with its strong, yet lightweight structure and rich, dark color. Customers will also be pleased to note the smooth interior design of the bag, as well as the robust metal clips which keep your notebook safe. The professional finish, elegant design and carrying comfort of this model make it the ideal business case.

Order Code:  
S26391-F1192-L900

### SOUNDSYSTEM DS P2100 Tube



Taking inspiration from a hi-fi sound bar, the Fujitsu SOUNDSYSTEM DS P2100 Tube presents you with living room design art pieces for acoustic enjoyment. Automatic amplifier adjustment ensures extremely low distortion, which will protect the hearing and avoid speaker damage. With new convenient volume control- Fade-in & Fade-out audio effect. The small & robust satellite speaker is decorated with a deluxe piano finish and the aluminum tube is adorned with a fine print of an exotic motif at its base.

Order Code:  
S26391-F7128-L500

**Mobile Bluetooth Communication Speaker**

The Fujitsu Mobile Bluetooth Communication Speaker is the perfect audio accessory for your connected mobile life. It is smaller than a tennis ball so you can bring it everywhere and it can connect via Bluetooth so you don't have to worry about cords. An integrated microphone gives you on-the-fly conference call capabilities for all your Bluetooth enabled mobile devices.

Order Code:  
S26391-F7128-L700

**HS S2000NC Headset**

The HS S2000NC Headset offers more than current headsets. Besides superb sound quality, the headset provides an impressive feature: a button to switch off noise and disburden your ears of unwanted noise level. Thanks to a special technology based on wave inversion this headset reduces unwanted noise by up to 70 % for a quieter audio experience. The sponge cushion specially made by BioProtein ensures optimum comfort for long hours travelling by rail or air.

Order Code:  
S26391-F7128-L710

# More information

## Fujitsu OPTIMIZATION Services

In addition to Fujitsu LIFEBOOK P702, Fujitsu provides a range of platform solutions. They combine reliable Fujitsu products with the best in services, know-how and worldwide partnerships.

## Fujitsu Portfolio

Build on industry standards, Fujitsu offers a full portfolio of IT hardware and software products, services, solutions and cloud offering, ranging from clients to datacenter solutions and includes the broad stack of Business Solutions, as well as the full stack of Cloud offering. This allows customers to leverage from alternative sourcing and delivery models to increase their business agility and to improve their IT operation's reliability.

## Computing Products

[www.fujitsu.com/global/services/computing/](http://www.fujitsu.com/global/services/computing/)

## Software

[www.fujitsu.com/software/](http://www.fujitsu.com/software/)

## More information

Learn more about Fujitsu LIFEBOOK P702, please contact your Fujitsu sales representative or Fujitsu Business partner, or visit our website.

[www.fujitsu.com/fts/mobile](http://www.fujitsu.com/fts/mobile)

## Fujitsu green policy innovation

Fujitsu Green Policy Innovation is our worldwide project for reducing burdens on the environment.

Using our global know-how, we aim to contribute to the creation of a sustainable environment for future generations through IT. Please find further information at <http://www.fujitsu.com/global/about/environment>



## Copyrights

All rights reserved, including intellectual property rights. Changes to technical data reserved. Delivery subject to availability. Any liability that the data and illustrations are complete, actual or correct is excluded. Designations may be trademarks and/or copyrights of the respective manufacturer, the use of which by third parties for their own purposes may infringe the rights of such owner.

For further information see [www.fujitsu.com/terms](http://www.fujitsu.com/terms)

Copyright © Fujitsu Technology Solutions

## Disclaimer

Technical data are subject to modification and delivery subject to availability. Any liability that the data and illustrations are complete, actual or correct is excluded. Designations may be trademarks and/or copyrights of the respective manufacturer, the use of which by third parties for their own purposes may infringe the rights of such owner.

## CONTACT

FUJITSU Technology Solutions

Website: [www.fujitsu.com/fts](http://www.fujitsu.com/fts)

2014-04-08 CE-EN

All rights reserved, including intellectual property rights. Changes to technical data reserved. Delivery subject to availability. Any liability that the data and illustrations are complete, actual or correct is excluded.

Designations may be trademarks and/or copyrights of the respective manufacturer, the use of which by third parties for their own purposes may infringe the rights of such owner.

For further information see [www.fujitsu.com/terms](http://www.fujitsu.com/terms)

Copyright © Fujitsu Technology Solutions