

MC362w/MC562w MFP

OKI®



All-in-one functionality plus wireless. HD Color output. Superior speed and media flexibility. Eco-friendly, too.



OKI and The Environment

- ENERGY STAR® Compliant** Superior energy efficiency
- Toner Save Mode** Extends life of toner cartridges
- Duplex (2-Sided) Printing** Saves energy and resources
- Automatic ECO Mode** Prints fast and with less energy
- 1-Piece Image Drum** Fewer consumables to replace
- Deep Sleep Mode** Reduces power to less than 2 watts



The MC362w/MC562w Color MFPs enhance productivity with print/copy/scan/fax and wireless functionality.

Highlights:

	MC362w Color MFP	MC562w Color MFP
• Print Speed (Maximum)¹	23 ppm Color, 25 ppm Mono	27 ppm Color, 31 ppm Mono
• Time to First Print¹	9.0 seconds Color, 8.5 seconds Mono	8.0 seconds Color, 7.5 seconds Mono
• Toner Capacity	3,000-pages CMY; 3,500-pages K (Black)	5,000-pages CMYK
• Keyboard	Alphanumeric keypad	Alphanumeric keypad and QWERTY keyboard
• SD Memory for Document Storage	N/A	4GB standard; 16GB option
• Duplex (2-sided) Printing	Standard	
• Paper Capacity (Standard / Max)	350 sheets / 880 sheets	
• Memory (Standard / Max)	256 MB / 768 MB	
• Processor	533 MHz Power PC CPU	
• Connectivity	High-speed USB 2.0; 10/100TX Network	
• Emulations	PCL® 5c, PCL 6; PostScript® 3™	
• Size (WxDxH)	16.8" x 20" x 17.5" (427 mm x 509 mm x 444 mm)	

Additional Highlights:

- **HD Color printing technology for outstanding print and copy quality**
- **Wireless printing from mobile devices via Apple® AirPrint™ and MotionPrint™ from OKI®**
- **Multi-tasking functionality standard**
- **PCL® and PostScript® 3™ emulations**
- **Duplex (2-sided) printing/copying standard**
- **Full-featured fax with dual access functionality and 4 MB fax memory**
- **Scan directly to a PC, network folder, e-mail or USB memory stick**
- **Print from USB memory stick**
- **50-sheet reversing automatic document feeder (RADF) standard – saves time and energy**
- **Banner printing capability on sheets up to 52" in length³**
- **Print Job Accounting software helps control costs by defining who can print what in color, monochrome or not at all**
- **Separate CMYK toner cartridges for lower cost of operation**
- **Compact design to fit the smallest environment**
- **ENERGY STAR® compliant**
- **3-Year Carry-In/Depot limited warranty⁴**
- **Live, toll-free technical support, 24/7/365⁴**

The OKI® MC362w/MC562w Color MFPs

combine high-quality color and four-in-one functionality with speed, reliability, ease of use and wireless printing capabilities—superior value from a desktop device that has a footprint small enough to fit easily into your environment.

MC362w and MC562w MFPs print and copy in HD Color, an OKI exclusive: multi-level print-heads and microfine toner provide more detail, greater color depth and reduced grain, for breathtaking output even on ordinary office paper.

They're the perfect solution for your company's small workgroups.

Enhance the productivity of your staff –

These MFPs are fast: they print or copy at up to 27 color pages or 31 black & white pages per minute, with the first color page printing in as little as 8 seconds.¹

Their reversing automatic document feeder (RADF) quickly scans both sides of a document, and their multi-tasking capabilities let you set up or perform two tasks at the same time. And, with their robust duty cycles, these durable devices can be relied upon to handle large daily print and copy volumes.

Scan at the machine or from your desk – Turn hard-copy documents into electronic files with multiple options. Scan documents in color or black & white, and send them to your PC, a network folder, a USB stick, or to a list of e-mail addresses.

You can also remotely preview and scan your documents on your PC via the network

connection. Insert a USB memory stick into the convenient front port to save scanned documents to or print files directly from the USB stick.

They can make your job easier – The MC362w and MC562w are really user friendly: network-ready right out of the box, with an intuitive operator panel that's simple to use: a 3.5" backlit LCD display that tilts up for easy reading, and 1-touch keys for fast dialing. The MC562w also has a full QWERTY keyboard, so you can quickly enter e-mail addresses or the names of documents.

Wireless printing – Both MFPs offer wired and Wi-Fi® wireless printing. There's nothing to install or configure. Print directly from your iPhone® or iPad® via Apple AirPrint™, or use MotionPrint™ from OKI to extend mobile printing to Android™ and BlackBerry® devices. Tap "Print," select the MC362w or MC562w and print. It's that simple.

Full-featured fax – Both models have robust faxing features that include Internet faxing; forwarding to e-mail or network folders (saving paper and securing sensitive documents); sending faxes directly from your PC; Tel/Fax Switching; Distinctive Ring; and 16 one-touch fax buttons.

Expect more support – You can expect total support for your MC362w/MC562w MFPs from your Authorized OKI MFP provider.

If you need technical assistance, you can speak to a live expert based in North America, 24/7/365, by calling toll-free: **800.OKI.DATA** (800.654.3282).⁴

Convert hard copies to digital files, manage your document workflow, and help the environment.

Full functionality at your fingertips – The user-friendly operator panel of MC362w/MC562w MFPs features a clear, organized array of navigation buttons, a backlit LCD display, alphanumeric keypad and 1-touch fax dialing keys. The MC562w also has a full QWERTY keyboard. Both models come with productivity-enhancing software:

- **PaperPort® from Nuance®** easily turns piles of paper and photos into PDF and JPEG files—using the MFP's scanner—and saves them to your computer for future use.
- **OmniPage® from Nuance**—optical character recognition (OCR) software—quickly turns hard-copy office documents and forms into electronic files for easy editing, searching and sharing.

- **Desktop Capture Solution**—works through PaperPort's Active Directory Authentication to move scanned documents into your SharePoint® or DocuWare® workflow, quickly and easily.⁵

Environmentally friendly features – The MC362w/MC562w MFPs also help you control your effect on the planet's health by providing:

- **Duplex (2-sided) printing** It's standard on the MC362w and MC562w. Use both sides of a sheet rather than two sheets. Saves paper—and is even more energy-efficient.
- **Automatic ECO mode** These MFPs optimize the print time for small jobs, using less energy. Same terrific output, faster throughput, lower power consumption. Everybody wins.

- **Deep sleep mode** When left on for an extended period, the MC362w and MC562w slip into this mode, which uses less than 1.5 watts of power.
- **One-piece image drum** This long-lasting, user-replaceable consumable remains friendly to your budget while lowering the number of items to dispose of and store.
- **ENERGY STAR® compliance** With their lower power consumption—especially in Deep sleep mode—both the MC362w and MC562w MFPs meet the government's standards for energy efficiency.

THE MC362w/MC562w MFPs AT A GLANCE



Easy-to-read and -use operator panel: ergonomically designed to meet the needs of your workflow environment—keeping tasks simple and end users more productive. Backlit LCD display tilts up to enhance user productivity.



Full QWERTY keyboard (MC562w, behind 1-Touch key panel): enables easy entry of email addresses and messages.

Dual access: scan faxes into memory while the unit is busy sending or receiving faxes

Flatbed scanner: handles up to 8.5" x 11" documents on the glass and up to 8.5" x 14" via the Reversing Auto Document Feeder (RADF)

Backlit LCD display: 3.5-inch screen tilts up as much as 90° to further simplify navigation

Multi-tasking: performs two tasks at the same time

High-Definition Color: HD Color printing technology ensures breathtaking output, even on plain paper

100-sheet multi-purpose tray: also handles 3" x 5" cards, envelopes and banner sheets up to 8.5" x 52"³

250-sheet paper tray: fewer user interventions means greater productivity

Optional 530-sheet 2nd paper tray: increases max paper capacity to 880 sheets



50-sheet RADF: scans both sides of a sheet; increases user productivity

Alphanumeric keypad: easily enter fax numbers, codes and quantities

1-Touch dialing: pre-program up to 16 fax locations (on MC562w, panel lifts to reveal QWERTY keyboard)

Scan to/Print from USB memory stick: convenient front port makes these operations quick and easy

Wireless connectivity: enables printing over a Wi-Fi CERTIFIED™ network

Single Pass Color™ technology: straight-through paper path allows for superior flexibility in paper handling

Compact, space-saving design: the small footprint of MC362w/MC562w MFPs allows them to fit into most work spaces

¹ Published performance results based on laboratory testing on simplex sheet (1 side). Individual results may vary.

² Based on ITU-T Test Chart #1.

³ Larger files may require additional memory.

⁴ Available in the U.S. and Canada only.

⁵ Requires optional connectors.

MC362w/MC562w MFP

Specifications

Printer

- **Print Speed:** MC362w – up to 23 ppm color, 25 ppm mono; MC562w – up to 27 ppm color, 31 ppm mono¹
- **Time to First Page:** MC362w – as fast as 9 sec. color, 8.5 sec. mono; MC562w – 8 sec. color, 7.5 sec. mono¹
- **HD Color Printing Technology:** Combines multilevel LED printheads and microfine toner for sharp detail and rich color depth
- **Print Resolution:** Up to 1200 x 600 dpi
- **Processor Speed:** 533 MHz
- **Monthly Duty Cycle:** MC362w – up to 45,000 prints/copies (recommended usage 3,000 pg.); MC562w – up to 60,000 prints/copies (recommended usage 5,000 pg.)
- **Duplex (2-Sided) Printing/Copying:** Standard
- **Print from USB Memory Stick:** Via front USB port
- **Connectivity:** USB v2.0 high-speed; 10/100 Base-TX Ethernet (network); Wireless
- **Printer Languages:** PCL® 6, PCL 5c; PostScript® 3™; IBM® ProPrinter®, Epson® FX
- **Operating Systems:** Microsoft® Windows® 8, Windows 7, Windows Vista®, Windows XP Home/XP Professional, Windows Server 2008, Server 2008 R2, Server 2003; Mac® OS X 10.5 and higher
- **Fonts:** Scalable – 87 PCL, 80 PostScript; Bitmap – OCR-A, OCR-B, Line Printer, USPS; Barcode – 12 types + PDF417

Copier

- **Copy Speed:** MC362w – up to 23 cpm color, 25 cpm mono; MC562w – up to 27 cpm color, 31 cpm mono¹
- **First Copy Out:** As fast as 14 sec. color, 12 sec. mono¹
- **Duplex (2-Sided) Copying:** Standard
- **Copy Resolution:** Up to 600 x 600 dpi
- **Copy Scaling:** 25% to 400% in 1% increments; 11 pre-set scaling sizes
- **Copy Quantity Selection:** 1–99
- **ID Card Copy:** Print both sides of ID on one side of sheet

Scanner

- **Scan Type:** Color flatbed; Reversing Auto Document Feeder (RADF)
- **Scan Resolution:** Up to 1200 x 1200 dpi
- **Scan Speed:** Approx. 3 sec./page color, approx. 2 sec./page mono at 300 dpi (simplex)
- **Scan-to-PC:** Create electronic file from hard copy original in PDF, TIFF or JPEG file formats (TWAIN scanning driver included; Windows compatible)
- **Address Book Management:** LDAP (Lightweight Directory Access Protocol)
- **Scan-to Functionality:** Scan to e-mail with LDAP support; to USB memory stick; to FTP sites; to network; and to PC
- **Formats Supported:** PDF, TIFF, JPEG, BMP, PCX, GIF, TGA, PNG, WMF, EMF
- **TWAIN Driver:** Windows 2000 and higher; enables remote preview and scan functionality via network

Fax

- **Fax Modem:** 33.6 Kbps Super G3
- **Transmission Speed:** 3 seconds/page²
- **Fax Resolution:** Up to 200 x 400 dpi
- **1-Touch Dials:** 16 locations
- **Speed Dials:** 100 locations

- **Broadcast Transmissions:** Up to 100 locations
- **Fax Memory:** 200 pages² (4 MB)
- **Fax Functions:** Dual access (perform additional functions while sending/receiving), T.37 Internet fax, Tel/Fax auto switching, Telephone answering device (TAD) interface, Distinctive ring, Broadcasting, Manual transmission, Delayed transmission, Auto redial, Auto receive, Activity reports, Protocol report (for troubleshooting)

Multi-Tasking

- **Operation:** Set up or perform two tasks at the same time

Wireless LAN

- **Protocols:** IEEE802.11 b/g/n; Infrastructure Mode; WEP; WPA™ (TKIP), WPA2™ (AES); WPS-PBC, WPS-PIN; Open system authentication; Shared key authentication; IEEE802.1x authentication

Operator Panel

- **Features:** 5-line, 3.5" tilting (up to 90°) backlit LCD display; Alphanumeric keypad; 1-touch fax dials (16); Full QWERTY keyboard (MC562w only)

Document Management

- **Utility Suite:** Nuance® PaperPort® SE v. 11, OmniPage® SE v. 16, OKI LPR, Color Correct, Swatch Utility, ActKey Utility, Network Card Setup Tool, MFP Configuration Tool, TWAIN Driver, Fax Driver, Printer Driver, Print Job Accounting, PrintSuperVision, Desktop Document Capture

System Memory

- **Standard/Max Imaging RAM:** 256 MB/768 MB
- **SD Card Storage:** 4 GB standard; 16 GB optional (MC562w only)

Paper Handling

- **Standard Input:** 350 sheets – 250 sheets via Main Tray + 100 sheets via Multi-purpose Tray (MPT)
- **Maximum Input:** 880 sheets (with optional 530-sheet 2nd Paper Tray)
- **Scanner RADF:** Up to 50 letter/legal sheets
- **Output Capacity:** 150 sheets, face down
- **Paper Sizes (Min./Max.):** Main Tray from 4.1" x 5.8" to 8.5" x 14"; optional 2nd Tray from 5.8" x 8.3" to 8.5" x 14"; MPT from 3" x 5" cards to 8.5" x 52" banners
- **Paper Types:** Letter, Legal 13/13.5/14, Banner, Executive, A4, A5, A6, B5; Envelopes – C5, DL, Monarch, COM 9, COM 10
- **Paper Weight:** Main Tray/Opt. 2nd Tray 17 lb. bond – 65 lb. cover (64–176 gsm); RADF 16 lb. – 28 lb. bond (60–105 gsm); MPT 17 lb. bond – 80 lb. cover (64–220 gsm)

Environmental

- **Size (WxDxH):** 16.8" x 20" x 17.5" (427 mm x 509 mm x 444 mm)
- **Weight:** Approx. 63 lb. (29 kg), including consumables
- **Power Consumption:** Operating Normal 570W; Max 1170W; Idle 100W; Power save mode 20W; Deep sleep mode <1.5W; Auto-off mode <0.5W
- **ENERGY STAR® Compliant:** Yes
- **Acoustic Noise:** Printing – 54.0dBA or less; Copying – 55.5dBA or less; Standby – 37.0dBA or less; Power Save – Inaudible

Ordering Information

Description	Part Numbers	
MC362w 120V (Multilingual)	62441804	
MC562w 120V (Multilingual)	62441904	
Options		
530-Sheet 2nd Paper Tray	44472101	
256 MB DIMM	70061801	
512 MB DIMM	70061901	
16 GB SD Card (MC562w only)	70061701	
Supplies		
Toner Cartridges:		
Cyan Toner Cartridge	3,000 pg. ⁴	44469703
Magenta Toner Cartridge	3,000 pg. ⁴	44469702
Yellow Toner Cartridge	3,000 pg. ⁴	44469701
Black Toner Cartridge	3,500 pg. ⁴	44469801
High-Capacity Toner Cartridges (MC562w only):		
Cyan Toner Cartridge	5,000 pg. ⁴	44469721
Magenta Toner Cartridge	5,000 pg. ⁴	44469720
Yellow Toner Cartridge	5,000 pg. ⁴	44469719
Black Toner Cartridge	5,000 pg. ⁴	44469802
Image Drum Kit:		
Single Image Drum (CMYK)	20,000 pg. ⁵	44494201
OKIcare® On-Site Warranties ³		
MC362w	U.S.	Canada
3-Year On-Site Warranty	38035603	38035613
MC562w		
3-Year On-Site Warranty	38035703	38035713

Warranty

- **System:** 3-Year Carry-In/Depot limited warranty³
- **Digital LED Printheads:** 5-Year limited warranty

For more information on Digital Color MFPs and supplies from OKI, including OKIcare® warranties: **1.800.OKI.DATA (800.654.3282)**³

¹ Published performance results based on laboratory testing of simplex sheet (1 side). Individual results may vary.

² Based on ITU-T Test Chart #1.

³ Available in the U.S. and Canada only.

⁴ Based on ISO 19798. MC362w ships with full set of 1,000-page and MC562w ships with 2,000-page toner cartridges (CMYK)

⁵ Estimated life, based on 3 pages per job.

Specifications are subject to change without notice.

©2013 OKI Data Americas, Inc. OKI Reg. T.M., M.D., OKI Electric Industry Co., Ltd. SynFlex T.M., OKI Data Americas, Inc. PCL Reg. T.M., Hewlett Packard Co. PostScript Reg. T.M., PostScript 3 T.M., Adobe Systems, Inc. Windows, Vista Reg. T.M., Microsoft Corp. Mac, iPad, iPhone Reg. T.M., AirPrint T.M., Apple, Inc. Android T.M., Google. BlackBerry Reg. T.M., Research In Motion. Nuance, PaperPort, OmniPage Reg. T.M., Nuance Communications, Inc. Wi-Fi Reg. T.M., Wi-Fi CERTIFIED, Wi-Fi Protected Setup, WPA, WPA2 T.M., Wi-Fi Alliance. ENERGY STAR Reg. T.M., U.S. EPA.



OKI DATA AMERICAS, INC.

USA
2000 BISHOPS GATE BLVD.
MOUNT LAUREL, NJ 08054-4620
TEL: 800.OKI.DATA (800.654.3282)
FAX: 856.222.5320

CANADA
4140B SLADEVIEW CRESCENT
UNITS 7 & 8
MISSISSAUGA, ONTARIO L5L 6A1
TEL: 905.608.5000
FAX: 905.608.5040

LATIN AMÉRICA
2000 BISHOPS GATE BLVD.
MOUNT LAUREL, NJ 08054-4620
TEL: 856.231.0002
FAX: 856.222.5071

OKI DATA DE MÉXICO, S.A. DE C.V.
MARIANO ESCOBEDO, 748 8º PISO
COL. NUEVA ANZURES C.P. 11590
MÉXICO, D.F.
TEL: 55.5263.8780
FAX: 55.5250.3501

OKI DATA DO BRASIL INFORMÁTICA LTDA.
AV. ALFREDO EGÍDIO DE SOUZA ARANHA, 100
BLOCO C – 4º ANDAR
04726-170 – SÃO PAULO – SP – BRASIL
TEL: 11.3444.3500
FAX: 11.3444.3502

WWW.OKIDATA.COM