

Ethernet WiFi Router

4 Ethernet Ports | Wireless-N | 300Mbps

WR-5882

Wireless-N Broadband Router



The Comtrend WR-5882 Wireless-N Broadband Router is designed for home and small office environments that require wired and/or wireless connectivity. Utilizing advanced MIMO technology, the IEEE802.11n standard provides great coverage, up to 300Mbps wireless speeds, and is backward compatible with IEEE802.11b/g devices. Additionally, Wi-Fi Protected Setup (WPS) enables instant security and device pairing by pressing the WPS button on both router and client device.

Router FEATURES

- Supports IPv6
- NAT/NAPT IP Sharing
- PPPoE/PPTP/Static IP/DHCP/L2TP/
- DHCP server to assign IP address automatically
- DMZ/Virtual Server/Port Forwarding
- Supports Special Applications (Port Trigger)
- Supports DDNS (DynDNS, TZO)
- VPN Pass Through (IPSec/L2TP/PPTP)
- Anti-DoS Firewall, QoS, IP/MAC/URL Filtering
- Web-based configuration and Firmware Upgrade

WR-5882

4 Ethernet Ports | Wireless-N | 300Mbps



Wireless Features

- Complies with IEEE 802.11b/g/n standards
- Support high data rate up to 300Mbps while connecting with IEEE 802.11n devices
- Supports Green WLAN for smart transmit power saving, Implicit receive power saving and CPU offload
- Support WMM function to enhance multi-media data transmitting and receiving performance
- Support 64/128-bit WEP, WPA, WPA2 and IEEE 802.1x wireless securities
- Support WPS hardware button for easy wireless association

Product appearance and specifications may change without notice.

Specifications

WAN Port

- 10/100M UTP Port x 1 (Auto MDI/MDI-X)

LAN Port

- 10/100M UTP Port x 4 (Auto MDI/MDI-X)

Frequency Band

- 2.4000~2.4835GHz (Industrial Scientific Medical Band)

Data Rate

- 11b: 1/2/5.5/11Mbps
- 11g: 6/9/12/24/36/48/54Mbps
- 11n (20MHz): MCS 0-7, up to 72Mbps
- 11n (40MHz): MCS 0-7, up to 150Mbps
- 11n (20MHz): MCS 8-15, up to 144Mbps
- 11n (40MHz): MCS 8-15, up to 300Mbps

Certifications

- FCC, Wi-Fi Certified

Output Power

- 11n: 12±1.5dBm, 11g: 12±1.5dBm, 11b: 16±1.5dBm

Antenna

- 2 dBi Dipole Fixed Antenna x 2

Power Module

- 5VDC, 1A Switching Power Adapter

Dimension

- 30(H) x 157(W) x 127(D) mm

Temperature

- Operating: 32~104°F (0~40°C)
- Storage: -4~140°F (-20~60°C)

Humidity

- Operating: 10~90% (NonCondensing)
- Storage: Max. 95% (NonCondensing)



COMTREND CORPORATION

Taiwan:

3F-1, No. 10, Lane 609, Chung Hsin Road
Section 5, San Chung Dist., New Taipei City,
Taiwan 24159
Tel: 886-2-2999-8261
Fax: 886-2-2999-8497

China:

NO. 88 East QianJin Road, Kunshan
City, JiangSu, China
Tel: 86-512-57383156, 86-512-57383157,
86-512-57384515
Fax: 86-512-57383155

Spain:

Edif. América II C/Prócion, 7 portal 3 bajo H
28023 Madrid, Spain
Tel: 34-917990403
Fax: 34-913510999

France:

87, Rue du Gouverneur Général Félix Eboué
92130 Issy-les-Moulineaux, France
Tel: 33-1-70715700
Fax: 33-1-70715701

USA & Canada:

16 Goodyear, Suite 120, Irvine, CA 92618, USA
Tel: 1-949-753-9640
Fax: 1-949-753-9020

Brazil:

Al. Campinas, 977 - 7º. Floor - Room 71 / 72 -
Jardins
Zip Code: 01404-001 - São Paulo - SP - Brazil
Tel: 00 55 11 3052-2295
Fax: 00 55 11 3052-2295

