



Swann
Advanced Security Made Easy™

◀ NEW
WIDESCREEN
960H
DVD-QUALITY

PRO-SERIES

960H

4
CHANNELS



Professional Security System

DVR4-4200 4 Channel 960H Digital Video Recorder

Cutting-edge protection for your home or business 24/7

- Swann's TruBlue™ blue-lit 960H DVR with real time, widescreen high resolution live video viewing & playback, perfect for 16:9 monitors
- Just add cameras to view & record 4 video streams simultaneously
- Set & forget by recording continuously from 4 channels for 30 days+ onto a 500GB hard drive, even longer with motion detection for extra capacity connect external hard drive to eSATA port
- Save time & have peace of mind by easily locating incident video, then transfer to external storage via USB or network
- View live or playback in high resolution on your HDTV, LCD or plasma TV using HDMI connection or on LCD screen via VGA port
- Setting up remote viewing has never been easier with Swann's 'My DVR' customizable network configuration & DDNS service
- Surveillance in the palm of your hand with live viewing on 3G/4G-enabled Smartphone & tablets including, iPhone, iPad, Android devices, BlackBerry devices and more* using the free SwannView app

960H
DVD-QUALITY

REAL TIME, WIDE SCREEN
HIGH RES RECORDING

HDMI
HDTV VIEWING

CONNECT TO HDTV, LCD & PLASMA TVs

DIY
EASY INSTALLATION

EASY DO-IT-YOURSELF INSTALLATION
WITH CABLES & CONNECTORS INCLUDED

500GB
30 DAYS RECORDING+

30 DAYS+ CONTINUOUS RECORDING
TO 500GB HDD

USB
EASY BACKUP

EASILY BACKUP INCIDENT VIDEO
TO USB OR NETWORK

Professional Security System

DVR4-4200™ 4 Channel 960H Digital Video Recorder

What's in the box

All installation accessories included

- DVR4-4200™
- 500GB HDD (installed)
- HDMI Cable
- Ethernet Cable
- Mouse
- Remote Control
- Software CD
- Power Adapter
- Operating Instructions
- Theft Deterrent Stickers x 4



Specifications

DVR4-4200™ Digital Video Recorder

Video

Video Signal Type NTSC or PAL
Video Inputs 960H 4 Channels BNC
Video Outputs VGA and HDMI Output
Display Resolution Up to 1080p
Display Frame Rate NTSC: 30fps per channel /
PAL: 25fps per channel

Audio

Audio Input 4 RCA Inputs
Audio Output 1 RCA Output

Recording

Compression Format H.264
Recording Resolution NTSC: 960H [960 x 480]
PAL: 960H [960 x 576]
Recording Frame Rate Real Time: NTSC: Global 120fps / 30fps per Channel /
PAL: Global 100fps / 25fps per Channel
Recording Modes Manual / Motion / Schedule
HDD Interface / Type 500GB SATA2 HDD (installed)
Hard Drive Support Up to 2TB SATA2 HDD

Network

LAN Connection One RJ45 Port
Network Protocol TCP/IP, PPPoE, DHCP, DNS, DDNS, NTP
Dynamic DNS Yes (swannvr.net, DYNDNS)
Remote Operation IE, MyDVR, CMS, SwannView
Operating Power DC 12V
Dimensions 10.23" x 8.46" x 1.97" / 260mm x 215mm x 50mm
Weight 3.1lbs / 1.4kg
Backup Method External storage via USB or network
Mouse Support Yes
Remote Control Yes (uses 2 x AAA batteries, included)

Code

Swann Code SWDVR-44200H

Stream Live Video Footage From Anywhere In The World

One of the great features of this product is its remote viewing capabilities. You can view your home or business from anywhere in the world via broadband Internet connection on computer (PC or Mac) or on your Smartphone* via the SwannView app.

Free Download SwannView App



COMPATIBLE WITH



Android®
Devices



Works with
iPhone



iPad

* Monitor and mobile phones not included

* Requires broadband internet & 3G/4G Smartphone



Installation is easy

Do-it-Yourself

Installing this Swann product is simple. For instructions, tips and videos see the operating instructions in this pack or visit www.swann.com

Professional Installation

Need extra help?

We have an installer in your region!

For more visit www.swann.com

Our Promise

Swann stands by its promise of Lifetime Support to make advanced security easy to use, install and maintain. Everything is in the pack but if you need it Swann's help desk is available **24 hours a day, 7 days a week** for the life of the product.



For more information on this product visit

www.swann.com