



# CPUAC1U1300 UNIVERSAL POWER ADAPTER



Your replacement or spare AC adapter for portable electronic equipment.

The CyberPower 1300mA CPUAC1U1300 Universal Power Adapter functions as a replacement AC adapter designed for devices requiring a round-pin connector or USB connection (not for use with laptops) such as portable radios, smartphones, electronic gaming systems, and home office equipment. Features include a folding AC plug, voltage selector, power cord (5 ft.), and a set of seven adapter tips compatible with many electronics. The CPUAC1U1300 comes with a one-year limited warranty.

## TYPICAL APPLICATIONS

- Audio Video
- Handheld Gaming Devices
- Laptop Computers

## FEATURES

- Charge type: AC
- Output: 1300mA (3-12 volts)
- USB charge port: 1
- USB output: 2.1 Amp
- Folding AC plug: Yes
- Power cord: 5-f.t
- Adapter tips: 7
- Dual polarity: Yes
- Voltage selector: Yes
- Overload: Protected
- Warranty: One-Year

## SPECIFICATIONS

INPUT		OUTPUT - CONT.	
Cord Length	5 ft. (1.5 m)	Output Voltage (Selectable)	3 VDC, 4.5 VDC, 5 VDC, 6 VDC, 7.5 VDC, 9 VDC, 12 VDC
Input Connector	AC Plug	USB Charge Port Amperage	2.1 Amps
Input Plug Type	NEMA 1-15P	USB Charge Port Quantity	1 x Type A
Input Voltage Range	100 - 120 VAC	USB Charge Port Voltage	5 VDC
Plug Style	Folding	PHYSICAL	
OUTPUT		Color	Black
Adapter Tips (Qty.)	7	Form Factor	Compact
Output Cord Length	5 ft.	Material of Construction	Plastic
Output Power	1300 mA		

# CPUAC1U1300

## UNIVERSAL POWER ADAPTER

### SPECIFICATIONS

PHYSICAL DIMENSIONS		ENVIRONMENTAL	
Physical Dimensions - Width/Height/Depth (cm)	5.84 x 9.4 x 3.3 cm	Operating Elevation	0 - 10,000 ft (0 - 3,048 m)
Physical Dimensions - Width/Height/Depth (mm)	58 x 94 x 33 mm	Operating Relative Humidity	0 - 95 % (non-condensing)
Physical Dimensions - Width/Height/Depth (in.)	2.3 x 3.7 x 1.3 in.	Operating Temperature	32 - 95 °F (0 - 35 °C)
Weight (kg)	0.11 kg	Storage Elevation	0 - 50,000 ft (0 - 15,239 m)
Weight (lb)	0.24 lbs.	Storage Temperature	5 - 113 °F (-15 - 45 °C)
SHIPPING DIMENSIONS		CERTIFICATIONS	
Shipping Dimensions - Width/Height/Depth (cm)	10.48 x 18.42 x 5.08 cm	Environmental	RoHS Compliant
Shipping Dimensions - Width/Height/Depth (mm)	104.78 x 184.15 x 50.8 mm	WARRANTY	
Shipping Dimensions - Width/Height/Depth (in.)	4.125 x 7.25 x 2 in.	Product Warranty	1-Year Limited Warranty
Weight (kg)	0.18 kg		
Weight (lb)	0.4 lbs.		