

20" Enclosure with Knockouts (no cover)

EN2085



The EN2085 series enclosures include five knockouts on the top of the enclosure. They are also vertically stackable to allow cable passthrough between any two ENxx85 enclosures. For Fiber to the Home (FTTH) applications, it will fit ONTs of 3.6" depth or less.

features & benefits

- Includes five openings on the top of the enclosure with knockouts
- Stackable design allows for connection of two systems
- Cover not included
- In FTTH applications, it fits ONTs of 3.6" depth or less. In 28" and 42" enclosures, 2.5" can be added to depth with enclosure extender
- UL listed
- Made in the USA

specifications

General Info

Color: Glossy White
finish: Powder Coat
Type: Enclosure

Listing Agencies/Third Party Information

cULus: Yes
UN SPS C: 43223306

Construction Information

Installation Location: In-Wall

Dimensions

Depth Metric: 9.4 cm
Depth U S: 3.7"
Height Metric: 51.1 cm
Height U S: 20.1"
Thickness U S: 20 Gauge
Width Metric: 36.3 cm
Width U S: 14.3 in

Technical Information

Humidity: 90% Relative Humidity (Non-Condensing)
Material: CRS
Mounting: Surface or Flush
Operating Temperature Celsius: 0°C to 50°C
Operating Temperature Fahrenheit: 32°F to 122°F