

Cat 5e 48-Port Rack Mount Patch Panel

48845C5E



This 48 port universal 568A/B Category 5e rack mount patch panel takes up a single rack space (1U). The patch panel performance exceeds the TIA Category 5e Patch Panel Standards. It supports data rates up to 10 Gigabits. It offers many cable management features such as rear cable management bar, cable ties for strain relief, and front facing labels.

features & benefits

- Supports 48 network connections up to 10 Gigabit Ethernet speeds.
- Included Cable Management bar secures rear cables and provide strain relief.
- Exceeds the TIA/EIA-568 standard for connecting hardware.

specifications

General Info

Cable Type: Cat 5e
Color: Black
Mod Jack Wiring: T568A/B Universal Wiring
Type: Rackmount Patch Panel
Input Plug Type: RJ45 Male

Listing Agencies/Third Party Information

cULus: Yes
FCC Standard: Yes
Fed Spec Number: FCC Part 68
UN SPS C: 43223309

Dimensions

Depth Metric: 8 cm

Depth U S: 3"

Height Metric: 8.89 cm

Height U S: 3.5"

Width Metric: 48 cm

Width U S: 19 in

Technical Information

Material: Plastic and Steel

Mounting: Rack

Performance Rating: High-performance panel

Product Fits Into: 19-inch rack

Receptacle Type: RJ45 Female, 8P8C

Number Of Receptacles: 48