

UD9 Series



PROFILE

Integrated into a 21.5" widescreen, the UD9 series support a wide range of applications and provides numerous interfaces and integrated features such as touchscreen, WLAN and a smartcard reader.

FEATURES AND BENEFITS

- ▶ **Wide 21.5" LCD monitor (55 cm)**
Increased user comfort and productivity
- ▶ **Thin client integrated into a modern monitor**
Small footprint and attractive design
- ▶ **Touchscreen display (optional)**
Use without keyboard and mouse, e.g., as a kiosk or PoS

- ▶ **Integrated WLAN module (optional)**
Use of the latest wireless standard enables optimal connectivity even without wired network infrastructure
- ▶ **Integrated smartcard reader (optional)**
Excellent for highly secure two-factor authentication, shared desktops or roaming users
- ▶ **Free evaluation:**
www.igel.com/evaluation



DEVICES

UD9 LX
UD9 LX Touch

UD9 W7
UD9 W7 Touch



Touchscreen



Display rotating by 90°



Smartcard reader



Connectivity options

- Parallel port
- Serial port
- Mic-in, Stereo-out, Headset
- 5xUSB 2.0
- RJ45 Ethernet
- VGA port
- Serial port
- 2xPS/2 keyboard/mouse
- Power

SYSTEM

Available Operating Systems	IGEL Linux v5 (LX) Microsoft Windows Embedded Standard 7 (W7)
Management	IGEL Universal Management Suite included
Form Factor	Integrated
Processor	Intel Atom N270 1.6 GHz
Chipset	Intel 945 GSE

MEMORY

RAM	1 GB (LX), 2 GB (W7)
Flash Memory	2 GB (LX), 4 GB (W7)

GRAPHICS

Chipset	Intel GMA 950
Video Memory	32–128 MB shared memory
Ports	1 x VGA-out
Supported Resolutions	Dualview: 1920 x 1080

NETWORK

Ethernet	10/100/1000 Base-T
WLAN	Optional, 802.11 b/g/n

AUDIO

Chipset	HD Audio compatible
Ports	1 x line-out, 1 x line-in, 1 x mic-in
Speakers	2 x internal

PERIPHERAL INTERFACES

PS/2	2 x
Serial	2 x
Parallel	1 x
USB 2.0	5 x
Kensington Lock	1 x back

DIMENSIONS

Device (DxWxH), upright	237 x 514 x 364 mm
Packaging (DxWxH), horizontal	650 x 335 x 465 mm
Weight	9.32 kg

ENVIRONMENT

Cooling	Fanless convection
Operating Temperature	0° to 40°C
Operating Humidity	20% – 80%, non-condensing

POWER

Input	Auto sensing 100~240VAC / 50~60 Hz
Power Supply	External
Power Consumption: Idle / Sleep Mode	38W / 2W

OPTIONS

Integrated Smartcard Reader	For secure smartcard-based authentication
Integrated WLAN Module	For environments with no physical network infrastructure
Touchscreen Display	For public facing or space-constraint environments
USB-to-Serial Adapter	For connecting peripherals that require a serial port
USB-to-Parallel Adapter	For connecting printers that require a parallel port
Shared WorkPlace	It allows user-dependent configuration based on setting profiles
Multimedia Codec Pack (UD Linux)	Required for multimedia re-direction and full multimedia functionality

After purchase, just register with us online, and all your IGEL thin clients UD2, UD3, and UD5 will be upgraded from a standard 2-year to a 5-year hardware warranty, according to our end customer hardware warranty declaration, at no additional cost. The UD9, UD10, IZ1, IZ2 and IZ3 series will be upgraded to a 3-year hardware warranty. The warranty upgrade does not cover any additional hardware options. IGEL is a registered trademark of IGEL Technology GmbH. All hardware and software names are registered trademarks of the respective manufacturers. Errors and omissions excepted.

©2009/2013 IGEL Technology | 85-EN-4-4 | WEEE-Reg.-Nr. DE 79295479

IGEL Technology Ltd | info@igel.com | www.igel.co.uk | www.igel.com/en

GERMANY Augsburg Bremen	AUSTRALIA Sydney	AUSTRIA Vienna	BELGIUM Leuven	CHINA Hong Kong Beijing Shanghai	FRANCE Paris	THE NETHERLANDS Utrecht	SINGAPORE Singapore	SWEDEN Sundsvall	SWITZERLAND Zurich	UNITED KINGDOM Reading	UNITED STATES Cincinnati
-------------------------------	---------------------	-------------------	-------------------	---	-----------------	----------------------------	------------------------	---------------------	-----------------------	---------------------------	-----------------------------

info@igel.com
www.igel.com

