



e2060Swda

49.5cm (19.5") LED MONITOR

Line:

Line:	Professional
Paneltype:	WLED
Monitor Size:	19.5"
Visible Screen Size:	49.5cm
Screen Format:	16:9
Brightness:	250 (typ) cd/m ²
Contrast Ratio Dynamic:	20.000.000:1 (DCR)
Contrast Ratio Typical:	1.000:1
Pixel / Dot / Pitch:	0.27 (H) x 0.27 (V)
Display Area:	432 (H) x 239.8 (V)
Viewing Angle:	170°/ 160 (CR 10)
Response Time:	5 ms

Scanning Frequency:

Scanning Frequency:	H: 30-83 KHz / V: 55-75 Hz
Pixel Frequency:	148.5 MHz

Resolution:

Maximum Resolution:	1600 x 900@60 Hz
Recommend Resolution:	1600 x 900@60 Hz
Colors:	16.7 M
HDCP compatible:	Yes

Signal Input:


Analogue Input: D-Sub:	Yes
Digital Input: DVI-D / HDMI:	Yes / No
Composite CVBS Input:	No
Component CVBS Input:	No
S-Video Input:	No
Component Input:	No
SCART:	No
CI Card:	No
Display Port Input:	No

Connectors:

D-Sub 15 pin:	Yes
DVI-D 24-pin:	Yes
HDMI:	No
Display Port Input:	No

Power:

Power Source:	90~240 VAC, 50/60 Hz
Power Consumption:	On: 26W, Standby: 0.3W, Off: 0.2W





e2060Swda

49.5cm (19.5") LED MONITOR

Tuner System:

-

Other Features:

User Control:	Button
Speaker:	Yes
Wallmount:	Yes
Height adjustment:	No
Pivot:	No
Swivel:	No

Regulations:	cCSAus CE EPEAT Gold Energy Star 5.0 EuP FCC GOST ISO 9241-307 RoHS TCO 6.0 TÜV-GS Win7
--------------	--

Other Features:	-5°~+15° Tilt Eco Mode e-Saver i-Menu Screen+ Kensington Security Lock VESA 100 mm DCR
-----------------	---

Accessories:

Accessories:	Power cable D-Sub cable DVI-D cable Audio cable Driver CD Warranty Card
--------------	--

Dimensions:

Dimensions (WxHxD):	477 × 358 × 185 mm
Weight:	3,79 Kg / 2,75 Kg
Warranty:	3 Years
EAN:	4038986101875

