


DS-2AF5268N-A(3)

700TVL PTZ Dome Analog Camera



DS-2AE5268N-A


DS-2AE5268N-A3



Key features

- 1/4" Sony CCD
- 700TVL horizontal resolution
- 36X / 23X optical zoom, 16X digital zoom
- True Day/Night, 3D DNR, Digital WDR
- 3D intelligent positioning

Dimensions



Accessories



	DS-2AF5268N-A	DS-2AF5268N-A3
Camera		
Image Sensor	1/4" Sony CCD	
Effective Pixel	768(H)×494(V)	
Horizontal Resolution	Color: 540 TVL, B/W: 600 TVL	
Min.Illumination	Color: 0.1Lux@(F1.6,AGC on), B/W: 0.01Lux@(F1.6,AGC on)	
White Balance	Auto / Manual / ATW	
AGC	Auto / Manual	
S / N Ratio	≥ 50dB	
Shutter Speed	1 ~1/10,000s	
Digital Noise Reduction	3D DNR	
Wide Dynamic Range	128X Digital WDR	
Day & Night	IR Cut Filter	
Digital Zoom	16X	
Privacy Masking	Up to 8 zones, maximum 8 zones on a same image, multiple colors and mosaics optional	
Focus Model	Auto / Semiautomatic / Manual	
Lens		
Focal Length	3.3 ~119mm, 36X	
Zoom Speed	Approx.6 s(Optical Wide-Tele)	
Angle of View	57.1~1.7 degree(Wide-Tele)	
Min. Working Distance	10 ~1000mm (Wide-Tele)	
Aperture	F1.4 ~ F3.7	
Pan and Tilt		
Pan and Tilt Range	Pan: 360° endless; Tilt: -5° ~90° (Auto Flip)	
Pan and Tilt Speed	Pan Manual Speed: 0.1° ~250° /s, Pan Preset Speed: 300° /s Tilt Manual Speed: 0.1° ~150° /s, Tilt Preset Speed: 200° /s	
Proportional Zoom	Rotation speed can be adjusted automatically according to zoom multiples	
Number of Preset	255	
Patrol	8 patrols, up to 32 presets per patrol	
Pattern	4 patterns, with the total recording time not less than 10 minutes	
Power-off Memory	Support	
Park Action	Preset / Patrol / Pattern / Pan scan / Tilt scan / Frame Scan / Random scan / Panorama scan	
PTZ Position Display	On / Off	
Compass	Support , the north can be set	
Scheduled Task	Preset / Patrol / Pattern / Pan scan / Tilt scan / Frame Scan / Random scan / Panorama scan / Day / Night	
Input/ Output		
Video Output	1.0 V[p-p] / 75Ω, PAL / NTSC composite, BNC	
General		
RS-485 Protocols	HIKVISION, Pelco-P, Pelco-D, self-adaptive	
Power	24VAC Outdoor dome: Max. 20W / 12W (Heater On / Off)	24VAC Indoor Ceiling: Max. 20W
Working Temperature	Outdoor dome: -30° C ~ 65° C(-22° F ~ 149° F)	
Humidity	90% or less	
Protection Level	IP66 standard (outdoor dome) TVS 4,000V lightning protection, surge protection and voltage transient protection	
Dimensions	Φ220 × 305mm (Φ8.66" × 12.00")(Outdoor)	
Weight (approx.)	5Kg (11.02lbs)	
Mount Option(for outdoor models)	Long-arm wall mount: DS-1601ZJ; Corner mount: DS-1633ZJ; Pole Mount: DS-1622ZJ; Power box mount:DS-1634ZJ	

Order models

DS-2AF5268N-A, DS-2AF5268N-A3