

Konftel 300Wx

Absolute freedom



The Konftel 300Wx wireless conference phone allows you to hold meetings wherever is convenient for you – without worrying about network and power outlets. The wireless DECT technology is both reliable and secure. Choose a base station to suit your company's telephony environment, IP or analog, or connect to an installed DECT system.

The rechargeable battery ensures more than 60 hours of call time, so you can talk for a full working week without recharging!

The Konftel 300Wx handles both conference calls by phone and PC-based collaboration systems such as Microsoft Teams, Cisco Webex and Zoom. It has a USB connection to your laptop while at the same time supporting wireless telephony, so all you need is a single speakerphone in the meeting room. This is the strength of Hybrid Conferencing.

OmniSound®      

- Room type: Small to Medium
- Wireless DECT
- Base station: IP, analog or GAP
- Battery with 60 hours of call time
- Hybrid: combine meeting app with phone calls
- Expandable with additional microphonesSupport for Konftel Unite via adapter
- Two-year warranty
- Climate Neutral certified

Choose between IP and analog. Always wireless.



KONFTEL 300Wx

The Konftel 300Wx without a base station is perfect if you have an installed third-party DECT/GAP base or system to register the telephone with. It is also ideal if you want to add additional conference phones to an existing base station from Konftel, IP or analog.

Item number: 910101078 / 840101078 (US)



KONFTEL 300Wx IP

Teaming the Konftel 300Wx with the Konftel IP DECT 10 is one of our most popular solutions. Now it is available as a single package, delivering wireless conference calls in HD quality via your IP telephony system (SIP). Each IP DECT base can handle up to 20 registered Konftel 300Wx devices and five ongoing calls.

Item number: 951101078 / 854101078 (US)



KONFTEL 300Wx ANALOG

Simple and reliable. Konftel 300Wx with Konftel DECT Base for analog connection. Simply plug the base station into the phone jack and your wireless conference solution is ready to go, with up to seven phones connected.

Item number: 910101077 / 840101077 (US)

Specifications Konftel 300Wx

GENERAL

Product name: Konftel 300Wx

Item no.: 910101078 / 840101078 (US) (without base station)

Contents (all packages): Konftel 300Wx, battery (900102095), Konftel charging cradle (900102094), USB cable (900103388), power cable (900103401), AC adapter (900102125)

Product name: Konftel 300Wx IP

Item no.: 9510101078 / 854101078 (US)

Contents: Konftel 300Wx (see contents above), Konftel IP DECT 10 (900102132), AC adapter (EU/UK/US)

Product name: Konftel 300Wx Analog

Item no.: 910101077 / 840101077 (US)

Contents: Konftel 300Wx (see contents above), Konftel DECT Base, AC adapter plus accompanying cable (180 cm). Screws for mounting to wall.

Warranty: 2 years (battery 1 year).

Size: Konftel 300Wx: Diameter 240 mm, height 77 mm
Konftel charging cradle: 180x165 mm.

Weight: Konftel 300Wx: 1 kg. Konftel charging cradle: 220 g.

Anti-theft protection: Kensington® security slot.

CALL FEATURES

During calls: Put calls on hold. Call waiting. Park/retrieve calls (if supported by PBX). Move incoming calls. Request. Music on hold. Dial plan.

Multi-party calls: Support for multi-party calls if the feature is available on the network or company PBX.

POWER SUPPLY

Battery: 5200 mAh, up to 60 hours of call time/270 hours standby.

AC adapter: 100-240 V AC/14 V DC

Konftel charging cradle: Yes

CONNECTIVITY

Wireless DECT: Version 6.0, GAP/CAT-Iq compatible, range of up to 200 m in open areas and up to 50 m indoors. A phone can be registered with 4 DECT base stations.

USB: 2.0 Mini B.

Mobile cable connection: RJ11. Use a mobile phone cable that fits your phone (see accessories).

AUDIO EXPANSION

Expansion microphones: 2 x modular 4/4.

AUDIO SPECIFICATIONS

Technology: OmniSound® with support for HD audio, full duplex, automatic echo cancellation and noise suppression.

Microphone: Omnidirectional 360°.

Reception area: Up to 12 people (30 m²). With expansion microphones, up to 20 people (70 m²).

Frequency: 2G 200–3300 Hz, 3G 200–7000 Hz, USB 200–7000 Hz.


ADDITIONAL FEATURES

Bridging connections/calls: DECT + cell + USB.

Recording: On a memory card. Support for SD/SDHC (≤32 GB).

Software updates: The Konftel upgrade utility (for Microsoft Windows) updates the software via USB. It is also possible to update via an SD card.

VERIFIED FOR



Specifications Konftel IP DECT 10

GENERAL

Product name: Konftel IP DECT 10

Item number: 900102132 / 840102132 (US)

Contents: Konftel IP DECT 10, EU/UK/US power adapter.

Warranty: 2 years.

Size: 118 × 177 × 32 mm (H × W × D)

Weight: 240 grams.

POWER SUPPLY

AC adapter: 100-240 V AC/5V DC.

CONNECTIVITY

SIP: RJ 45. Interface for IP network: 10/100 BASE-T IEEE802.3.

NETWORK AND COMMUNICATION

Network addressing: DHCP-alternative 66 and adapted.

AUDIO SPECIFICATIONS

Codecs: 5 audio channels via use of G.726/G711 codec.

Specifications Konftel DECT base

GENERAL

Product name: Konftel DECT base (analog).

Item number: 900102128 / 840101028 (US)

Contents: Konftel DECT base, transformer, power cable (180 cm) and screws.

Warranty: 2 years.

Size: 160 × 175 × 40 mm (H × W × D)

Weight: 240 grams.

POWER SUPPLY

AC adapter: 100-240 V AC/5 V DC.

CONNECTIVITY

Analog: Analogue PBX or PSTN, RJ-11.

View full technical specifications at konftel.com

RETAILER SPACE

© Konftel AB. In line with our policy for continuous product development, we reserve the right to change the product specifications. Visit www.konftel.com for the latest information.

Konftel is a leading company within collaboration endpoint solutions. Since 1988, our mission has been to help people in businesses around the world to have meetings regardless of distance. We know that remote collaboration is an effective way to save time, money and contribute to a more sustainable world. We are Climate Neutral Certified, offering customers an option to purchase conferencing equipment while keeping a clear climate conscience. Crystal clear audio and a sharp video image are essential for efficient meetings; this is why we only focus on cutting-edge technology in our Collaboration Solutions. Our audio technology OmniSound® is built into all Konftel Conference phones and devices. The products are sold globally under the Konftel brand and our headquarters are based in Sweden. Read more about the company and our products at konftel.com.