



## Isobar 10-Outlet Home/Business Theater Surge Protector, 8 ft. Cord with Right-Angle Plug, 3840 Joules, LEDs, Metal Housing

MODEL NUMBER: HT10DBS



Premium protection for A/V home or business theater components, including HDTVs and stereo receivers, against dangerous power surges, spikes and line noise. Recommended for medium-to-large home and business theater installations.

### Features

**Network-Grade 3840-Joule Surge Protection for Your Home or Business Theater**Protects your A/V components against even the strongest surges and spikesFull normal mode (H-N) and common mode (N-G/H-G) line surge suppressionExceeds IEEE 587 Category A and B surge suppression specifications

**10 Outlets Accept Wide Range of Electronic Devices**10 NEMA 5-15R AC outlets accept most home theater equipment4 widely spaced outlets accommodate bulky transformers without blocking other outletsIncluded safety covers block accidental contact with unused outletsColor-coded labels make it easy to coordinate outlets with equipment cords

**Isolated Filter Banks Provide Extra Protection**Outlets arranged in 2 exclusive isolated filter banks to limit noise interaction among connected equipmentBlock disruptive EMI/RFI line noise up to 60 dB that can cause equipment damage or data lossCombine large toroidal chokes, ferrite rod-core inductors, HF/VHF capacitors and metal oxide varistors to block interference

**Protects Coaxial/Telephone/Modem/Ethernet Connections From Surges**3-line 2.2 GHz gold coaxial protection1-line telephone/modem protection1-line high-speed 10/100 Mbps Ethernet protection

**Premium Safety Features**Lighted on/off switch provides one-touch control over connected equipmentAutomatic shutoff permanently cuts power to outlets if protection circuit is incapacitated, preventing equipment damage and indicating replacement is requiredDiagnostic LEDs confirm power, protection and line fault status at a glanceConforms to current UL 1449 3rd Edition safety standards

**Fits Effortlessly Into Your Setup**8 ft. (2.4 m) AC power cord reaches nearby outletsSpace-saving right-angle NEMA 5-15P plug allows furniture and equipment to move flush against the wallKeyhole slots on bottom panel provide convenient wall or desk mounting optionsMetal housing designed for long life

**Backed by Tripp Lite's Ultimate Lifetime Insurance**\$500,000 Ultimate Lifetime Insurance covers any connected components damaged by power surge (U.S., Canada and Puerto Rico only)

### Highlights

- 10 NEMA 5-15R outlets in exclusive isolated filter banks
- Network-grade 3840-joule surge protection rating
- Coaxial/telephone/modem/Ethernet surge protection
- 12A resettable circuit breaker prevents dangerous overloads
- 8 ft. power cord with space-saving right-angle NEMA 5-15P plug

### Package Includes

- HT10DBS Isobar 10-Outlet Home/Business Theater Surge Protector, Metal Housing
- RJ11 telephone cable, 6 ft.
- RG59 coaxial cable, 6 ft.
- RJ45 Cat5 Ethernet cable, 6 ft.
- (4) Outlet safety covers
- Owner's manual

## Specifications

### OVERVIEW

UPC Code	037332121745
<b>INPUT</b>	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Input Cord Gauge Type	14 gauge; SJT
Voltage Compatibility (VAC)	120
Maximum Surge Amps	150000
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	8
Right-Angle Plug	Yes
Input Cord Length (m)	2.44
Integrated Cord Clip	No
<b>OUTPUT</b>	
Frequency Compatibility	50 / 60 Hz
Output (Watts)	1440
Output Receptacles	(10) 5-15R
Circuit Breaker (amps)	12
Transformer Accommodation	(6) Yes
Right-Angle Outlets	No
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
Diagnostic LED(s)	Yes
Switches	Combination AC circuit breaker and illuminated 2 position on/off power switch
Diagnostic LED Details	Built-in LEDs confirm line power, protection and ground status
<b>SURGE / NOISE SUPPRESSION</b>	
AC Suppression Joule Rating	3840
AC Suppression Response Time	NM = instantaneous CM = < 1 ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression
Clamping Voltage (RMS)	140
UL1449 Let Through Rating	330V - UL verified
EMI / RFI Filtering	Up to 60 dB
Isolated Filter Banks	2
Automatic Shut-Off	Yes

DATALINE SURGE SUPPRESSION	
Telephone/DSL Protection	Yes
Telephone/DSL Protection Details	1 line
Cable (Coax) Protection	Yes
Cable (Coax) Protection Details	3 line
Network (Ethernet) Protection	Yes
PHYSICAL	
Color	Black
Antimicrobial Coating	No
Color (AC Line Cord)	Black
Integrated Keyhole Mounting Slots	Yes
Keyhole Slot Mounting Measurement (Center to Center)	Distance between horizontal tabs = 355.09mm; Distance between vertical tabs = 58.17mm
Material of Construction	Metal
Outlets Measurement (Center to Center)	Distance between horizontal standard outlets = 39.45mm; Distance between horizontal transformer outlets = 53mm; Distance between vertical outlets = 38.76mm
Receptacle Color	Black
Shipping Dimensions (hwd / cm)	41.91 x 7.87 x 23.37
Shipping Dimensions (hwd / in.)	16.50 x 3.10 x 9.20
Shipping Weight (kg)	2.09
Shipping Weight (lbs.)	4.60
Unit Dimensions (hwd / cm)	36.2 x 2 x 5.7
Unit Dimensions (hwd / in.)	14.25 x 2.25 x 3.5
Unit Weight (kg)	1.59
Unit Weight (lbs.)	3.5
COMMUNICATIONS	
Network Speed	10/100 Mbps
SPECIAL FEATURES	
Rotatable Outlets	No
STANDARDS & COMPLIANCE	
Canada	Approved for Canada by ETL
Approvals	Exceeds IEEE 587 category A&B specifications
UL1449 3rd Edition (AC Suppression)	Tested to UL1449 3rd Edition requirements by ETL



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

UL497A (Communications)	UL497A
FCC Part 68 (Communications)	FCC Part 68
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$500,000 <a class="insuranceLink" href="//www.tripplite.com/support/insurance-policy">Ultimate Lifetime Insurance</a>

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>