

FUJITSU Document Scanner

# fi-7180 & fi-7280

High Performance Color  
Duplex Scanners

Fast, productive and reliable with advanced feeding

- Fast 80ppm / 160ipm at 300 dpi color
- Large Capacity 80 Page Feeder
- 2D Barcode Support
- Plastic and Embossed Credit Card Scanning
- Latest USB 3.0 Connectivity
- Eco-Friendly LED Scanning
- Interactive, Multi-Line LCD Panel
- Innovative Acoustic Paper Protection
- Automatic Image Cleanup with PaperStream IP Drivers (TWAIN & ISIS)
- Advanced PaperStream Capture Software
- Scanner Central Admin Software for Fleet Management



**FUJITSU**

# fi-7180 & fi-7280

Designed for heavy workloads and built to last, the Fujitsu fi-7180 and fi-7280 scanners offer exceptional return on investment (ROI) through increased scanning speeds and reduced operator intervention.


## Scanning Performance

With duplex scanning speeds of 160 images per minute at 300 dpi in Color, Grayscale, and Monochrome, the fi-7180 and fi-7280 protect your documents with acoustic sensors, ensure your data is captured with smart ultrasonic technology, and reduce rescans by cleaning up documents automatically in a single pass. Reliability is enhanced even further with new skew prevention technology for exceptional paper handling.

- Rapid power up time in less than 4 seconds.
- Hard and embossed credit card scanning up to 1.4mm thick
- Scan sticky notes, taped receipts, and labels while securing against multifeds
- Long document support up to 18.3 feet in PaperStream IP
- Latest USB 3.0 for forward compatibility
- 32/64 Bit Driver for PaperStream IP (TWAIN & ISIS)

## Fleet Management

Bundled with fi-7180 and fi-7280, the Scanner Central Admin provides IT departments an efficient way to manage medium to large scanner deployments. With remotely accessible fleet information, IT departments can now allocate resources effectively based on scan volume, consumable wear, depreciation schedules and maintenance expiration.



## Included with Scanner

Fujitsu fi-7180 and fi-7280 scanners have everything needed to integrate with thousands of software applications in the market or with PaperStream Capture, an advanced yet easy to use scanning application provided in the box.

- PaperStream IP Image Cleanup (TWAIN & ISIS)
- 2D Barcode Support
- PaperStream Capture batch scanning and PDF creation software
- One-year Advance Exchange Limited Warranty

## Accessories & Options

The following options are available for purchase:

- Training & Installation to get the most out of the equipment
- Advanced Exchange Warranties in multi-year bundles
- ScanAid Kit with consumables and cleaning supplies
- fi-7180 Post-Imprinter for backside endorsing
- Black Background for fi-7280 flatbed auto-cropping
- Carrier Sheet for double letter stitching

For full details on the Limited Warranty and other service programs, please go to [www.ImagingService.com](http://www.ImagingService.com) or call (800) 626-4686.



This scanner is designed to digitize materials that can be reproduced lawfully, in accordance with applicable copyright regulations and other laws. This product is a green product and Fujitsu promotes recycling for the scanner. Users are solely responsible for how they use this scanner. It is imperative that users comply with all applicable local rules and laws, including, without limitation, copyright laws when using this scanner.

**Fujitsu Computer Products of America, Inc.** 1250 East Arques Avenue Sunnyvale, CA 94085-4701  
(800) 626-4686 (408) 746-6000 • [info@cpa.fujitsu.com](mailto:info@cpa.fujitsu.com) • <http://us.fujitsu.com/fcpa>



Technical Specifications			
Models	fi-7180 (ADF only) / fi-7280 (ADF+Flatbed)		
Image Sensor Type	Color CCDs (Color Charge Coupled Device)		
Light Source	White LED Array		
Optical Resolution	600 dpi		
Output Resolution <sup>1</sup>	Color (24 bit)	50 to 600 dpi, 1200 dpi <sup>2</sup>	
	Grayscale (8 bit)		
	Monochrome		
Output Color Depth	Color: 24-bit; Grayscale: 8-bit; Monochrome: 1-bit		
Internal Video Processing	65536 levels (16-bit)		
Image Processing Function	Hardware	Deskew, cropping	
	Software	Multi-image, Blank page skip, i-DTC, Advanced-DTC, Simplified-DTC, sRGB, Auto color, Deskew cropping, Punch hole removal, Tab cropping, Upper lower separation, Error diffusion, Dither, Moire removal, Image Emphasis, Color cleanup, Dropout color (None, Specified, Color Saturation), Edge repair, Vertical Streaks Reduction	
Performance			
Scanning Speed (A4, Portrait) <sup>3</sup>	Color <sup>4</sup> , Grayscale <sup>4</sup> , Monochrome	ADF	Simplex: 80 ppm, Duplex: 160 ipm (200 dpi / 300 dpi)
		Flatbed (fi-7280)	(1.7 seconds (200 dpi))
ADF Capacity <sup>5</sup>	80 Sheets (Letter 20 lb. or A4: 80 g/m <sup>2</sup> )		
Document size	ADF minimum	2 x 2.13 in. (50.8 x 54 mm)	
	ADF maximum <sup>6</sup>	8.5 x 14 in. (216 x 355.6 mm)	
	Long document	8.5 x 220 in. (18.3') (210 x 5,588 mm) <sup>7</sup>	
	Flatbed (fi-7280)	8.5 x 11.69 in. (216 x 297 mm)	
ADF Feeding Paper Weight (Thickness)	Letter	7.2 to 110 lb. (27 to 413 g/m <sup>2</sup> )	
	A8 sheets	34 to 56 lb. (127 to 209 g/m <sup>2</sup> )	
	Card <sup>8</sup>	Up to 1.4 mm (portrait / landscape) <sup>9</sup>	
Interface	USB 3.0 (backward compatible)		
Physical Specifications			
Power requirements	100 to 240VAC ±10%		
Power consumption (Operating)	fi-7180	42 W or less (Sleep: 1.8 W; Standby: 0.35 W) <sup>10</sup>	
	fi-7280	43 W or less (Sleep: 1.8 W; Standby: 0.35 W) <sup>10</sup>	
Dimensions (WxDxH) <sup>11</sup>	fi-7180	11.8 x 6.7 x 6.4 in. (300 x 170 x 163 mm)	
	fi-7280	11.8 x 22.7 x 9.2 in. (300 x 577 x 234 mm)	
Weight	fi-7180	9.26 lb. (4.2 kg)	
	fi-7280	19.4 lb. (8.8 kg)	
Environmental compatibility <sup>12</sup>	ENERGY STAR® / RoHS / EPEAT Silver		
Operating Environment	Temperature	42° to 95° F (5° to 35° C)	
	Relative humidity	20% to 80% (non-condensing)	
Inbox Contents	ADF paper chute, AC cable, AC adapter, USB cable, Setup DVD-ROM, Getting Started Guide		
Bundled Software	PaperStream IP (TWAIN/ISIS) Driver, Software Operation Panel, Error Recovery Guide, PaperStream Capture, ScanSnap Manager for fi Series, Scan to Microsoft SharePoint, ABBYY FineReader for ScanSnap, Scanner Central Admin Agent		
Options	Post-scan Imprinter (fi-7180 only), Carrier Sheet, Black Document Pad (fi-7280 only)		
OS Support	Windows® 8 (32-bit/64-bit), Windows® 7 (32-bit/64-bit), Windows Vista® (32-bit/64-bit), Windows XP® (32-bit/64-bit), Windows Server® 2008 (32-bit/64-bit), Windows Server® 2012 (64-bit)		
Feed Detection Features	Ultrasonic Double Feed Detection Sensor, Acoustic Paper Protection Sensor, Intelligent Multi-Feed Function (Manual Bypass)		
Other Features	Embossed Card Scanning Capability, Long Document Scanning, Scanner Central Admin management, USB 3.0 Support, Acoustic Paper Protection, Automatic: Color Recognition, Paper-Size Detection, De-skew Correction, 2D Barcode Support		
Limited Warranty	One-year. Advance Exchange program also available; restrictions apply. For full details, visit <a href="http://www.ImagingService.com">www.ImagingService.com</a> or call (800) 626-4686.		
Service Options	Post-Warranty: Advance Exchange Plus; restrictions apply. Consumables: ScanAid™ kit. For full details, visit <a href="http://www.ImagingService.com">www.ImagingService.com</a> or call (800) 626-46866		
Part Number	fi-7180	PA03670-B005	
	fi-7280	PA03670-B505	

<sup>1</sup> Maximum output resolutions may vary, depending upon the size of the area being scanned and whether the scanner is scanning in simplex or duplex. <sup>2</sup> Scanning limitations brought about by scanning mode, document size and available memory may occur when scanning at high resolutions (600dpi or higher). <sup>3</sup> Actual scanning speeds are affected by data transmission and software processing times. <sup>4</sup> JPEG compressed figures. <sup>5</sup> Maximum capacity varies, depending upon paper weight. <sup>6</sup> Document sizes larger than A4, but not exceeding A3, can be scanned (single-side) using an optional carrier sheet. <sup>7</sup> The scanning of documents that exceed 34 inches in length will be limited to using PaperStream IP at 200 dpi or less. 300 dpi is 215 inches. <sup>8</sup> Supports ISO7810 embossed cards. <sup>9</sup> Capable of scanning up to 3 cards at a time. (Note: does not support multi-embossed card feeding.) Under 300 dpi 1.2 mm thickness. <sup>10</sup> fi-7180 only. <sup>11</sup> Excluding the ADF paper chute and stacker. <sup>12</sup> PFU Limited, a Fujitsu company, has determined that this product meets RoHS requirements (2002/95/EC).

©2013 Fujitsu Computer Products of America, Inc. All rights reserved. Fujitsu and the Fujitsu logo are registered trademarks of Fujitsu Limited. Microsoft, SharePoint, Windows and Vista are either registered trademarks or trademarks of Microsoft Corporation in the United States and/or other countries. ISIS is a registered trademark of Pixel Transitions, a division of Captiva Software Corporation. ABBYY, FineReader are trademarks of ABBYY Software House. As an ENERGY STAR® Partner, Fujitsu Ltd. has determined that this product meets the ENERGY STAR® guidelines for energy efficiency. ENERGY STAR® is a U.S. registered trademark. PaperStream is registered trademark of PFU LIMITED, Japan. All other trademarks are the property of their respective owners. All statements herein are valid only in the U.S. for U.S. residents, are based on normal operating conditions, are provided for informational purposes only, and are not intended to create any implied warranty of merchantability or fitness for a particular purpose. Fujitsu Computer Products of America, Inc. reserves the right to modify at any time without prior notice these statements, our products, their performance specifications, availability, price and warranty, post-warranty and service programs. Printed in the U.S.A. DS401001125