

## 1 Port 10/100 Mbps Ethernet Parallel Network Print Server

StarTech ID: PM1115P2



The PM1115P2 Ethernet to Parallel Network Print Server lets you convert a standard parallel printer into a shared network printer over a 10/100Mbps network. Providing network printing access allows you to share a single printer among multiple network connected computers, while also avoiding the added costs and inconveniences of purchasing printers for each workstation or area.

This compact, lightweight Ethernet print server connects directly to the Centronics port on your printer, for a discreet solution that doesn't require a cable between your printer and the device - simply connect the device to the network using an RJ45 cable. The ability to position your printer anywhere on the network does away with the need for a dedicated print server PC, saving resources and avoiding performance bottlenecks.

The parallel print server can have you up and running in minutes, using either a remote web-based or Windows® based installation wizard. The print server offers broad operating system compatibility and works with a wide variety of parallel printing devices for easy installation into mixed environments, and also supports Simple Network Management Protocol (SNMP) for remote monitoring.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

### Applications

- Convert a standard parallel printer into a standalone network printer and share a single printer among multiple network connected computers
- A convenient network printing solution for education and government institutions
- Eliminate performance issues of an always-on dedicated PC acting as the printer server

## Features

- Connects directly to the Centronics port of a printer
- Compliant with IEEE 802.3, and IEEE 802.3u standards
- Compact and lightweight
- Supports SNMP for remote printer management - works with most SNMP based applications
- Easy-to-use web interface or Windows-based configuration and setup
- Support for Internet Printing Protocol(IPP), Print Job Control/Status, Email Alert, Rendezvous, DHCP Client, SNMP & HP Web JetAdmin, Windows Print Monitor Technology
- Supports 10/100Mbps Ethernet network

**Technical Specifications**

Warranty	2 Years
Industry Standards	IEEE 802.3 10BASE-T, IEEE 802.3u 100BASE-TX
Interface	Parallel
Interface	RJ45 (10/100 Ethernet)
Ports	1
Connector Type(s)	1 - Centronics (36 pin) Male
Connector Type(s)	1 - RJ-45 Female
Maximum Data Transfer Rate	100Mbps
Remote Management Ability	Yes
Supported Protocols	IPX TCP/IP (LPR, IPP, RAW 9100) NetBEUI AppleTalk SNMP SMB
OS Compatibility	Windows® 8 (32/64bit), 7 (32/64), Vista (32/64), XP (32/64), 2000 Windows® Server 2012, 2008 R2, 2003 (32/64) Mac OS 10.2 and up (Tested up to 10.9) Unix/Linux
Color	Beige
Enclosure Type	Plastic
Product Height	0.9 in [22 mm]
Product Length	2.2 in [56 mm]
Product Weight	1.9 oz [53 g]
Product Width	2 in [52 mm]
LED Indicators	1 - Power/Status: Yellow Solid
LED Indicators	1 - 100Mbps Link/Activity: Green Solid/Flashing
LED Indicators	1 - 10Mbps Link/Activity: Yellow Solid/Flashing
Center Tip Polarity	Positive
Input Current	0.31 A
Input Voltage	100~240V
Output Current	2 A
Output Voltage	3.3 DC
Plug Type	G
Power Adapter Included	Yes
Humidity	10~70% RH
Operating Temperature	0°C to 50°C (32°F to 122°F)
Storage Temperature	0°C to 50°C (32°F to 122°F)
System and Cable Requirements	Ethernet network cable not included
Package Quantity	1

Shipping (Package) Weight	12.8 oz [362 g]
Included in Package	1 - Parallel Print Server
Included in Package	1 - Power Adapter
Included in Package	1 - Software CD
Included in Package	1 - Quick Start Guide

**Certifications, Reports and Compatibility**

