



8 Channel DVR | 960H Recording Resolution | 700TVL Cameras

QC588-4E4-1

Q-See's QC588-4E4-1 compact 8-channel DVR with a 1TB pre-installed hard drive features state-of-the-art 960H resolution for a truer, larger image size of 960 x 480 pixels for even more detailed viewing. This surveillance bundle comes with four high-resolution 700TVL bullet cameras boasting an effective pixel size of 756 x 504. With the addition of high-quality infrared cut filters, images will be bright at night while colors are true-to-life during the day. The indoor/outdoor cameras are weatherproof for greater durability and long-lasting use. Each of the four cameras comes with 60' of standard BNC cable, 3-axis anti-vandal mounting brackets and kits that allow for precise positioning and protect the cables by safely routing them securely through a wall or ceiling.

- Q-See's start-up wizard walks you through setup step-by-step making complete protection easier than ever.
- Real-time recording accommodates up to 30 frames per second on each of its 8 channels and delivers smooth, continuous and uninterrupted video that reveals details not visible to the naked eye.
- The QC588's compact and sleek design offers additional protection against tampering and theft without sacrificing important features.

Q-See's QM9702B 960H cameras coupled with a 960H DVR produces the clearest surveillance image possible for maximum image detail and exceptional viewing on a widescreen monitor or TV screen all while maintaining image integrity and minimizing distortion. The system includes 4 700TVL high-resolution cameras with 976 x 496 effective pixels for sharp, detailed images that ensure the entire property is clearly covered both day and night.

Q-See's new compact QC588 960H DVR boasts all the same features and technology as a conventional DVR but without all the bulk. With an array of remote monitoring features, these DVRs keep you connected. Whether you want to make sure your kids made it home from school, check on employee productivity, monitor customer traffic or see if a package has been delivered, simply download the free Q-See Apps and access your DVR via iPhone, iPad, Android, or Windows Phone from anywhere at any time. Instantly receive email alerts with incident snapshots when motion is detected or even when a camera loses video. With free apps from Q-See for your smartphone or tablet, peace of mind is at your fingertips.

As a leader in innovation, Q-See is the trusted leader in surveillance solutions for home and business, delivering peace of mind anywhere, anytime.

FEATURES:

- Free Q-See Apps for Remote Monitoring
- Compatible with Mac and PC
- HDMI® Port for Hi-Res Viewing
- up to 100ft of Night Vision
- Weatherproof Cameras for Indoor and Outdoor Use
- 4 Cameras with 700 TVL of Resolution
- 8 Channel Real-Time 960H DVR
- Connect up to 4 more cameras

SPECIFICATIONS:

DVR

Model	QC588(DVR)
Video Compression	Advanced H.264
Max Hard Drive Storage	Supports 1 SATA HDD up to 3 TB
Backup Via	PC, Flash Drive, USB Hard Drive
Power	DC12V / 2A (Adapter Included)
Recording Option	NTSC: other: Real Time: 960H Resolution 960,
other Recording Option	











Resolution	NTSC: other (240 FPS/ 30 FPS per channel),
Recording Mode	Motion Detection, Time Schedule, Manual
Video Inputs/Outputs	1 BNC Input(s) / 1 VGA Output(s) / 1 HDMI Output(s) / 1 BNC Output(s)
Network Interface	RJ-45 for Router Connection Enabling Remote Monitoring
DVR Dimensions/Weight	8 x 8 x 2 in / 1.1lbs

Cameras	
Camera Model	QM7008B
Weatherproof	Weatherproof Indoor & Outdoor
IP Rating	65
Horizontal Resolution	700 TV Lines
Image Sensor	1/3, CMOS, Color
Infrared LEDs	Up to 100 ft
Night Vision Range	4.6mm lens 50°-55° field of view
Lens	3-Axis Stands
Mount	60 Feet of Cable with Each Camera
Camera Cables	60 Feet of Cable with Each Camera
Camera Dimensions/Weight	2.25" x 4" x 2.25" (w/o bracket)

Viewing

NTSC	
Live Display Resolution	704x480, 1024x768, 1280x1024
Display Modes	Single Camera, Split Screen Multi-Camera, Auto-Sequence
Video Search	Time, Motion Detection, Manual
Simultaneous Remote Viewers	Up to 20 Users
Stream	Dual Stream

Compatibility

Computer System Support				
Windows	 XP	 Vista	 7	 8
Mactonish	 10.7	 10.8	 10.9	
Compatible Browsers				
Browsers	 Chrome (w/ IE plugin)	 Explorer	 Firefox	
Mobile Phone Support				
iPhone / iPad				
Android				
Windows Phone 7.5/8				