

# VA2249S

**21.5" Full HD IPS Display. Full HD IPS Display for better entertainment experience.**



The ViewSonic VA2249s is a high-performance 21.5" wide-angle display with SuperClear® image enhancement technology that delivers true colour performance and consistent image quality. With Full HD 1080p resolution, 20M:1 MEGA Dynamic Contrast Ratio, and 5ms response time, the VA2249S offers a stunning visual experience for video and photo viewing, web surfing, gaming and more. It combines function and form with an attractive glossy finish and slim bezel design, as well as VGA and DVI inputs for PC or laptop connections. With an integrated power-saving Eco-mode and Energy Star certification, this energy-efficient display has a lower total cost of ownership. VESA-mount and Kensington security lock compliant, the VA2249S is a flexible and secure solution for homes and semi-public areas.

**Full HD Resolution for Superior Pixel Performance**

**SuperClear® technology presents Consistent Color Performance from any angle**

ViewSonic's VA2249S display features Full HD 1920x1080 resolution to deliver superior pixel-by-pixel performance for a more realistic viewing experience. At this resolution you'll experience greater image clarity and detail—qualities that will bring high-definition TV programs, HD movies and other multimedia content to life.



### Dynamic contrast ratio delivers rich color performance


Dynamic contrast ratio defines a differentiating relationship between darkest and brightest colors when reproducing an image. With dynamic contrast ratio, VA2249S is capable of automatically detecting the brightness and darkness of an image and adjusts the LED backlight accordingly. It maximizes grayscale and color ranges and boosts contrast ratio to an 20,000,000:1, resulting in rich, vibrant visuals.



### VESA compliance provides flexible mounting options

This display is compliant with 100mm x 100mm VESA-standard mounts, providing more safe mounting options. It can be mounted on a monitor stand, display or wall, depending on your specific needs. Detachable base also included.

Get the best view, wherever you are. Industry-leading SuperClear® technology delivers 178-degrees of vertical and horizontal viewing angles. Experience accurate, vivid colors, and consistent brightness levels whether you're looking at the screen from above, below, the front, or the side—with no distortion or decay.



### Eco-mode conserves more energy and cuts costs

ViewSonic's proprietary Eco-mode energy-saving feature is built into all LED displays, offering "Optimize (75%)" or "Conserve (50%)" settings that save up to 25% in electricity costs. In low ambient light, Eco-mode adjusts brightness and improves visibility, while reducing eye fatigue. With Eco-mode, the lifespan of the LED backlighting is also greatly increased.



### ENERGY STAR® Certification

The VA2249S is environmentally sound, complete with an energy-saving mercury-free LED backlight and Eco-mode. Its ENERGY STAR® certification means you save up to 40% in energy costs when compared to regular 21.5" monitors.



## Windows®8 certified compliance

Windows®8 Certified, the VA2249S provides the most updated Windows® 8 experience without any compatibility issues. Experience the all-new Windows® 8 operating system with ViewSonic's VA2249S display.



## Technical Specifications

Model No.: VS15451

|                             |                    |   |
|-----------------------------|--------------------|---|
| <b>LCD</b>                  | Type               | 21.5" Wide                                    |
|                             | Display Area       | 21.5 inch                                     |
|                             | Optimum Resolution | 1920x1080                                     |
|                             | Contrast Ratio     | 1000:1 (typical), 20,000,000:1 (DCR)          |
|                             | Brightness         | 250 cd/m <sup>2</sup> (typ)                   |
|                             | Viewing Angles     | 178° horizontal, 178° vertical                |
|                             | Response Time      | 5ms (GTG)                                     |
|                             | Panel Surface      | Anti-glare Type, 3H Hardness                  |
|                             | Light Source       | 30,000hr (min.)                               |
| <b>Video Input</b>          | Analog             | RGB Analog (75Ω, 0.7 / 1.0 Vp-p)              |
|                             | Digital            | DVI (TMDS, 100 ohms)                          |
|                             | Frequency          | Fh: 24-82KHz; Fv: 50-75Hz                     |
|                             | Sync               | Separate Sync / Composite Sync / SOG          |
| <b>Compatibility</b>        | PC                 | VGA up to 1920 x 1080 Non-interlaced          |
|                             | Mac                | MAC up to 1920 x 1080                         |
| <b>Connector</b>            | Analog             | RGB Analog x 1                                |
|                             | Digital            | DVI-D x 1                                     |
|                             | Power              | Internal Power Board , 3-pin Plug (CEE22) x 1 |
| <b>Power</b>                | Voltage            | AC 100 - 240V (Universal); 50 / 60Hz          |
|                             | Consumption        | 26W(typ.). Optimize: 22W, Conserve: 18W       |
| <b>Operating Conditions</b> |                    | VA2249S                                       |

|                         |   |  |
|-------------------------|---|--|
| Temperature             | 32°F to 104°F (0°C to 40°C)   |  |
| Humidity                | 10% to 90% (No Condensation)  |  |
| <b>Dimensions</b>       | Physical  | 505.6mm (width) x 365.9mm (height) x 204.3mm (depth) |
| <b>Weight</b>           | Net   | 3.7 kg   |
| <b>Regulations</b>      | WEEE, RoHS, CE, CB, Window 7, windows 8 UL/c UL, FCC-B, Energy Star, EPEAT (silver), Mexico Energy CU cert, UkrSEPRO + DoC, Erp, REACH SVHC List & DoC, CCC, CEL Level 1, CECP, BSMI, PSB, C-tick, SASO |  |
| <b>Wall Mount</b>       | 100mm * 100mm   |  |
| <b>Package Contents</b> | Power Cable *1, D-Sub *1, Quick Start Guide *1, ViewSonic CD Wizard *1  |  |

For more product information, visit us at [www.viewsonic.com](http://www.viewsonic.com)

All rights reserved by ViewSonic Corporation. All other Corporate names and trademarks are the property of their respective companies. E&OE. All prices and specifications are subject to change without written notice. Images are for illustrative purpose only. Terms & Conditions Apply.

