




PRODUCT SPECIFICATION

CCI CATALOG NUMBER:	L1323
DESCRIPTION:	24 High Intensity LED Portable Work Light
OPERATING ENVIRONMENT:	Indoor / Outdoor
APPROVALS:	cULus

CONSTRUCTION PARAMETERS:

Housing :	Die Cast
Housing finish:	Green
Handle:	Steel w/ Foam Padding
Stand:	Steel H Frame
Reflector:	Nonmetallic
Power switch:	Weatherproof Push button
Battery:	Not Applicable
Cord type:	18/3
Cord length:	3FT
Plug :	Grounded
Dimensions:	12.75" X 11.25" X 6.125"
Lamp type:	(24) 5630 SMD LED's
Lumens:	779
Color Temp:	5700K
Energy Consumed:	10 watts
Lighting Facts:	YES



The information presented here is, to the best of our knowledge, true and accurate. However, since conditions of use are beyond our control, all recommendations or suggestions are presented without guarantee or responsibility on our part. We disclaim all liability in connection with the use of information contained herein or otherwise.

This specification is proprietary intellectual property of Coleman Cable Inc. Any information contained herein shall not be disclosed to any party without written consent of Coleman Cable Inc.