



Xtream S2

Portable Bluetooth 3.0 Wireless Speakers

www.adesso.com



■ Product Overview

The Adesso® Xtream S2 features Bluetooth 3.0 wireless hands-free audio to go along with Double Bass Subwoofer sound technology, with (L/R) Left and Right for high quality stereo sound. Make flawless hands-free phone calls using the integrated microphone. Never run out of Battery with the iOS on-screen indicator. Multipoint technology connects up to two devices at the same time.

■ Bluetooth 3.0 Wireless Technology

Bluetooth 3.0 wireless technology offers 30 feet of wireless freedom, plus lower battery consumption and higher security encryption. Has built in Omni-directional microphone to facilitate hands-free calling capability.

■ Double Bass Subwoofer with (L/R) Stereo


Features subwoofer technology dedicated to the reproduction of low-pitched audio frequencies with (L/R) Left and Right speakers for high quality stereo sound.

■ Rechargeable battery with iOS Indicator


Software interfaces directly with the iOS on your device to show you in real-time how much battery life is available.

■ Effective Range


Stream sound from up to 30' feet (10M)



Bluetooth 3.0 Wireless Technology



Deep Bass Subwoofer



Rechargeable Battery with iOS Indicator



Effective Range

Specifications

Connection	Bluetooth 3.0 +EDR
Bluetooth Profiles	A2DP, AVRCP, HSP, HFP
Music Time	6 Hours
Standby Time	Up to 250 Hours
Charging Time	4~5 Hours
Range	Up to 30' feet
Talk Time	9 Hours
Input	DC : 5V/500ma
Dimensions	6.96 x 2.17 x 2.68 in (17.7 x 5.5 x 6.8cm)
Net Weight	1 lb.
Battery	Rechargeable 1800MAH Li-polymer battery
Color (s)	Black/ Blue/ Pink/ Yellow/ Green

Requirements

Device	Works on most Bluetooth® enabled devices
--------	--

Includes:	Adesso® Xtream S2 Micro USB Charge Cable Quick Start Guide
------------------	--

Shipping Information

ITEM	UPC CODE	Pack Dims	Pack Weight	QTY/Carton
Xtream S2B	783750006422	7.2 x 2.8 x 3.9 in	TBA	10/40
Xtream S2BL	783750006439	7.2 x 2.8 x 3.9 in	TBA	10/40