



IPAC12KS (Cooling only)...12,000 BTU
IPAH12KS (Heat & Cool)....12,000 BTU
IPAC14KS (Cooling only)...14,000 BTU
IPAH14KS (Heat & Cool)....14,000 BTU



PMTS

COOLING UNIT
3-IN-1 MULTIFUNCTION
COOL • FAN • DEHUMIDIFY

COOLING & HEATING UNIT
4-IN-1 MULTIFUNCTION
COOL • HEAT • FAN • DEHUMIDIFY

PORTABLE ROOM AIR CONDITIONER



Whisper Quiet
Operation



Remote Control
with LED Display



24 Hour
Timer



Eco-Friendly
Refrigerant



LED
Display



Auto Restart



No Water
Bucket Needed

PMTS (Personal Mapping Temperature Sensor)



Includes a Deluxe Remote control with large LED display! There is no need to strain your eyes to view the temperature settings on your unit. The "Personal Mapping Temperature Sensor" will sense the temperature from where the remote control is located. The Air conditioner will continue to cool until your desired temperature has reached the area (in the room) where the remote control is located.

SPECS

Model		IPAC12KS	IPAH12KS	IPAC14KS	IPAH14KS
Performance	Cooling Capacity (BTU/hr)	12000	12000	14000	14000
	Heating Capacity (BTU/hr)	/	11000	/	11000
	Application area (Sq. Feet)	450-550 (Recommended up to 300)	450-550 (Recommended up to 300)	550-700 (Recommended up to 400)	550-700 (Recommended up to 400)
	EER	8.9	8.9	8.9	8.9
	Air Flow (m3/h High)	508	508	497	497
Electrical Ratings	Voltage	115	115	115	115
	Watts (Cooling)	1355	1355	1580	1580
	Watts (Heating)	/	1240	/	1240
	Amps (Cooling)	11.8	11.8	13.8	13.8
	Amps (Heating)	/	10.8	/	10.8
	COP (Heating)	/	2.6	/	2.6
	Cord Length (Ft.)	7.4	7.4	7.4	7.4
	PMTS	Yes	Yes	Yes	Yes
Features	Dry Mode	Yes	Yes	Yes	Yes
	Electronic Control /LED Display	Yes	Yes	Yes	Yes
	Remote Control	Yes - w/ LED Display	Yes - w/ LED Display	Yes - w/ LED Display	Yes - w/ LED Display
	Cool/Fan Speed	3/3	3/3	3/3	3/3
	Auto Restart	Yes	Yes	Yes	Yes
	Timer	Yes - 24 Hour	Yes - 24 Hour	Yes - 24 Hour	Yes - 24 Hour
	Sleep Mode	Yes	Yes	Yes	Yes
	Air Direction	2 way - Auto Swing	2 way - Auto Swing	2 way - Auto Swing	2 way - Auto Swing
	Moisture Removal (L/hr)	1.2	1.2	1.4	1.4
	Indoor noise level dB(A) (Low)	54.1	51.5	55.2	49.9
Dimensions	Refrigerant type	R410A	R410A	R410A	R410A
	Unit Width	18.38	18.38	18.38	18.38
	Unit Depth	15.63	15.63	15.63	15.63
	Unit Height	30.14	30.14	30.14	30.14
	Carton Width	20.35	20.35	20.35	20.35
	Carton Depth	17.2	17.2	17.2	17.2
Weight	Net / Gross (Lbs.)	70.55 / 78.26	71.65 / 79.36	72.75 / 81.57	73.85 / 82.67
	Loading Q'ty				
Loading Q'ty	Pallet	12	12	12	12
	Container (40'HQ)	346	346	346	346



IN HOME SERVICE
2YR PARTS & LABOR
5YR SEALED SYSTEM

FLEXIBLE EXHAUST KIT INCLUDED
 EASY ASSEMBLY. NO TOOLS NEEDED
 Exhaust hose extends to 59"
 Window Panel extends up to 48.5" in width