



Planar PT1745R

17" Touch Screen Monitor

The cost-effective Planar PT1745R 17" touch screen monitor is perfect for use in retail, point-of-sale (POS), government, education, healthcare and kiosk applications. Easily integrated with a variety of POS, thin client or PC systems, the touch monitor features 5-wire resistive touch screen with dual RS-232/USB touch screen interface, an internal power supply, speakers and is designed for touch enclosure.



SPECIFICATION	DETAIL
Product Name	PT1745R
Planar Part Number	997-5969-00 (Black)
Viewable Size	17" diagonal (13.30" horizontal x 10.64" vertical)
Touchscreen Type	5-wire Resistive
Number of Touch Points	1
Touchscreen Interface	Dual Serial/USB
Transmissivity	80±2%
Contrast Ratio (typ)	1000:1
Viewing Angle (typ)	170° Horizontal and 160° Vertical
Response Time (typ)	5 ms
Brightness (w/touchscreen)	200 cd/m ²
Brightness (w/o touchscreen)	250 cd/m ²
Brightness (Typical)	N/A
Display Type	LCD Active Matrix Flat Panel Display (TFT)

Display Resolution	1280 X 1024
Aspect Ratio	N/A
Tilt Range	-5° to 90°
Palette	16.7 million colors
Pixel Pitch	0.264 mm
Refresh Rate	56 to 75 Hz
Panel Depth	N/A
Dimensions (W x H x D)	15.2" x 13.5" x 8.0" (386.8 mm x 341.9 mm x 202.0 mm)
Dimensions without Stand	15.2" x 12.6" x 2.3" (386.8 mm x 318.8 mm x 59.0 mm)
Display Weight	12.8 lbs (5.8 kg)
Display Weight (w/o stand)	9.3 lbs (4.2 kg)
Shipping weight	18 lbs (8.2 kg)
Video Inputs	Analog
Audio Output	Integrated stereo speakers with 1W/channel
Compatibility	Windows® 7, Vista, XP, 2000, ME, 98, NT 4.0, CE, XP Embedded, Apple® Mac OS, Linux, HID Compliant - no drivers needed for basic touchscreen operation
External Connections	D-sub 15-pin, D-sub 9-pin, Type B socket USB, Stereo Jack - 3mm, AC Power-in
Power Supply	Internal
Power Requirements	100-240 VAC, 50/60 Hz
Power Consumption (max)	21.4W (1.7W standby, 0.9W off)
Operating Temperature	0° to +40° C
VESA Compatible/Location	Built-in 100 mm VESA, back
Service and Support	3-Year Customer First™ Warranty featuring FREE 2-Day Advance Replacement (US only)
Options / Features	Anti-glare coating, Multi-language display, On screen display (OSD), Kensington® Security Slot
Product Approvals	UL/c-UL, FCC-Class B, CE, RoHS
CI-Black-PN	997-5969-00
CI-White-PN	997-5970-00
In the Box	PT1745R 17" Touchscreen LCD Monitor, Power Cord, VGA Cable, RS-232 Cable, USB Cable (A to B), Audio-in Cable, Driver CD, User's Guide, Quick Start Guide
UPC	8 10689 05969 1

For more information, please visit www.planar.com

Specifications are subject to change without notice.

Specification Report Date: 3/7/2014

© Copyright 2014 Planar Systems, Inc. All rights reserved