

S8

8 Port 10/100Mbps Ethernet Switch

This Ethernet Switch provides 8 x 10/100Mbps Auto-Negotiation RJ45 ports. All ports support auto MDI/MDIX function, eliminating the need for crossover cables or Uplink ports. The S8 Switch provides you with a low-cost, easy to-use, high-performance, seamless and standard upgrade to improve your old network to a 100Mbps network. It will boost your network performance up to full duplex data transfer.



Specifications

Header

- Manufacturer:
 - Amer
- Model:
 - S8

Performance

- Switching Capacity:
 - 1.6Gb
- MAC Address Table Size:
 - 1K
- Networking Standards:
 - IEEE 802.3; IEEE 802.3u; IEEE 802.3x; CSMA/CD;

Ports & Port Features

- RJ45 10/100Base-T:
 - 8
- Auto-negotiation:
 - For port speed and duplex mode
- LED Status Indicators:
 - Port link activity; Port connectivity; Power;

Warranty and Support

- Warranty: Limited lifetime Warranty for as long as the original customer/end user owns the product, or 5 years after product discontinuance, whichever occurs first (excluding power supplies and fans).
- Support: Free technical support (phone/email)

Electronic Features & Electrical Emissions

- Emissions:
 - CE Mark Class A
- Power Supply:
 - 7.5VDC External Power Adapter

Environmental Parameters

- Humidity Range Operating:
 - 10-90%
- Max Operating Temperature:
 - 104F
- Min Operating Temperature:
 - 32F

Dimensions & Weight

- Width x Depth x Height:
 - 74 x 125 x 25mm
- Weight:
 - 1.5lbs(0.68kg)