

USB Crash Cart Adapter with File Transfer & Video Capture

Product ID: NOTECONS02



The USB crash cart adapter gives you control of a headless system, turning your laptop into a portable crash cart for rack servers, PCs, ATMs, kiosks, and more.

Instant System Access

Simply connect the laptop crash cart adapter to your computer using the included USB cable, then connect the integrated USB and VGA cables to your server for instant BIOS-level control. With no server-side software required, you can be up and running instantly.



Troubleshoot More Efficiently

With the flexible software interface, you can transfer files from your laptop to the server, capture videos for records or instructional purposes, take screenshots and scale the display window to full screen mode or smaller, with no scroll bars helping you to troubleshoot faster.

Self-Powered Reliability

Powered from the server-side USB connection, the KVM adapter doesn't require an AC outlet so you can connect to any PC or device that has a VGA and USB port, even if there's no power outlet available.

Take It Anywhere

This pocket-sized adapter features a compact design that easily fits inside your laptop bag and requires no additional accessories to connect, eliminating the need to lug around a large, awkward traditional crash cart to troubleshoot and service your systems.

StarTech.com offers a wide selection of high-quality KVM-related products to help you access your systems more efficiently without the expense and clutter of extra keyboards, mice and monitors. This USB KVM crash cart adapter is backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- ATM and VLT maintenance and repair
- Mobile systems and server repair

Features

- Access any VGA and USB system directly from your laptop via the KVM console adapter
- Set up quickly with included cables and instant BIOS-level control
- Share troubleshooting information and display errors with video capture at 1920 x 1200 60Hz
- Simple self-powered portability with no external power adapter necessary
- Easily troubleshoot systems with bi-directional file transfers between local and remote computer

Hardware	Warranty	2 Years
	Audio	No
	Cables Included	Yes
	Daisy-Chain	No
	KVM Ports	1
	Number of Monitors Supported	1
	PC Interface	USB
	PC Video Type	VGA
	Rack-Mountable	No
Performance	Hot-Key Selection	No
	IP Control	No
	Maximum Analog Resolutions	1920x1200 @ 60Hz
	Maximum Number of Users	1
	MTBF	909000
	On-Screen Display	No
Connector(s)	Console Interface(s)	1 - USB Mini-B (5 pin) Female Input
	Host Connectors	1 - USB Type-A (4 pin) USB 2.0 Male
		1 - VGA (15 pin, High Density D-Sub) Male
Software	OS Compatibility	Windows® XP, Vista, 7, 8, 8.1, 10 Windows Server® 2008 R2, 2012, 2012 R2, 2016, 2019 Mac OS® 10.9 to 10.15 Linux 2.6 to 4.11 <i>LTS versions only</i>
Special Notes / Requirements	Note	If you're interfacing with a Linux device, this adapter is only compatible with standard QWERTY keyboards in U.S English configuration
Indicators	LED Indicators	1 - Host/Server Keyboard/Mouse USB Link 1 - Host/Server Video (VGA) Link 1 - User Console/USB Link
Power	Power Source	USB-Powered
Environmental	Humidity	80% RH
	Operating Temperature	0°C to 40°C (32°F to 104°F)
	Storage Temperature	-40°C to 70°C (-40°F to 158°F)
Physical Characteristics	Cable Length	16.4 in [416 mm]

		1 x 15in (385mm) USB host cable, 1 x 3in (76mm) VGA host cable, 1 x 6ft (1.8m) USB Console cable
	Color	Black
	Enclosure Type	Plastic
	Product Depth	4.5 in [115 mm]
	Product Height	0.6 in [1.5 cm]
	Product Width	2.9 in [74 mm]
	Weight of Product	6 oz [170 g]
Packaging Information	Package Height	1.8 in [46 mm]
	Package Length	11.9 in [30.3 cm]
	Package Width	6.5 in [16.6 cm]
	Shipping (Package) Weight	12.8 oz [363 g]
What's in the Box	Included in Package	1 - USB Crash Cart Adpater
		1 - USB A to Mini-B Cable
		1 - USB Software Key

Product appearance and specifications are subject to change without notice.