

Contour Series 4 Inch LED Downlight Lamp, 3000K. 800 lumens, 80W Halogen Replacement. Dimmable

- 80W halogen replacement lamp
- Simple installation – replaces both recessed housing trim and halogen bulb
- Compatible with 4" recessed can housings
- E26 Socket Adapter included – Also compatible with GU24 connectors (GU24 Adapter not included)
- Reduces energy consumption by over 80% when compared to traditional halogen bulbs.
- 40,000 hour design lifetime* reduces maintenance costs
- Compatible with most commercial dimmers, offering 10-100% dimming performance**
- 3000K, warm white light – ideal for most commercial, hospitality and residential retrofit applications
- Environmentally friendly – contains no mercury or other hazardous materials; UL listed.
- 5-Year Limited Warranty

* Lifetime statement on packaging may state 25,000 hours (directional lamp) or 15,000 hours (decorative lamp) based on Energy Star life testing requirements.

** Dimming range may vary based on dimmer used.



Specifications

Lamp Type	Contour Series 4in Downlight 3000K 800lm
Model	D4-L800-C30-W
Wattage	12W
Lumen Output	800 lm
Efficacy	67 lm/W
Color Temperature	3000K
CRI	80
Beam Angle	90°
Dimmable	Yes
Voltage	120V
Operating Temperature	-20 °C to 40 °C
Socket	E26
Weight	8.96 oz.
Design life	40,000 Hrs.
Part Number	98393