

Contour Series 6 Inch LED Downlight Lamp, 3000K. 1180 lumens, 120W Halogen Replacement. Dimmable

- 120W halogen replacement lamp
- Simple installation – replaces both recessed housing trim and halogen bulb
- Compatible with both 5" and 6" recessed can housings – mounting clips pre-installed in 6" position
- E26 Socket Adapter included – Also compatible with GU24 connectors (GU24 Adapter not included)
- Reduces energy consumption by over 80% when compared to traditional halogen bulbs.
- 40,000 hour design lifetime* reduces maintenance costs
- Compatible with most commercial dimmers, offering 10-100% dimming performance**
- 3000K, warm white light – ideal for most commercial, hospitality and residential retrofit applications
- Environmentally friendly – contains no mercury or other hazardous materials; UL listed.
- 5-Year Limited Warranty

* Lifetime statement on packaging may state 25,000 hours (directional lamp) or 15,000 hours (decorative lamp) based on Energy Star life testing requirements.

** Dimming range may vary based on dimmer used.



Specifications

Lamp Type	Contour Series 6in Downlight 3000K 1180lm
Model	D6-L1180-C30-W
Wattage	19W
Lumen Output	1200 lm
Efficacy	62 lm/W
Color Temperature	3000K
CRI	80
Beam Angle	90 °
Dimmable	Yes
Voltage	120V
Operating Temperature	-20 °C to 40 °C
Socket	E26
Weight	13.12 oz.
Design life	40,000 Hrs.
Part Number	98395