

MR16 GU5.3 12V LED, 3000K. 500 lumens, 50W Halogen Replacement. Dimmable

- High CBCP design allows for direct replacement of 50W halogen MR16 lamps.
- Reduces energy consumption by over 85% when compared to traditional halogen MR16 lamps
- 30,000 hour lifetime reduces maintenance costs
- Warm color temperatures of 2700K and 3000K ideal for retail and hospitality retrofit environments.
- Compatible with the vast majority of existing MR16 lighting fixtures
- Compatible with most commercial dimmers and low voltage electronic transformers, offering 10%-100% dimming performance.
- Environmentally-friendly product has no mercury or other hazardous materials and is RoHS compliant and UL listed.
- 3-year limited warranty

Specifications

Lamp Type	MR16 3000K 500lm
Model	M16-L500-C30-B24
Wattage	7W
Lumen Output	500 lm
Efficacy	71 lm/W
Color Temperature	3000K
CRI	80
Beam Angle	24°
Dimmable	Yes
Voltage	12V
Operating Temperature	-20°C to 40°C
Socket	GU5.3
Weight	1.8 oz.
Design life	30,000 Hrs.
CBCP	2600cd
Part Number	98185

