

Contour Series PAR20 LED Lamp with 40-Degree Beam Angle, 3000K, 490 lumens, 50w Replacement, Dimmable.

- 50W Halogen replacement lamp
- Smooth, streamlined exterior – no visible heat sink fins. Utilizes Thru-Vent technology to increase air circulation for maximum cooling.
- Features non-glare optics to reduce eyestrain and maximize productivity.
- Reduces energy consumption by over 80% when compared to traditional PAR lamps.
- 40,000 hour design lifetime* reduces maintenance costs.
- Compatible with most commercial dimmers, offering 10-100% dimming performance**
- 40-degree beam angle
- 3000K, warm white light – ideal for most commercial, hospitality and residential retrofit applications.
- Cool beam protects illuminated objects from radiated heat. Environmentally friendly – contains no mercury or other hazardous materials; RoHS compliant
- UL, cUL Listed, CE approved
- 5-Year Limited Warranty

* Lifetime statement on packaging may state 25,000 hours (directional lamp) or 15,000 hours (decorative lamp) based on Energy Star life testing requirements.

Specifications

Lamp Type	Contour Series PAR20, 3000K, 490lm, 40-degree beam angle
Model	P20-L490-C307-B40-W
Wattage	8W
Lumen Output	490lm
Efficacy	61 lm/W
Color Temperature	3000K
CRI	80
Beam Angle	40°
Dimmable	Yes
Voltage	120V
Operating Temperature	-20°C to 40°C
Socket	E26
Weight	5.92 oz
Design life	40,000 Hrs.*
CBCP	782 cd
Part Number	98567

