


# Contour Series BR40 LED Lamp, 3000K, 685 lumens, 75w Replacement, Dimmable.

- 75W Halogen replacement lamp
- Uses only 10 watts - reducing energy consumption by over 85% when compared to traditional halogen lamps
- Smooth, streamlined exterior – no visible heat sink fins.
- 40,000 hour design lifetime\* reduces maintenance costs.
- Compatible with most commercial dimmers, offering 10-100% dimming performance\*\*
- 3000K, warm white light – ideal for most commercial, hospitality and residential retrofit applications.
- Environmentally friendly – contains no mercury or other hazardous materials; RoHS compliant
- UL, cUL Listed, CE Approved
- 5-Year Limited Warranty

\* Lifetime statement on packaging may state 25,000 hours (directional lamp) or 15,000 hours (decorative lamp) based on Energy Star life testing requirements.

\*\* Dimming range may vary based on dimmer used.



## Specifications

Lamp Type	Contour Series BR40, 3000K, 685lm
Model	R40-L685-C30-W
Wattage	10W
Lumen Output	685 lm
Efficacy	69 lm/W
Color Temperature	3000K
CRI	80
Beam Angle	-
Dimmable	Yes
Voltage	120V
Operating Temperature	-20°C to 40°C
Socket	E26
Weight	15.5oz
Design life	40,000 Hrs.*
Part Number	98563